

High Performance Schottky Rectifier, 2 A



Cathode ————— Anode

SMA (DO-214AC)


RoHS
COMPLIANT

FEATURES

- Low forward voltage drop
- Guard ring for enhanced ruggedness and long term reliability
- Small foot print, surface mountable
- High frequency operation
- Meets MSL level 1, per J-STD-020, LF maximum peak of 260 °C
- Designed and qualified for industrial level
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912

DESCRIPTION

The VS-20MQ060TRNPbF surface mount Schottky rectifier has been designed for applications requiring low forward drop and very small foot prints on PC boards. Typical applications are in disk drives, switching power supplies, converters, freewheeling diodes, battery charging, and reverse battery protection.

PRODUCT SUMMARY	
Package	SMA (DO-214AC)
$I_{F(AV)}$	2 A
V_R	60 V
V_F at I_F	See Electrical table
I_{RM}	7.5 mA at 125 °C
T_J max.	150 °C
Diode variation	Single
E_{AS}	2.0 mJ

MAJOR RATINGS AND CHARACTERISTICS			
SYMBOL	CHARACTERISTICS	VALUES	UNITS
$I_{F(AV)}$	Rectangular waveform	2	A
V_{RRM}		60	V
I_{FSM}	$t_p = 5 \mu s$ sine	40	A
V_F	2 A _{pk} , $T_J = 125$ °C	0.68	V
T_J	Range	-55 to +150	°C

VOLTAGE RATINGS			
PARAMETER	SYMBOL	VS-20MQ060NTRPbF	UNITS
Maximum DC reverse voltage	V_R	60	V
Maximum working peak reverse voltage	V_{RWM}		

ABSOLUTE MAXIMUM RATINGS						
PARAMETER	SYMBOL	TEST CONDITIONS		VALUES	UNITS	
Maximum average forward current See fig. 4	$I_{F(AV)}$	50 % duty cycle at $T_C = 110$ °C, rectangular waveform On PC board 9 mm ² island (0.013 mm thick copper pad area)		2	A	
		50 % duty cycle at $T_C = 120$ °C, rectangular waveform On PC board 9 mm ² island (0.013 mm thick copper pad area)		1.5		
Maximum peak one cycle non-repetitive surge current See fig. 6	I_{FSM}	5 μs sine or 3 μs rect. pulse	Following any rated load condition and with rated V_{RRM} applied	40	A	
		10 ms sine or 6 ms rect. pulse		10		
Non-repetitive avalanche energy	E_{AS}	$T_J = 25$ °C, $I_{AS} = 1$ A, $L = 4$ mH		2.0	mJ	
Repetitive avalanche current	I_{AR}	Current decaying linearly to zero in 1 μs Frequency limited by T_J maximum $V_A = 1.5 \times V_R$ typical		1.0	A	

ELECTRICAL SPECIFICATIONS						
PARAMETER	SYMBOL	TEST CONDITIONS		VALUES	UNITS	
Maximum forward voltage drop See fig. 1	$V_{FM}^{(1)}$	2 A	$T_J = 25^\circ C$	0.78	V	
		1.5 A		0.71		
		1 A		0.63		
		2 A	$T_J = 125^\circ C$	0.68		
		1.5 A		0.63		
		1 A		0.57		
Maximum reverse leakage current See fig. 2	$I_{RM}^{(1)}$	$T_J = 25^\circ C$	$V_R = \text{Rated } V_R$	0.5	mA	
		$T_J = 125^\circ C$		7.5		
Threshold voltage	$V_{F(TO)}$	$T_J = T_J \text{ maximum}$		0.45	V	
Forward slope resistance	r_t			86.8	$m\Omega$	
Typical junction capacitance	C_T	$V_R = 10 V_{DC}$, $T_J = 25^\circ C$, test signal = 1 MHz		31	pF	
Typical series inductance	L_S	Measured lead to lead 5 mm from package body		2.0	nH	
Maximum voltage rate of change	dV/dt	Rated V_R		10 000	V/ μ s	







Note

(1) Pulse width < 300 μ s, duty cycle < 2 %

THERMAL - MECHANICAL SPECIFICATIONS				
PARAMETER	SYMBOL	TEST CONDITIONS	VALUES	UNITS
Maximum junction and storage temperature range	$T_J^{(1)}$, T_{Stg}		-55 to +150	°C
Maximum thermal resistance, junction to ambient	R_{thJA}	DC operation	80	°C/W
Approximate weight			0.07	g
			0.002	oz.
Marking device		Case style SMA (DO-214AC) (similar D-64)	2H	

Note

(1) $\frac{dP_{tot}}{dT_J} < \frac{1}{R_{thJA}}$ thermal runaway condition for a diode on its own heatsink


Note

(1) Formula used: $T_C = T_J - (Pd + Pd_{REV}) \times R_{thJC}$
 $Pd = \text{forward power loss} = I_{F(AV)} \times V_{FM} \text{ at } (I_{F(AV)}/D)$ (see fig. 6);
 $Pd_{REV} = \text{inverse power loss} = V_{R1} \times I_R (1 - D)$; I_R at $V_{R1} = 80\%$ rated V_R

ORDERING INFORMATION TABLE

Device code	VS-	20	M	Q	060	N	TR	PbF
	1	2	3	4	5	6	7	8
1 - Vishay Semiconductors product								
2 - Current rating (20 = 2 A)								
3 - M = SMA								
4 - Q = Schottky "Q" series								
5 - Voltage rating (060 = 60 V)								
6 - N = new SMA								
7 - TR = tape and reel								
8 - PbF = lead (Pb)-free								

ORDERING INFORMATION (Example)

PREFERRED P/N	PREFERRED PACKAGE CODE	MINIMUM ORDER QUANTITY	PACKAGING DESCRIPTION
VS-20MQ060NTRPbF	5AT	7500	13" diameter plastic tape and reel


LINKS TO RELATED DOCUMENTS

Dimensions	www.vishay.com/doc?95400
Part marking information	www.vishay.com/doc?95403
Packaging information	www.vishay.com/doc?95404
SPICE model	www.vishay.com/doc?95396


SMA

DIMENSIONS in inches (millimeters)

DO-214AC (SMA)



Mounting Pad Layout



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Vishay](#):

[VS-20MQ060NTRPBF](#)