




Relays & Contactors > Relays > Power Relays



Power Relay Type: **Standard**
Coil Magnetic System: **Monostable, DC**
Coil Power Rating DC: **403 mW**
Coil Resistance: **62 Ω**
Coil Special Features: **UL Coil Insulation Class F**

Features

Product Type Features

| | |
|-----------------------|-----------------|
| Power Relay Type | Standard |
| Relay Connection Type | PCB Solder Pins |

Electrical Characteristics

| | |
|--|----------------|
| Insulation Initial Dielectric Between Coil & Contact Class | 4000 V |
| Insulation Initial Dielectric Between Open Contacts | 1000 Vrms |
| Contact Limiting Making Current | 30 A |
| Contact Limiting Short-Time Current | 16 A |
| Contact Limiting Continuous Current | 16 A |
| Insulation Creepage Class | 8 mm |
| Coil Power Rating Class | 400 – 500 mW |
| Insulation Initial Dielectric Between Contacts & Coil | 5000 Vrms |
| Insulation Creepage Between Contact & Coil | 10 mm[.394 in] |
| Contact Limiting Breaking Current | 16 A |
| Coil Magnetic System | Monostable, DC |



| | |
|---------------------------------|----------------------------|
| Coil Power Rating DC | 403 mW |
| Coil Resistance | 62 Ω |
| Coil Special Features | UL Coil Insulation Class F |
| Coil Voltage Rating | 5 VDC |
| Contact Switching Voltage (Max) | 400 VAC |
| Contact Voltage Rating | 250 VAC |

Body Features

| | |
|-----------------------------|-------------------------------------|
| Insulation Special Features | Tracking Index of Relay Base PTI250 |
| Product Weight | 14 g[.494 oz] |

Contact Features

| | |
|------------------------------|---------------|
| Contact Arrangement | 1 Form A (NO) |
| Contact Current Class | 16 A |
| Contact Current Rating (Max) | 16 A |
| Contact Material | AgNi90/10 |
| Contact Number of Poles | 1 |

Mechanical Attachment

| | |
|--------------------|-----------------------|
| Product Mount Type | Printed Circuit Board |
|--------------------|-----------------------|

Dimensions

| | |
|---|------------------|
| Length Class (Mechanical) | 25 – 30 mm |
| Insulation Clearance Class | 8 mm |
| Height Class (Mechanical) | 15 – 16 mm |
| Insulation Clearance Between Contact & Coil | 10 mm[.394 in] |
| Width Class (Mechanical) | 12 – 16 mm |
| Product Width | 12.7 mm[.5 in] |
| Product Length | 29 mm[1.14 in] |
| Product Height | 15.7 mm[.618 in] |

Usage Conditions

| | |
|---|---------------|
| Environmental Ambient Temperature Class | 70 – 85 °C |
| Environmental Ambient Temperature (Max) | 85 °C[185 °F] |

Packaging Features

| | |
|------------------|--------------------|
| Packaging Method | Box & Tube, Carton |
|------------------|--------------------|

Other



| | |
|----------------|-------------|
| Solder Process | Wave Solder |
|----------------|-------------|

Product Compliance

For compliance documentation, visit the product page on TE.com>

| | |
|---|---|
| EU RoHS Directive 2011/65/EU | Compliant |
| EU ELV Directive 2000/53/EC | Compliant |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold |
| EU REACH Regulation (EC) No. 1907/2006 | Current ECHA Candidate List: JAN 2024 (240) Candidate List Declared Against: JAN 2024 (240) Does not contain REACH SVHC |
| Halogen Content | Not Low Halogen - contains Br or Cl > 900 ppm. |
| Solder Process Capability | Wave solder capable to 265°C |


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Also in the Series | [Potter & Brumfield Power PCB Relay RT1](#)



Power Relays(26)

Customers Also Bought



TE Part #DTT-20-03

CRIMP TOOL



TE Part #HDP24-24-16SE-L015

REC, 16P, BLK, E, THD, 12, S



TE Part #K1007153

Toggle Switch 08-1-1-13



TE Part #DRC16-70SBE-P013UK

PLG, 70P, BLK, E, SEAL BOND, B



TE Part #YHDP26-24-35PEL017

PLG, 35P, BLK, E, RNG, 16/20, P



TE Part #2-2176245-2

CRGS1206 5% 56R



TE Part #K1002956

Toggle Switch 08-4-1-13



TE Part #K1008699

Relay 26-60-05



TE Part #SRK-PC-080-25-601

PIN, SOLID, SIZE M8, 25mm2, AG

Documents

- CAD Files

Customer View Model

[ENG_CVM_CVM_1-1419108-2_G.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-1419108-2_G.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-1419108-2_G.2d_dxf.zip](#)



English

3D PDF

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages
Power PCB Relay RT1 Potter & Brumfield

English

Product Specifications
Definitions General Purpose Relays

English

Agency Approvals
VDE Certificate

English

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-1419108-2](#)