



Terminals & Splices > Splices



Wire Size: .34 mm²

Sealable: No

Compatible Insulation Diameter Range: 1.3 mm [.051 in]

Product Length: 12.19 mm [.48 in]

Features

Product Type Features

Sealable	No
----------	----

Termination Features

Termination Method to Wire & Cable	Solder
------------------------------------	--------

Dimensions

Wire Size	.34 mm ²
Compatible Insulation Diameter Range	1.3 mm[.051 in]
Product Length	12.19 mm[.48 in]

Usage Conditions

Insulation Option	Fully Insulated
Operating Temperature Range	-55 – 150 °C[-67 – 302 °F]

Industry Standards

Government Qualified Splice	No
-----------------------------	----

Packaging Features

Packaging Method	Bag
------------------	-----

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Not Compliant



China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2024 (240) Candidate List Declared Against: JAN 2024 (240) SVHC > Threshold: Pb (37% in Solder) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Bromine/Chlorine - Br and Cl < 900 ppm per homogenous material. Also BFR /CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought

TE Part #ABC03N-20P-4048 IN-LINE RECP	TE Part #324159 TERM, RING, PIDG, 16-14, #4	TE Part #2-1617076-4 3SBH1227A2 = M39016/53-008M	TE Part #322819 TERMINAL,SOLIS FLAG R 16-14 10
TE Part #650098-000 D-436-75	TE Part #ABC03O-20P-4048 IN-LINE RECP	TE Part #5053152042 RNF-100-3/8-RD-STK	TE Part #5067244004 DR-25-NR506-0-SP



TE Part #1-2322421-1
M12 A-M-8 CAB ASS (PLG-PLG) 6.0 M
CAT 7

Documents

Product Drawings

D-129-03

English

Datasheets & Catalog Pages

1654025_Sec8_B-155_CWT_D-129_D-141_D-71X

English

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[D-129-03](#)