




Wire Protection & Management > Heat Shrink Shapes > Cable Transitions & Breakouts



Adhesive Requirement: **Adhesive Precoat**
Operating Temperature Range: **-20 – 60 °C [-4 – 140 °F]**
Adhesive Code: **42**
Resistance Protection: **Occasional Fluid Exposure**

Features

Configuration Features

Adhesive Requirement	Adhesive Precoat
----------------------	------------------

Body Features

Primary Product Material	Polyolefin Flexible Modified
--------------------------	------------------------------

Dimensions

Inside Diameter Range (Body)	14 – 43 mm[.55 – 1.69 in]
Inside Diameter Range (Leg 1)	7 – 43 mm[.28 – 1.69 in]

Usage Conditions

Operating Temperature Range	-20 – 60 °C[-4 – 140 °F]
Resistance Protection	Occasional Fluid Exposure

Other

Adhesive Code	42
---------------	----

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2024 (240)




Candidate List Declared Against: JAN 2024
(240)
Does not contain REACH SVHC

Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Customers Also Bought




TE Part #NB13892001
TAT-125-1/2-0-STK




TE Part #204510-1
RECEPT ASSY,104 POSN,AMPLIMITE




TE Part #1-640387-0
10P MTA156 HDR ASSY SQ R/A




TE Part #6979344003
HFT5000 Heat Shrink Tubing




TE Part #889088-000
202C642-71/42-0



TE Part #988208-000
NAE-143-3 HALOGEN LAMP



TE Part #1478769-1
ANTI-VIB NYLON GLD 12MM BLK



TE Part #642145-000
S01-02-R



Documents

Product Drawings

QFT2-130/42-0

English

Datasheets & Catalog Pages

Raychem Molded Parts Visual Guide

English

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[QFT2-130/42-0](#)