



HW

TE Internal #: F34216-000

Standard Labels, UL, Width 9.5 mm [.375 in], Height 8 mm [.315 in], White, Polyester, Label Thickness 97 Micron, HW

[View on TE.com >](#)

Identification & Labeling > Labels > Standard Labels > HW High Tack White Polyester Labels



Label Type: **Industrial Label**

Label Style: **Die-Cut**

Label Adhesive Type: **High Tack Permanent Acrylic Adhesive**

Compatible With Agency/Standards Products: **UL**

Product Width: **9.5 mm [.375 in]**

[All HW High Tack White Polyester Labels \(46\)](#)

Features

Product Type Features

Label Type	Industrial Label
------------	------------------

Body Features

Primary Product Color	White
Primary Product Material	Polyester

Dimensions

Product Width	9.5 mm[.375 in]
Product Height	8 mm[.315 in]

Usage Conditions

Operating Temperature Range	-40 – 150 °C[-40 – 302 °F]
-----------------------------	----------------------------

Printer/Label Features

Number of Labels Across	5
Label Style	Die-Cut
Length of Label Roll	63.5 m[208.33 ft]
Label Thickness	97 Micron

Industry Standards

Compatible With Agency/Standards Products	UL
---	----



Packaging Features

Packaging Quantity	25000
Packaging Method	Roll

Other

Label Adhesive Type	High Tack Permanent Acrylic Adhesive
---------------------	--------------------------------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JAN 2024 (240) Does not contain REACH SVHC
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1-2186500-1
T3212-PRINTER



TE Part # 1-2186502-1
T3224-PRINTER



TE Part # 1-2186503-1
T3224-SWARE-PRINTER



TE Part # 1-2186501-1
T3212-SWARE-PRINTER



Also in the Series | HW

Standard Labels(46)

Customers Also Bought

TE Part #5-1478762-1
Metal backshell 9 way Top Entry-KIT

TE Part #9727873001
99M0111-20-2L

TE Part #3822543004
44A1121-22-0/9-9

TE Part #6632933001
99M0111-16-2L

TE Part #3624213001
99M0111-16-45

TE Part #1631693001
99M0111-12-2L

TE Part #100P275-16-4-C-SB
100P275-16-4-C-SB

Documents

Product Drawings

HW-095080-25-9

English

Datasheets & Catalog Pages

IDENTIFICATION SELECTION GUIDE

English

HW High Tack White Polyester labels

English

Product Specifications

IDENTIFCATION PRINTER PRODUCT RIBBON MATRIX

English

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[HW-095080-25-9](#)