


CUSTOMER DRAWING



Part Description	Product Dimensions		
	L Max	B Ref	ØA Min
RT-555-3/8-2.75/A287-0	69.9 (2.75)	25.4 (1.00)	8.9 (0.35)
RT-555-3/8-4.75/A287-0	120.7 (4.75)	76.2 (3.00)	8.9 (0.35)
RT-555-1/2-2.75/A287-0	69.9 (2.75)	25.4 (1.00)	12.7 (0.50)
RT-555-1/2-5.75/A287-0	146.1 (5.75)	101.6 (4.00)	12.7 (0.50)
RT-555-3/4-3.00/A287-0	76.2 (3.00)	31.8 (1.25)	18.3 (0.72)
RT-555-3/4-6.75/A287-0	171.5 (6.75)	127.0 (5.00)	18.3 (0.72)
RT-555-1.0-3.75/A287-0	95.3 (3.75)	50.8 (2.00)	22.8 (0.90)
RT-555-1.0-6.75/A287-0	171.5 (6.75)	127.0 (5.00)	22.8 (0.90)

MATERIALS

1. INSULATION SLEEVE: Heat-shrinkable, radiation cross-linked modified fluoropolymer. Color: Black.
2. MELTABLE INSERT: Environment resistant modified thermoplastic fluoroelastomer. Color: Light Blue

APPLICATION

1. This part is designed to provide an immersion resistant seal on wires having insulation diameters as specified on table and temperature rating of at least +150°C (302°F).
2. Temperature range: -65°C to +200°C (-85°F to +392°F).
Maximum temperature of 260°C (500°F) when exposed for 500 continuous hours.

		Raychem Devices	TITLE: SEALING SLEEVE		
TE CONNECTIVITY (TE) RESERVES THE RIGHT TO CHANGE THIS DRAWING AT ANYTIME. USERS SHOULD EVALUATE THE SUITABILITY OF THE PRODUCT FOR THEIR APPLICATION.			DOCUMENT NO.: RT-555-X/X-YYY/A287-0		
TOLERANCES: 0.00 N/A 0.0 N/A 0 N/A	ANGLES: N/A ROUGHNESS IN MICRON	Unless otherwise specified dimensions are in millimeters. [Inches dimensions are shown in brackets]	REV: A2	DATE: August 12, 2015	
PREPARED BY: RODRIGUEZ	CAGE CODE: 06090	ECO NUMBER: ECO-15-011757	SCALE: NTS	SIZE: A	SHEET: 1 of 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[EG7669-000](#)