


Surface Mount Trench MOS Barrier Schottky Rectifier

TMBS® eSMP® Series



Top View

Bottom View

SlimSMA (DO-221AC)

Cathode  Anode 

DESIGN SUPPORT TOOLS

3D
Models
Available

[click logo to get started](#)

FEATURES

- Very low profile - typical height of 0.95 mm
- Ideal for automated placement
- Trench MOS Schottky technology
- Low power losses, high efficiency
- Low forward voltage drop
- Meets MSL level 1, per J-STD-020, LF maximum peak of 260 °C
- AEC-Q101 qualified available
 - Automotive ordering code: base P/NHM3
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912



RoHS
COMPLIANT
HALOGEN
FREE

TYPICAL APPLICATIONS

For use in high frequency inverters, freewheeling, DC/DC converters, and polarity protection in commercial, industrial, and automotive applications.

MECHANICAL DATA

Case: SlimSMA (DO-221AC)

Molding compound meets UL 94 V-0 flammability rating
Base P/N-M3 - halogen-free, RoHS-compliant
Base P/NHM3 - halogen-free, RoHS-compliant, and AEC-Q101 qualified

Terminals: matte tin plated leads, solderable per J-STD-002 and JESD 22-B102
M3 and HM3 suffix meets JESD 201 class 2 whisker test

Polarity: color band denotes cathode end

PRIMARY CHARACTERISTICS	
$I_{F(AV)}$	5.0 A
V_{RRM}	150 V
I_{FSM}	100 A
V_F at $I_F = 5.0$ A (125 °C)	0.66 V
T_J max.	150 °C
Package	SlimSMA (DO-221AC)
Circuit configuration	Single

MAXIMUM RATINGS ($T_A = 25$ °C unless otherwise noted)			
PARAMETER	SYMBOL	VSSAF515	UNIT
Device marking code		V515	
Maximum repetitive peak reverse voltage	V_{RRM}	150	V
Maximum average forward rectified current	$I_{F(AV)}^{(1)}$	1.8	A
	$I_{F(AV)}^{(2)}$	5.0	
Peak forward surge current 10 ms single half sine-wave superimposed on rated load	I_{FSM}	100	A
Operating junction and storage temperature range	T_J, T_{STG}	-40 to +150	°C

Notes

(1) Free air, mounted on recommended copper pad area
(2) Mounted on 30 mm x 30 mm pad area

ELECTRICAL CHARACTERISTICS ($T_A = 25^\circ\text{C}$ unless otherwise noted)							
PARAMETER	TEST CONDITIONS		SYMBOL	TYP.	MAX.	UNIT	
Instantaneous forward voltage	$I_F = 2.5 \text{ A}$	$T_A = 25^\circ\text{C}$	V_F ⁽¹⁾	0.77	-	V	
	$I_F = 5.0 \text{ A}$			1.02	1.10		
	$I_F = 2.5 \text{ A}$	$T_A = 125^\circ\text{C}$		0.58	-		
	$I_F = 5.0 \text{ A}$			0.66	0.75		
Reverse current	$V_R = 100 \text{ V}$	$T_A = 25^\circ\text{C}$	I_R ⁽²⁾	0.01	-	mA	
		$T_A = 125^\circ\text{C}$		0.6	-		
	$V_R = 150 \text{ V}$	$T_A = 25^\circ\text{C}$		-	0.2		
		$T_A = 125^\circ\text{C}$		2	5		
Typical junction capacitance	4.0 V, 1 MHz		C_J	280	-	pF	

Notes

(1) Pulse test: 300 μs pulse width, 1 % duty cycle

(2) Pulse test: Pulse width $\leq 40 \text{ ms}$

THERMAL CHARACTERISTICS ($T_A = 25^\circ\text{C}$ unless otherwise specified)				
PARAMETER	SYMBOL	VSSAF515		UNIT
Typical thermal resistance	$R_{\theta JA}$ ⁽¹⁾⁽²⁾	115		°C/W
	$R_{\theta JM}$ ⁽³⁾	12		

Notes

(1) Free air, mounted on recommended PCB, 2 oz. pad area; thermal resistance $R_{\theta JA}$ - junction to ambient, $R_{\theta JM}$ - junction to mount







(2) The heat generated must be less than thermal conductivity from junction-to-ambient: $dP_D/dT_J < 1/R_{\theta JA}$

(3) Mounted on 30 mm x 30 mm pad area

ORDERING INFORMATION (Example)				
PREFERRED P/N	UNIT WEIGHT (g)	PREFERRED PACKAGE CODE	BASE QUANTITY	DELIVERY MODE
VSSAF515-M3/H	0.032	H	3500	7" diameter plastic tape and reel
VSSAF515-M3/I	0.032	I	14 000	13" diameter plastic tape and reel
VSSAF515HM3/H ⁽¹⁾	0.032	H	3500	7" diameter plastic tape and reel
VSSAF515HM3/I ⁽¹⁾	0.032	I	14 000	13" diameter plastic tape and reel

Note

(1) AEC-Q101 qualified

RATINGS AND CHARACTERISTICS CURVES ($T_A = 25^\circ\text{C}$ unless otherwise noted)

Fig. 1 - Maximum Forward Current Derating Curve

Fig. 4 - Typical Reverse Leakage Characteristics

Fig. 2 - Forward Power Loss Characteristics

Fig. 5 - Typical Junction Capacitance

Fig. 3 - Typical Instantaneous Forward Characteristics

Fig. 6 - Typical Transient Thermal Impedance





Fig. 7 - Thermal Resistance Junction to Ambient
vs. Copper Pad Area

PACKAGE OUTLINE DIMENSIONS in inches (millimeters)



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Vishay](#):

[VSSAF515HM3/H](#) [VSSAF515-M3/H](#) [VSSAF515-M3/I](#) [VSSAF515HM3/I](#)