


REV. 0
DCO 142764

COIL: @ 25°C
RESISTANCE _____ 500 OHMS \pm 10%
NOMINAL VOLTAGE _____ 12.0 VDC
MUST OPERATE _____ 7.0 VDC
MUST RELEASE _____ 4.0 VDC MAX, 0.63 VDC MIN.

ENVIRONMENT:
VIBRATION _____ 10 _____ CPS TO _____ 3000 _____ CPS @ _____ 30 _____ g's
SHOCK _____ 75 _____ g's _____ 6 _____ MS. DURATION
TEMPERATURE _____ -65 _____ °C TO _____ +125 _____ °C
NOTES: OPERATE TIME 2.0 MS MAX
RELEASE TIME 2.0 MS MAX
CONTACT BOUNCE 1.5 MS MAX

CUSTOMER DATA SHEET



TERMINAL VIEW

CONTACT RATING: LOW LEVEL TO 1A
28 VDC RESISTIVE 100,000 OPERATIONS

DR. PBB 2/27/01 (K) *[Signature]* 2/28/01

CH Technologies
advanced control electronic solutions

CUST. _____ QPL
CUST. NO. M39016/7-034L REV. _____ "J1MA" RELAY

J1MAC-12XLS

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1617118-1](#)