

D

C

B




A

D


C

B


A




SECTION A-A



SECTION B-B



SECTION C-C



SECTION D-D

- 1 UNPLATED
- 2 .000030 GOLD ON CONTACT AREA, GOLD FLASH ON THE REMAINDER, ALL OVER .000050 NICKEL.
- 3 GOLD PLATING NOT REQUIRED THIS AREA.
- 4 .000050 NICKEL ENTIRE CONTACT, .000015 GOLD ON CONTACT AREA.
- 5 SHEARED EDGES PERMITTED TO BE UNPLATED.
- 6 PREPLATED .000050-.000150 BRIGHT TIN.
- 7. REELED FOR MINI APPLICATOR.
- 8 .000015 GOLD ON CONTACT AREA, .000100-.000200 BRIGHT TIN-LEAD ON AREA K, OVER .000050 NICKEL.
- 9 CUT OUTS ON BOX AT MANUFACTURER'S OPTION.
- 10 .000030 GOLD ON CONTACT AREA, .000100-.000200 BRIGHT TIN-LEAD IN AREA K, ALL OVER .000050 NICKEL.
- 12 POINT OF MEASUREMENT FOR PLATING THICKNESS (INSIDE BEAMS)
- 13 OBSOLETE PART NUMBER
- 14 .000015 GOLD ON CONTACT AREA, .000100-.000200 MATTE TIN ON AREA K, OVER .000050 NICKEL.
- 15 .000030 GOLD ON CONTACT AREA, .000100-.000200 MATTE TIN IN AREA K, ALL OVER .000050 NICKEL.

6-102316-4	5 15	5-102316-8
6-102316-3	5 14	5-102316-6
1-102316-4	5 10	102316-8
1-102316-3	5 8	102316-6
1-102316-2	6	102316-5
1-102316-1	4 5	102316-3
1-102316-0	13 2	102316-2
---	1	102316-1
LOOSE PIECE PART NO	FINISH	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
INCHES

MATERIAL
CU-SN-P ALLOY 521
.008 THK

SEE TABLE

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	±	-
1 PLC	±	-
2 PLC	±	-
3 PLC	±	0.13 [.005]
4 PLC	±	-
ANGLES	±	-

FINISH

DWN
—
CHK
—
APVD
—

15 NOV 78
14 FEB 79
20 FEB 79

PRODUCT SPEC
—
APPLICATION SPEC
—
WEIGHT
—

CUSTOMER DRAWING

TE Connectivity

CONTACT, FEMALE, MOD IV
CRIMP SNAP-IN

SIZE
A2

CAGE CODE
00779

DRAWING NO
C=102316

RESTRICTED TO
—

SCALE
8:1

SHEET
1 of 1

REV
R2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[6-102316-4](#)