


## High Current Density Surface-Mount TMBS® (Trench MOS Barrier Schottky) Rectifier

Ultra Low  $V_F$  = 0.53 V at  $I_F$  = 5 A

### eSMP® Series



### SMPC (TO-277A)



### DESIGN SUPPORT TOOLS

[click logo to get started](#)



### PRIMARY CHARACTERISTICS

|                       |                |
|-----------------------|----------------|
| $I_{F(AV)}$           | 10 A           |
| $V_{RRM}$             | 120 V          |
| $I_{FSM}$             | 160 A          |
| $V_F$ at $I_F$ = 10 A | 0.63 V         |
| $T_J$ max.            | 175 °C         |
| Package               | SMPC (TO-277A) |
| Circuit configuration | Single         |

### FEATURES

- Very low profile - typical height of 1.1 mm
- Trench MOS Schottky technology
- Low forward voltage drop, low power losses
- High efficiency operation
- Meets MSL level 1, per J-STD-020, LF maximum peak of 260 °C
- AEC-Q101 qualified available
  - Automotive ordering code: base P/NHM3
- Material categorization: for definitions of compliance please see [www.vishay.com/doc?99912](http://www.vishay.com/doc?99912)



**RoHS**  
COMPLIANT  
HALOGEN  
FREE

### TYPICAL APPLICATIONS

For use in low voltage high frequency DC/DC converters, freewheeling, and polarity protection applications.

### MECHANICAL DATA

#### Case: SMPC (TO-277A)

Molding compound meets UL 94 V-0 flammability rating  
Base P/N-M3 - halogen-free, RoHS-compliant  
Base P/NHM3\_X - halogen-free, RoHS-compliant, and AEC-Q101 qualified  
("X") denotes revision code e.g. A, B, ....)

**Terminals:** matte tin plated leads, solderable per J-STD-002 and JESD 22-B102

M3 suffix meets JESD 201 class 2 whisker test, HM3 suffix meets JESD 201 class 2 whisker test

### MAXIMUM RATINGS ( $T_A$ = 25 °C unless otherwise noted)

| PARAMETER   | SYMBOL    | V10PM12     | UNIT |
|---|-----------|-------------|------|
| Device marking code   |           | 10M12       |      |
| Maximum repetitive peak reverse voltage   | $V_{RRM}$ | 120         | V    |
| Maximum DC forward current  | $I_F$ (1) | 10          | A    |
|   | $I_F$ (2) | 3.9         |      |
| Peak forward surge current 10 ms single half sine-wave superimposed on rated load | $I_{FSM}$ | 160         | A    |
| Operating junction temperature range  | $T_J$ (3) | -40 to +175 | °C   |
| Storage temperature range   | $T_{STG}$ | -55 to +175 | °C   |

#### Notes

(1) Mounted on 30 mm x 30 mm pad areas aluminum PCB

(2) Free air, mounted on recommended pad area

(3) The heat generated must be less than the thermal conductivity from junction to ambient:  $dP_D/dT_J < 1/R_{\theta JA}$

| ELECTRICAL CHARACTERISTICS ( $T_A = 25^\circ\text{C}$ unless otherwise noted) |                       |                           |             |      |      |               |  |
|---|-----------------------|---------------------------|-------------|------|------|---------------|--|
| PARAMETER   | TEST CONDITIONS       |                           | SYMBOL      | TYP. | MAX. | UNIT          |  |
| Instantaneous forward voltage   | $I_F = 5 \text{ A}$   | $T_A = 25^\circ\text{C}$  | $V_F^{(1)}$ | 0.60 | -    | V             |  |
|   | $I_F = 10 \text{ A}$  |                           |             | 0.75 | 0.83 |               |  |
|   | $I_F = 5 \text{ A}$   | $T_A = 125^\circ\text{C}$ |             | 0.53 | -    |               |  |
|   | $I_F = 10 \text{ A}$  |                           |             | 0.63 | 0.71 |               |  |
| Reverse current   | $V_R = 90 \text{ V}$  | $T_A = 25^\circ\text{C}$  | $I_R^{(2)}$ | 2.9  | -    | $\mu\text{A}$ |  |
|   |                       | $T_A = 125^\circ\text{C}$ |             | 2.0  | -    | $\text{mA}$   |  |
|   | $V_R = 120 \text{ V}$ | $T_A = 25^\circ\text{C}$  |             | -    | 400  | $\mu\text{A}$ |  |
|   |                       | $T_A = 125^\circ\text{C}$ |             | 4.8  | 28   | $\text{mA}$   |  |
| Typical junction capacitance  | 4.0 V, 1 MHz          |                           | $C_J$       | 900  | -    | $\text{pF}$   |  |

**Notes**

(1) Pulse test: 300  $\mu\text{s}$  pulse width, 1 % duty cycle

(2) Pulse test: Pulse width  $\leq 5 \text{ ms}$

| THERMAL CHARACTERISTICS ( $T_A = 25^\circ\text{C}$ unless otherwise noted) |                          |         |  |  |                           |
|--|--------------------------|---------|--|--|---------------------------|
| PARAMETER  | SYMBOL                   | V10PM12 |  |  | UNIT                      |
| Typical thermal resistance   | $R_{\theta JA}^{(1)(2)}$ | 62      |  |  | $^\circ\text{C}/\text{W}$ |
|  | $R_{\theta JM}^{(3)}$    | 4       |  |  |                           |

**Notes**

(1) The heat generated must be less than the thermal conductivity from junction to ambient:  $dP_D/dT_J < 1/R_{\theta JA}$







(2) Free air, mounted on recommended PCB, 2 oz. pad area; thermal resistance  $R_{\theta JA}$  - junction to ambient


(3) Units mounted on 30 mm x 30 mm aluminum PCB, thermal resistance  $R_{\theta JM}$  - junction to mount

| ORDERING INFORMATION (Example) |                 |                        |               |                                    |  |
|--------------------------------|-----------------|------------------------|---------------|------------------------------------|--|
| PREFERRED P/N                  | UNIT WEIGHT (g) | PREFERRED PACKAGE CODE | BASE QUANTITY | DELIVERY MODE                      |  |
| V10PM12-M3/86A                 | 0.10            | 86A                    | 1500          | 7" diameter plastic tape and reel  |  |
| V10PM12-M3/87A                 | 0.10            | 87A                    | 6500          | 13" diameter plastic tape and reel |  |
| V10PM12HM3_A/H <sup>(1)</sup>  | 0.10            | H                      | 1500          | 7" diameter plastic tape and reel  |  |
| V10PM12HM3_A/I <sup>(1)</sup>  | 0.10            | I                      | 6500          | 13" diameter plastic tape and reel |  |

**Note**

(1) Automotive grade

**RATINGS AND CHARACTERISTICS CURVES** ( $T_A = 25^\circ\text{C}$  unless otherwise noted)

**Fig. 1 - Forward Current Derating Curve**

**Fig. 4 - Typical Reverse Leakage Characteristics**

**Fig. 2 - Forward Power Loss Characteristics**

**Fig. 5 - Typical Junction Capacitance**

**Fig. 3 - Typical Instantaneous Forward Characteristics**

**Fig. 6 - Typical Transient Thermal Impedance**

**PACKAGE OUTLINE DIMENSIONS** in inches (millimeters)


Conform to JEDEC® TO-277A

## **Disclaimer**

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Vishay](#):

[V10PM12-M3/87A](#) [V10PM12HM3\\_A/H](#) [V10PM12-M3/86A](#) [V10PM12HM3\\_A/I](#)