



1	ASSEMBLY MAY BE BROKEN TO THE DESIRED NUMBER OF POSITIONS.
2	THE NOTED DIMENSIONS APPLY AT THE INTERSECTION OF THE POST AND HOUSING
3	POINT OF MEASUREMENT FOR PLATING THICKNESS
4	BREAKAWAY NOTCH ANGLE CAN BE ORIENTED TO THE RIGHT (AS SHOWN) OR TO THE LEFT
5	FINISH: POSTS— .000015 GOLD ON CONTACT AREA, .000100—.000200 MATTE TIN—LEAD ON SOLDER TAIL, ALL OVER .000050 NICKEL
6	FINISH: POSTS— .000015 GOLD ON CONTACT AREA, .000100—.000200 MATTE TIN ON SOLDER TAIL, ALL OVER .000050 NICKEL
7	HIGH TEMPERATURE CONFIGURATION
8	OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

OBSOLETE	8	3.984	3.900	39	40	4-102974-0
	6	3.884	3.800	38	39	3-102974-9
	8	3.784	3.700	37	38	3-102974-8
	6	3.684	3.600	36	37	3-102974-7
	8	3.584	3.500	35	36	3-102974-6
	6	3.484	3.400	34	35	3-102974-5
	8	3.384	3.300	33	34	3-102974-4
	6	3.284	3.200	32	33	3-102974-3
	8	3.184	3.100	31	32	3-102974-2
	6	3.084	3.000	30	31	3-102974-1
	8	2.984	2.900	29	30	3-102974-0
	6	2.884	2.800	28	29	2-102974-9
	8	2.784	2.700	27	28	2-102974-8
	6	2.684	2.600	26	27	2-102974-7
	8	2.584	2.500	25	26	2-102974-6
	6	2.484	2.400	24	25	2-102974-5
	8	2.384	2.300	23	24	2-102974-4
	6	2.284	2.200	22	23	2-102974-3
	8	2.184	2.100	21	22	2-102974-2
	OBSOLETE	6	2.084	2.000	20	21
8		1.984	1.900	19	20	2-102974-0
6		1.884	1.800	18	19	1-102974-9
8		1.784	1.700	17	18	1-102974-8
6		1.684	1.600	16	17	1-102974-7
8		1.584	1.500	15	16	1-102974-6
6		1.484	1.400	14	15	1-102974-5
8		1.384	1.300	13	14	1-102974-4
6		1.284	1.200	12	13	1-102974-3
8		1.184	1.100	11	12	1-102974-2
OBSOLETE	6	1.084	1.000	10	11	1-102974-1
	8	.984	.900	9	10	1-102974-0
OBSOLETE	6	.884	.800	8	9	102974-9
	8	.784	.700	7	8	102974-8
SUP BY 5-102974-7	6	.684	.600	6	7	102974-7
OBSOLETE	8	.584	.500	5	6	102974-6
	6	.484	.400	4	5	102974-5
SUP BY 5-102974-3	8	.384	.300	3	4	102974-4
	6	.284	.200	2	3	102974-3
OBSOLETE	8	.184	.100	1	2	102974-2
	6	.084	—	—	1	102974-1
	PLATING	C	B	A	NO OF POSN	PART NUMBER

4805 (3/11)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[6-102974-2](#)