





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	Y	REVISED PER ECR-17-002209	10APR2017	RS	MM
	Z	REVISED PER ECO-17-015890	31OCT2017	RS	MM



RECOMMENDED HOLE LAYOUT



SECTION A-A

- 1 .000100 BRIGHT TIN-LEAD OVER .000050 NICKEL.
- 2 POINT OF MEASUREMENT FOR PLATING THICKNESS.
- 3 THE NOTED DIMENSIONS APPLY AT THE INTERSECTION OF THE POST AND THE HOUSING.
- 4 ON ASSEMBLIES WITH FOUR OR MORE POSITIONS, TWO POLARIZATION SLOTS. ON ASSEMBLIES WITH TWO OR THREE POSITIONS, ONE POLARIZATION SLOT.
- 5 .000100 BRIGHT TIN OVER .000050 NICKEL.
- 6 PRELIMINARY PART-NOT RELEASED FOR PRODUCTION.
- 7 .000100 MATTE TIN OVER .000050 NICKEL.
- 8 HIGH TEMPERATURE CONFIGURATION
- 9 STANDOFFS NOT PRESENT ON UNDERSIDE OF ASSEMBLY
- 10 SUPERSEDED BY P/N 5-103639-2.
- 11 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

THIS DRAWING IS A CONTROLLED DOCUMENT.

0

PLC

±

-

1

PLC

±

-

2

PLC

±

0.13[.005]

3

PLC

±

-

4

PLC

±

-

ANGLES

±

-

TOLERANCES UNLESS OTHERWISE SPECIFIED:

SEE TABLE

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN

S.SHUEY

05MAR91

CHK

L.CASTAGNA

27MAR93

APVD

L.CASTAGNA

27MAR93

PRODUCT SPEC

108-25034

APPLICATION SPEC

114-25026

MATERIAL

HOUSING:

FINISH

SEE TABLE

WEIGHT

-

CUSTOMER DRAWING

NAME

HDR ASY,VERT,SNGL ROW
2.54[100] C/L 0.64[025] SQ PST,
WTH PLZN<CHNG,AMPMODU MTE

SIZE

A2

CAGE CODE

-

DRAWING NO

103639

RESTRICTED TO

-

SCALE

4:1

SHEET

1 OF 2

REV

Z

TE Connectivity

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[6-103639-4](#)