



LOC	DIST	REVISIONS					
AD	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			F	REVISED PER ECO-14-000066	27JUN2014	NK	MM



RECOMMENDED HOLE LAYOUT

- ① THE NOTED DIMENSIONS APPLY AT THE INTERSECTION OF THE POST AND THE HOUSING
- ② POINT OF MEASUREMENT FOR PLATING THICKNESS
- ③ SELECTIVE POSTS ARE FORMED TO PROVIDE CONNECTOR RETENTION TO PC BOARD UNTIL SOLDERED. RETENTION FEATURE IS FOR .055 MINIMUM PC BOARD THICKNESS. SEE DETAIL Z FOR FORM AND TABLE FOR LOCATIONS.
- ④ BREAKAWAY NOTCH ANGLE CAN BE ORIENTED TO THE RIGHT (AS SHOWN) OR TO THE LEFT
- ⑤ POSTS: .000015 GOLD IN CONTACT AREA, .000100-.000200 MATTE TIN-LEAD ON SOLDER TAIL, ALL OVER .000050 NICKEL.
- ⑥ POSTS: .000015 GOLD IN CONTACT AREA, .000100-.000200 MATTE TIN ON SOLDER TAIL, ALL OVER .000050 NICKEL.
- ⑦ HIGH TEMPERATURE CONFIGURATION.
- ⑧ OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

OBSOLETE			1,2,3,4,37,38,39,40	3.984	3.900	39	40	7-104430-7
			1,2,3,4,32,33,34,35	3.484	3.400	34	35	7-104430-6
			1,2,3,4,27,28,29,30	2.984	2.900	29	30	7-104430-5
			1,2,3,4,23,24,25,26	2.584	2.500	25	26	7-104430-4
			1,2,3,4,22,23,24,25	2.484	2.400	24	25	7-104430-3
			1,2,3,4,21,22,23,24	2.384	2.300	23	24	7-104430-2
			1,2,3,4,20,21,22,23	2.284	2.200	22	23	7-104430-1
			1,2,3,4,19,20,21,22	2.184	2.100	21	22	7-104430-0
			1,2,3,4,18,19,20,21	2.084	2.000	20	21	6-104430-9
			1,2,3,4,17,18,19,20	1.984	1.900	19	20	6-104430-8
			1,2,3,4,16,17,18,19	1.884	1.800	18	19	6-104430-7
			1,2,3,4,15,16,17,18	1.784	1.700	17	18	6-104430-6
			1,2,3,4,14,15,16,17	1.684	1.600	16	17	6-104430-5
			1,2,3,4,13,14,15,16	1.584	1.500	15	16	6-104430-4
			1,2,3,4,12,13,14,15	1.484	1.400	14	15	6-104430-3
			1,2,3,4,11,12,13,14	1.384	1.300	13	14	6-104430-2
			1,2,3,4,10,11,12,13	1.284	1.200	12	13	6-104430-1
			1,2,3,4,9,10,11,12	1.184	1.100	11	12	6-104430-0
			1,2,3,4,8,9,10,11	1.084	1.000	10	11	5-104430-9
	 OBSOLETE			1,2,3,4,7,8,9,10	.984	.900	9	10
			1,2,3,4,6,7,8,9	.884	.800	8	9	5-104430-7
			1,2,3,4,5,6,7,8	.784	.700	7	8	5-104430-6
			1,2,3,4,5,6,7	.684	.600	6	7	5-104430-5
			1,2,3,4,5,6	.584	.500	5	6	5-104430-4
			1,2,3,4,5	.484	.400	4	5	5-104430-3
			1,2,3,4	.384	.300	3	4	5-104430-2
			1,2,3	.284	.200	2	3	5-104430-1
			1,2,3,4,37,38,39,40	3.984	3.900	39	40	2-104430-7
			1,2,3,4,32,33,34,35	3.484	3.400	34	35	2-104430-6
			1,2,3,4,27,28,29,30	2.984	2.900	29	30	2-104430-5
			1,2,3,4,23,24,25,26	2.584	2.500	25	26	2-104430-4
			1,2,3,4,22,23,24,25	2.484	2.400	24	25	2-104430-3
			1,2,3,4,21,22,23,24	2.384	2.300	23	24	2-104430-2
			1,2,3,4,20,21,22,23	2.284	2.200	22	23	2-104430-1
			1,2,3,4,19,20,21,22	2.184	2.100	21	22	2-104430-0
			1,2,3,4,18,19,20,21	2.084	2.000	20	21	1-104430-9
			1,2,3,4,17,18,19,20	1.984	1.900	19	20	1-104430-8
			1,2,3,4,16,17,18,19	1.884	1.800	18	19	1-104430-7
			1,2,3,4,15,16,17,18	1.784	1.700	17	18	1-104430-6
		1,2,3,4,14,15,16,17	1.684	1.600	16	17	1-104430-5	
		1,2,3,4,13,14,15,16	1.584	1.500	15	16	1-104430-4	
		1,2,3,4,12,13,14,15	1.484	1.400	14	15	1-104430-3	
		1,2,3,4,11,12,13,14	1.384	1.300	13	14	1-104430-2	
		1,2,3,4,10,11,12,13	1.284	1.200	12	13	1-104430-1	
		1,2,3,4,9,10,11,12	1.184	1.100	11	12	1-104430-0	
		1,2,3,4,8,9,10,11	1.084	1.000	10	11	104430-9	
		1,2,3,4,7,8,9,10	.984	.900	9	10	104430-8	
		1,2,3,4,6,7,8,9	.884	.800	8	9	104430-7	
		1,2,3,4,5,6,7,8	.784	.700	7	8	104430-6	
		1,2,3,4,5,6,7	.684	.600	6	7	104430-5	
		1,2,3,4,5,6	.584	.500	5	6	104430-4	
		1,2,3,4,5	.484	.400	4	5	104430-3	
		1,2,3,4	.384	.300	3	4	104430-2	
		1,2,3	.284	.200	2	3	104430-1	
REMARKS	PLATING		HOLD-DOWN POST CONFIG LOCATIONS	C	B	A	NO OF POSN	ASSEMBLY PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DIN 28JUN88 H. MOLL GFK R. FEIDT 28JUN88		 TE Connectivity	
DIMENSIONS: INCHES 		TOLERANCES UNLESS OTHERWISE SPECIFIED: APVD R. FEIDT 28JUN88 PRODUCT SPEC — APPLICATION SPEC		NAME HEADER ASSY, MOD II, BREAKAWAY, SINGLE ROW, .100 C/L, RT ANGLE, .025 SQ POSTS, WITH HOLD - DOWN CONFIG	
MATERIAL: INVENTING: FLAME RETARDANT THERMOPLASTIC COLOR: BLACK POST: COPPER ALLOY		WEIGHT: — CUSTOMER DRAWING		SIZE: CAGE CODE: DRAWING NO: A1 00779 C=104430 RESTRICTED TO: —	
FINISH: SEE TABLE		SCALE: 4:1		SHEET: 1 OF 1 REV: F	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[7-104430-7](#)