

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
A1	-		B3	REWORKED PER ECR 09-026789	08DEC2009	MH	BR
			B4	ECR-11-002636	05APR2011	SR	AR
			B5	REVISED PER ECR-16-016780	22AUG2017	NG	MKO

Exploded view diagram of a telescope. The main tube (1) is shown with a sliding mechanism. The eyepiece (2) is shown separately. The diagram is labeled "SCALE 5:1".

Technical drawing of a mechanical part, showing a side view and a cross-section. The side view is a rectangle with a central vertical slot. The cross-section is a rectangle with a central vertical slot. The drawing includes dimension lines and a section line.

$\varnothing A_{-0.05}$



A dimension line with arrows at both ends, indicating a width of $B + 0.05$.


1	MATERIAL SEE TABLE
2	SURFACE SEE TABLE
3	ASSEMBLY WEIGHT SEE TABLE
4	PACKAGING: 50 PIECES IN POLY-BAG 0-1243085-8
5	PACKAGING: 500 PIECES IN POLY-BAG 0-1243085-8
6	PACKAGING: 10 PIECES IN POLY-BAG 0-1243085-8
7	CROSS-SECTION MARKING

SCALE 4:1

[illegible][illegible]

HN.D - C - Bu, Ag, Ni, 1.5 mm 2
HN.D - C - Bu, Ag, Ni, 4, 0 mm 2
HN.D - C - Bu, Cu, Ni, 0, 14 - 0, 37 mm 2
HN.D - C - Bu, Fe, Au, 0, 14 - 0, 37 mm 2
HN.D - C - Bu, Au, 2, 5 mm 2
HN.D - C - Bu, Au, 1, 5 mm 2
HN.D - C - Bu, Au, 0, 75 - 1, 00 mm 2
HN.D - C - Bu, Au, 0, 5 mm 2
HN.D - C - Bu, Au, 0, 14 - 0, 37 mm 2
HN.D - C - Bu, Ag, 2, 5 mm 2
HN.D - C - Bu, Ag, 1, 5 mm 2
HN.D - C - Bu, Ag, 0, 75 - 1, 00 mm 2
HN.D - C - Bu, Ag, 0, 5 mm 2
HN.D - C - Bu, Ag, 0, 14 - 0, 37 mm 2

TE Connectivity

DIMENSIONS: mm 	TOLERANCES UNLESS OTHERWISE SPECIFIED: ISO 2875 DIN 152-2768 m6- DIN 9000-150 <table><tr><td>0</td><td>PLC</td><td>±</td></tr><tr><td>1</td><td>PLC</td><td>±</td></tr><tr><td>2</td><td>PLC</td><td>±</td></tr><tr><td>3</td><td>PLC</td><td>±</td></tr><tr><td>4</td><td>PLC</td><td>±</td></tr></table> ANGLES ±1°	0	PLC	±	1	PLC	±	2	PLC	±	3	PLC	±	4	PLC	±
0	PLC	±														
1	PLC	±														
2	PLC	±														
3	PLC	±														
4	PLC	±														
MATERIAL 1	FINISH 2															

DWN Braun	23.07.1997	 TE Connectivity			
CHK Schnurpfel	23.07.1997				
APVD -	-	NAME SOCKET CONTACT SERIES HN.D -			
PRODUCT SPEC 108-74018					
APPLICATION SPEC 114-74015		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
WEIGHT -		A2	00779	C=1105051	-
CUSTOMER DRAWING		SCALE 10:1	SHEET 1 OF 1	REV B5	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[3-1105051-2](#)