

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
E	B		C	ECR-05-016219	24NOV05	JMS	FWK

NOTES:

- 1 PACK IN ACCORDANCE WITH AMP SPEC 107-3275
- 2 100 TRAY PACK IN ACCORDANCE WITH AMP SPEC 107-3275
- 3 Ag PLATING
- 4 THIS ITEM MUST BE WHITE
- 5 HAND TOOL : 9-1478240-0
- 6 DIE SET : 9-1478242-0

- 7 ELECTRICAL CHARACTERISTICS

FREQUENCY RANGE:

NOMINAL IMPEDANCE:

INSULATION RESISTANCE:

WORKING VOLTAGE:

DIELECTRIC WITHSTAND VOLTAGE:

CONTACT RESISTANCE:

CENTRE CONTACT:

OUTER CONTACT:

VSWR @ 2GHz:

INSERTION LOSS dB @ x 2 GHz:

DC - 2 GHz

75 Ohm

5000 MOhm

500 Volts RMS at Sea Level

1500 Volts RMS Max

1.50 mOhm Max

0.20 mOhm Max

1.20:1 Max

0.20 Max
- 8 MECHANICAL CHARACTERISTICS

COUPLING RETENTION FORCE:

CABLE RETENTION FORCE:

MOUNT NUT RECOMMENDED TORQUE:

DURABILITY:

N/A



170N Min

4N


500 Cycles Min
- 9 ENVIRONMENTAL CHARACTERISTICS

OPERATING TEMPERATURE:

-65 to +165 DegC



		1	1	BRASS	3	CONTACT	8
		1	1	BRASS	3	FERRULE	7
		1	1	BRASS	3	CHASSIS	6
		1	1	PTFE		INSULATION	5
		1	1	BRASS	3	BODY	4
		1	1	SILICON RUBBER	4	GASKET	3
		1	1	STEEL	3	LOCKWASHER	2
		1	1	BRASS	3	HEX NUT	1
		6--0	1--0	MATERIAL		DESCRIPTION	ITEM
		3	3				
QUANTITY PER ASSY				PARTS LIST			

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J.SANDWELL	24NOV05	tyco Electronics		Tyco Electronics Corporation	
		CHK S.PARLOW	24NOV05			Bideford EX39 4HE	
DIMENSIONS: mm	<div>TOLERANCES UNLESS OTHERWISE SPECIFIED:</div> <div><div>0 PLC ± -</div><div>1 PLC ± -</div><div>2 PLC ± -</div><div>3 PLC ± -</div><div>4 PLC ± -</div><div>ANGLES ± -</div></div>	APVD F.WHEELER-KING	24NOV05	NAME			
		PRODUCT SPEC	BNC BULKHEAD JACK REAR MOUNT CRIMP 75 OHM				
		108-3435	RG59B/U, 62A/U, 140/U, 210/U, URM90,				
		APPLICATION SPEC	KX6A, KX25, KX52, KX53				
MATERIAL	FINISH	411-3247		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
SEE TABLE	-	WEIGHT	-	A3	00779	C-1337436	-
CUSTOMER DRAWING				SCALE	NTS	SHEET	1 OF 1
						REV	C

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-1337436-0](#)