




1. RECOMMENDED SPARE PARTS.
2. GREASE RAM, CAM, CAM FOLLOWER AND FEED ROD LIGHTLY.
3. LUBRICATE DAILY PER THE APPLICATOR INSTRUCTION SHEET SUPPLIED WITH THE APPLICATOR.
4. CRIMP TENSILE VALUE TO BE 70% OF THE WIRE TENSILE STENGTH.
5. THIS APPLICATOR WAS DESIGNED SPECIFICALLY FOR GERMAN MARKET ONLY.
6. WIRE RANGE QUOTED IS THAT OF THE TERMINAL & SHOWN FOR INFORMATION PURPOSES ONLY.



QTY READ PER ASSY				PARTS LIST			
		DIMENSIONS: mm [INCHES] DO NOT SCALE PRINT. TOLERANCES UNLESS OTHERWISE SPECIFIED: 1 PLC DEC ±0.5 [0.2 IN] 2 PLC DEC ± 3 PLC DEC ± ANGLES ± SURF TEXTURE: ✓		MATL —		HT TR —	
				FIN —			
		DR 26NOV01 MCLIFFORD		APP 26NOV01 F.BACKHURST		 AMP Incorporated Harrisburg, PA 17105-3608	
		CHK —		REL 29-05-02 MCLIFFORD			
TE 12-03 MC MAY02 APP DATE		REMOVE BURRS, BREAK SHARP EDGES RO.38 MAX		NAME SIDE FEED HD-I APPLICATOR		MACHINE REF HD-I APPL	
		SCALE —		D DNG NO 1426274		SHEET 1 of 1 REV B	
		CAGE CODE 00779		CUSTOMER AND ASSEMBLY DRAWING			
						RESTRICTED TO —	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1426274-2](#)