








1438129-1
SHOWN WITH SPACER
IN SEATED POSITION





MIN. FEED THRU
CONDITION WITH 1mm
CLEARANCE ALL AROUND
SHOWN WITH SPACER IN SEATED POSITION



SHOWN WITH CAM
LEVER AND SPACER
IN LOADED POSITION




SECTION A-A
SPACER AND LEVER IN
PRE-SEATED POSITION
(DELIVERY CONDITION)



REVISIONS					
P.	LTR	DESCRIPTION	DATE	DWN	APVD
F32		REVISED PER ECO-16-003418	08MAR2016	DLD	DCM
F33		REVISED PER ECO-16-018427	25JAN2017	DLD	DCM
F34		REVISED PER ECO-17-007768	30MAY2017	DLD	DCM
F35		REVISED PER ECO-17-014872	24OCT2017	JMS	CM

1. PRINT PART NUMBER (5S4T-14A464-L*-***, 5S4T-14A464-M*-***, 5S4T-14A464-N*-***) AND TRACEABILITY (YY : 2 DIGIT YEAR, JJJ = JULIAN DATE, HH = 2 DIGIT MILITARY HOUR CODE IN THE LOCATION AT ASSEMBLY. SEE SHEET 3 THRU 7 (-*) PART NUMBERS.
2. APPLICABLE MOLEX (1.5) POWER TERMINAL PART NUMBERS:
33012-0002 TIN 0.50-1.50mm²
3. CAM LEVER AND SPACER ARE SHIPPED IN THEIR PRE-ASSEMBLED POSITIONS.
4. REFERENCE TE CONNECTIVITY INSTRUCTION SHEET 408-8893.
5. COMPANY LOGO.





SCALE 1:1

APPLICABLE COMPONENTS (FOR REFERENCE ONLY)						
DESCRIPTION	NOMINAL TERMINAL SIZE	COLOR/ PLATING	FORD COMPONENT PART NUMBER	SUPPLIER PART NUMBER	MATERIAL/SPECIFICATION NUMBER	SAE WIRE SIZE
TERMINAL - FEMALE (Ag)	0.64 (CAT. 0)	SILVER	7S4T-14474-AA	1393366-2	COPPER ALLOY/SILVER PLATE	20AWG
						18AWG
TERMINAL - FEMALE (Ag)	0.64 (CAT. 0)	SILVER	7S4T-14474-BA	1393367-2	COPPER ALLOY/SILVER PLATE	22AWG
TERMINAL - FEMALE (Sn)	0.64 (CAT. 0)	TIN	1L2T-14474-AA	1393366-1	COPPER ALLOY/TIN PLATE	20AWG
						18AWG
TERMINAL - FEMALE (Sn)	0.64 (CAT. 0)	TIN	1L2T-14474-BA	1393367-1	COPPER ALLOY/TIN PLATE	22AWG
TERMINAL - FEMALE (Au)	0.64 (CAT. 0)	GOLD	1L2T-14474-CA	1393365-1	COPPER ALLOY/GOLD PLATE	20AWG
						18AWG
TERMINAL - FEMALE (Au)	0.64 (CAT. 0)	GOLD	1L2T-14474-DA	1393364-1	COPPER ALLOY/GOLD PLATE	22AWG


ANY DESIGN CHANGES ON THIS ASSEMBLY MAY
ALSO BE REQUIRED ON ASSEMBLY DRAWING 1438691

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN R. VESTAL	15APR2005	NAME TE Connectivity 50-WAY HARNESS ASSEMBLY, PCM	SIZE A1	CAGE CODE 00779	DRAWING NO. 1438129	RESTRICTED TO -
DIMENSIONS:			CHK T. VALASEK	15APR2005					
TOLERANCES UNLESS OTHERWISE SPECIFIED:			APVD T. VALASEK	15APR2005					
mm			PRODUCT SPEC						
0 PLC ±0.3			APPLICATION SPEC						
1 PLC ±0.10			WEIGHT						
2 PLC ±0.10			CUSTOMER DRAWING						
3 PLC ±0.10									
4 PLC ±0.10									
ANGLES ±1°									
FINISH									
MATERIAL									


REVISIONS					
P.	LTR.	DESCRIPTION	DATE	DWN.	APVD.
-	-	SEE SHEET 1	-	-	-




1438129-1
KEYING OPTION "A"




1438129-2
KEYING OPTION "B"




1438129-3
KEYING OPTION "C"



1438129-4
KEYING OPTION "D"



1438129-5
KEYING OPTION "E"



1438129-6
KEYING OPTION "F"

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R. VESTAL 15APR2005	TE Connectivity	
DIMENSIONS:		CHK T. VALASEK 15APR2005		
mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD T. VALASEK 15APR2005	NAME 50-WAY HARNESS ASSEMBLY, PCM	
	0 PLC ±.3 1 PLC ±0.3 2 PLC ±0.10 3 PLC ±. 4 PLC ±. ANGLES ±1° FINISH	PRODUCT SPEC APPLICATION SPEC	SIZE A100779	
MATERIAL	-	WEIGHT	C=1438129	
-	-	CUSTOMER DRAWING	SCALE 2:1 SHEET 2 OF 10 REV F35	

[illegible]

REVISIONS				
P	LYR	DESCRIPTION	DATE	DWN APVD
-	-	SEE SHEET 1	-	- -

KEYING OPTION B

CAVITIES WITH A NUMERIC SYMBOL INDICATES CLOSED TERMINAL LOCATIONS

BLANK CAVITIES INDICATES OPEN TERMINAL HOLE LOCATIONS

TERMINAL HOLE POSITION

5S4T-14A464-M* PIN-OUT CHART

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN
CHK
T. VALASEK

15APR2005

DIMENSIONS:
mm

0 PLC
1 PLC
2 PLC
3 PLC
4 PLC
ANGLES
FINISH

±
±0.3
±0.10
±
±
#1°
-

MATERIAL
-

-

TOLERANCES UNLESS OTHERWISE SPECIFIED:

±
±0.3
±0.10
±
±
#1°
-

PRODUCT SPEC
-

APPLICATION SPEC
-

WEIGHT
-

CUSTOMER DRAWING

DWN
CHK
T. VALASEK

15APR2005

NAME
50-WAY HARNESS ASSEMBLY, PCM

SIZE
A1

CAGE CODE
100779

DRAWING NO
C=1438129

RESTRICTED TO
-

SCALE
1:1

SHEET
4


OF
10

REV
F35



TE Connectivity

8	7	6	5	4	3	2	1
THIS DRAWING IS UNPUBLISHED.		RELEASED FOR PUBLICATION		20			
COPYRIGHT 20		BY -		ALL RIGHTS RESERVED.			


8		7		6		5		4		3		2		1	
THIS DRAWING IS UNPUBLISHED.				RELEASED FOR PUBLICATION				20							
© COPYRIGHT 20				BY -				ALL RIGHTS RESERVED.							



SCALE 2:1




SECTION B-B



DETAIL E
SCALE 8:1


NOTES: UNLESS OTHERWISE SPECIFIED

- GENERAL TOLERANCE:
±0.3 ALL ONE PLACE DIMENSIONS
±0.10 ALL TWO PLACE DIMENSIONS
±1°00' ALL ANGULAR DIMENSIONS
- DRAFT ANGLE PERMISSIBLE ONLY WITHIN DRAWING TOLERANCE.
- SEALING SURFACE, NO WITNESS LINES OR DAMAGE PERMITTED.
- ALL UNMARKED RADIUS TO BE 0.5 MAX., UNLESS OTHERWISE SPECIFIED.
- VENT HOLE SIZE AND LOCATION IS OPTIONAL.
- THIS AREA TO REMAIN CLEAR FOR THE HARNESS ASSEMBLY.
- TERMINAL POSITION IDENTIFICATION.
- MATES WITH TYCO ELECTRONICS PART NUMBERS 1438129-# & 1438950-#












SECTION A-A

SEE RECOMMENDED CONTACT
PIN 0.8 X 1.5 DETAIL

THIS DRAWING IS A CONTROLLED DOCUMENT.		OWN R. VESTAL	15APR2005	 TE Connectivity	
DIMENSIONS:		CHK T. VALASEK	15APR2005		
mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD T. VALASEK	15APR2005	NAME 50-WAY HARNESS ASSEMBLY, PCM	
	0 PLC ±.3	PRODUCT SPEC		SIZE CAGE CODE DRAWING NO	
	1 PLC ±0.10	APPLICATION SPEC		RESTRICTED TO	
MATERIAL		WEIGHT		A100779C=1438129	
FINISH		CUSTOMER DRAWING		SCALE 1:1 SHEET 9 OF 10 REV F35	

HEADER INTERFACE KEYING OPTIONS

REVISIONS				
P	LTR	DESCRIPTION	DATE	OWN APVD
-	-	SEE SHEET 1	-	-



THIS DRAWING IS A CONTROLLED DOCUMENT.		OWN R. VESTAL 15APR2005	TE Connectivity
DIMENSIONS:		CHK T. VALASEK 15APR2005	
mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD T. VALASEK 15APR2005	NAME 50-WAY HARNESS ASSEMBLY, PCM
	0 PLC ±0.3	PRODUCT SPEC	SIZE CAGE CODE DRAWING NO
	1 PLC ±0.10	APPLICATION SPEC	A100779C=1438129
	2 PLC ±0.10	WEIGHT	RESTRICTED TO
	3 PLC ±0.10	CUSTOMER DRAWING	SCALE 1:1 SHEET 10 OF 10 REV F35
	4 PLC ±0.10		
MATERIAL	FINISH		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1924783-7](#)