



2		1						
LOC	DIST	REVISIONS						
HB		P	LTR	DESCRIPTION	ECN	DATE	DWN	APVD

3. CONNECTION DIAGRAM(BOTTOM VIEW)




4. DRILLING DIAGRAM



1-1461758-2	48V	SRUUh-SH-148DM1	I
1-1461758-1	24V	SRUUh-SH-124DM1	k
1-1461758-0	12V	SRUUh-SH-112DM1	j
1461758-9	9V	SRUUh-SH-109DM1	i
1461758-8	6V	SRUUh-SH-106DM1	h
1461758-7	5V	SRUUh-SH-105DM1	g
1461758-6	48V	SRUUh-SS-148DM1	f
1461758-5	24V	SRUUh-SS-124DM1	e
1461758-4	12V	SRUUh-SS-112DM1	d
1461758-3	9V	SRUUh-SS-109DM1	c
1461758-2	6V	SRUUh-SS-106DM1	b
1461758-1	5V	SRUUh-SS-105DM1	a
PART NO	PART B	PART A	TYPE

RELAY TYPE

		UV RESIN	UV SEAL	14
		EPOXY RESIN	SEAL	13
		UEW	MAGNETIC WIRE	12
UL 94V-0		PBT	CASE	11
UL 94V-0		PBT	BOBBIN	10
		CP WIRE	COIL TERMINAL	9
		Ag ALLOY	STATIONARY CONTACT	8
		Ag ALLOY	MOVABLE CONTACT	7
		Cu ALLOY	DUMMY B-TERMINAL	6
		Cu	M-TERMINAL	5
		Cu ALLOY	MOVABLE SPRING	4
	Ni PLATING	STEEL	CORE	3
	Ni PLATING	STEEL	ARMATURE	2
	Ni PLATING	STEEL	YOKE	1
INCOMBUSTIBILITY	TREATMENT	MATERIAL	DESCRIPTION	ITEM



NOTE:
LOT NO. SYSTEM AS FOLLOWING:

WEEK
YEAR

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.	
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:
	0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±
MATERIAL	FINISH

DWN	CHK	APVD	PRODUCT SPEC	APPLICATION SPEC	WEIGHT	CUSTOMER DRAWING
Tyco Electronics Tyco Electronics Corporation ShenZhen, China						NAME SRUUh-DM1 ,000 CUSTOMER DRAWING
SIZE A3	CAGE CODE 00779	DRAWING NO C= 1461758	RESTRICTED TO -	SCALE 5:1	SHEET 2 OF 2	REV B

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-1461758-0](#)