THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION -,- -
© COPYRIGHT - By - ALL RIGHTS RESERVED.

LOC	DIST
AD	39

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	P	REVISED PER ECO-11-004820	21MAR11	RK	HMR

1. ASSEMBLY MAY BE BROKEN TO THE DESIRED NUMBER OF POSITIONS
2. TRUE POSITION TOLERANCE OF THE POST TIPS APPLIES WHEN THE HEADER IS HELD FLAT AGAINST THE PRINTED CIRCUIT BOARD
3. THE NOTED DIMENSIONS APPLY AT THE INTERSECTION OF THE POST AND HOUSING
4. HOUSING: FLAME RETARDANT THERMOPLASTIC; COLOR: BLACK.
5. FINISH: 0.000381 [.000015] GOLD ON CONTACT AREA, ALL OVER 0.00127 [.000050] NICKEL ENTIRE POST.





RECOMMENDED HOLE LAYOUT

G	F	E	NO. OF POSITIONS	PART NUMBER
101.19 [3.984]	99.06 [3.900]	39	40	4-146482-0
98.65 [3.884]	96.52 [3.800]	38	39	3-146482-9
96.11 [3.784]	93.98 [3.700]	37	38	3-146482-8
93.57 [3.684]	91.44 [3.600]	36	37	3-146482-7
91.03 [3.584]	88.90 [3.500]	35	36	3-146482-6
88.49 [3.484]	86.36 [3.400]	34	35	3-146482-5
85.95 [3.384]	83.82 [3.300]	33	34	3-146482-4
83.41 [3.284]	81.28 [3.200]	32	33	3-146482-3
80.87 [3.184]	78.74 [3.100]	31	32	3-146482-2
78.33 [3.084]	76.20 [3.000]	30	31	3-146482-1
75.79 [2.984]	73.66 [2.900]	29	30	3-146482-0
73.25 [2.884]	71.12 [2.800]	28	29	2-146482-9
70.71 [2.784]	68.58 [2.700]	27	28	2-146482-8
68.17 [2.684]	66.04 [2.600]	26	27	2-146482-7
65.63 [2.584]	63.50 [2.500]	25	26	2-146482-6
63.09 [2.484]	60.96 [2.400]	24	25	2-146482-5
60.55 [2.384]	58.42 [2.300]	23	24	2-146482-4
58.01 [2.284]	55.88 [2.200]	22	23	2-146482-3
55.47 [2.184]	53.34 [2.100]	21	22	2-146482-2
52.93 [2.084]	50.80 [2.000]	20	21	2-146482-1
50.39 [1.984]	48.26 [1.900]	19	20	2-146482-0
47.85 [1.884]	45.72 [1.800]	18	19	1-146482-9
45.31 [1.784]	43.18 [1.700]	17	18	1-146482-8
42.77 [1.684]	40.64 [1.600]	16	17	1-146482-7
40.23 [1.584]	38.10 [1.500]	15	16	1-146482-6
37.69 [1.484]	35.56 [1.400]	14	15	1-146482-5
35.15 [1.384]	33.02 [1.300]	13	14	1-146482-4
32.61 [1.284]	30.48 [1.200]	12	13	1-146482-3
30.07 [1.184]	27.94 [1.100]	11	12	1-146482-2
27.53 [1.084]	25.40 [1.000]	10	11	1-146482-1
24.99 [.984]	22.86 [.900]	9	10	1-146482-0
22.45 [.884]	20.32 [.800]	8	9	146482-9
19.91 [.784]	17.78 [.700]	7	8	146482-8
17.37 [.684]	15.24 [.600]	6	7	146482-7
14.83 [.584]	12.70 [.500]	5	6	146482-6
12.29 [.484]	10.16 [.400]	4	5	146482-5
9.75 [.384]	7.62 [.300]	3	4	146482-4
7.21 [.284]	5.08 [.200]	2	3	146482-3
4.67 [.184]	2.54 [.100]	1	2	146482-2
2.13 [.084]	– –	–	1	146482-1

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm [INCHES]

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ± –
1 PLC ± –
2 PLC ± 0.51[.02]
3 PLC ± 0.127[.005]
4 PLC ± 0.0127[.0005]
ANGLES ± –

MATERIAL 4

FINISH 5

DWN E. BRANDBERG 14-MAR-97
CHK G. DUBNICZKI 14-MAR-97
APVD G. DUBNICZKI 14-MAR-97
PRODUCT SPEC –
APPLICATION SPEC –
WEIGHT –

TE Connectivity

NAME HEADER ASSEMBLY, MOD II, STACKING, SINGLE ROW, .025 SQ.POST, UNSHROUDED

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A1	00779	C-146482	–

CUSTOMER DRAWING

SCALE 4:1 SHEET 1 OF 1 REV P

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

TE Connectivity:

1-146482-0