


1. HOUSING: HIGH-TEMPERATURE, GLASS-FILLED POLYMER. COLOR: GRAY OR WHITE
POST: BRASS.
2. POST: DIN 41612 CLASS 2 IN CONTACT AREA, TIN-LEAD ON POSTS.
3. RECOMMENDED HOLE SIZE FOR MANUAL APPLICATION OF CONNECTOR ONTO PC BOARD.
4. PART NUMBER, DATE CODE MARKED THIS APPROXIMATE AREA.
5. MARKINGS ON THIS SIDE.
6. THE 5.69 [.224] LONG MAKE FIRST POSTS EXCEED THE ALIGNMENT CAPABILITY OF THE HOUSING AND COULD POSSIBLY STUB DURING MATING. CUSTOMER MUST TAKE THIS INTO CONSIDERATION IN CARD CAGE DESIGN.



SECTION Z-Z

1-32	NONE	B	32	148528-2
1-32	NONE	A	32	
1-3,6-15,18,20-23,25,31,32	4,5,16,17,19,24,26-30	B	32	
2,3,6,7,11-14,16,20-24,29-31	1,4,5,8-10,15,17-19,25-28,32	A	32	148528-1
POSITIONS LOADED WITH 5.69 [.224] CONTACTS	POSITIONS LOADED WITH 4.16 [.164] CONTACTS	ROWS	NO OF LOADED POSITIONS	PART NUMBER
THIS DRAWING IS A CONTROLLED DOCUMENT.		Tyco Electronics Corporation Harrisburg, PA 17105-3608		
DIMENSIONS: mm [INCHES]		NAME		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		SIZE CAGE CODE DRAWING NO		
0 PLC ± -		RESTRICTED TO		
1 PLC ± -		WEIGHT		
2 PLC ± 0.13 [.005]		A1 00779 148528		
3 PLC ± -		CUSTOMER DRAWING		
4 PLC ± -		SCALE 5:1 SHEET 1 OF 1 REV B		
ANGLES ± -				
FINISH				
MATERIAL				

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[148528-2](#)