

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD

D

C

B

A

REPLACED BY OCEAN STYLE APPLICATOR PART NUMBER

FOR REPLACEMENT PARTS FOR APPLICATOR REFER TO ADDITIONAL PAGE(S). SPARE PARTS KIT (IF LISTED) WILL REMAIN AVAILABLE.

THE REPLACEMENT OCEAN STYLE APPLICATOR HAS THE SAME TERMINATOR/PRESS INTERFACE AS APPLICATOR

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:



TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±

1 PLC ±

2 PLC ±

3 PLC ±

4 PLC ±

ANGLES ±

FINISH

MATERIAL

DWN

CHK

APVD

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

TE Connectivity

NAME

SIZEA3

CAGE CODE

DRAWING NOG-

RESTRICTED TO

SCALE

SHEET OF

REV

1470-19 (3/11)

Pro/ENGINEER DRAWING

[illegible]

- [illegible]

	POST FEED 40 mm STROKE	POST FEED 30 mm STROKE	PRE FEED 30 mm STROKE	PRE FEED 40 mm STROKE
LOC				
A				
DIST				
66				

ON INSTALLATION, SET WIRE DISC TO LARGEST WIRE SIZE SETTING. USE OF SETTINGS BELOW MIN REQUIRED CRIMP HEIGHT SETTING WILL CAUSE DAMAGE TO CRIMP TOOLING.

				DIMENSIONS: mm [INCHES] DO NOT SCALE PRINT.				MATL		HT TR		FIN			
				TOLERANCES UNLESS OTHERWISE SPECIFIED:				DR LLOTHOUSE		23SEP04 APP		23SEP04 F BACKHURST			
				1 PLC DEC ±				CHK		REL		21-10-04 M CLIFFORD			
				2 PLC DEC ±				NAME		FINE ADJ SIDE FD HD-I APPL					
				3 PLC DEC ±				SURF TEXTURE:		SCALE		DWG NO			
				ANGLES ±				REMOVE BURRS, BREAK		1528452		SHEET			
				SHARP EDGES: NO.38 MAX				D		1 OF 1		REV			
E ECR-11-018513				RS	SEP11					MACHINE REF					
D ECR-11-011976				LZ/SX	01/0011					HD-I APPL					
C ECR-06-020043				TM	ADG-06										
B 0150-1481-04				BH	DEC04										
A SEE ECN 015A-0800-04				MC	0CT04										
P	F	LTR	REVISION	RECORD	APP	DATE									
3							CUSTOMER AND ASSEMBLY DRAWING							RESTRICTED TO	
CAGE CODE 00779														-	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1528452-2](#)