





- 1 CONNECTOR BODY AND JAM NUT MATERIAL: 6061-T6 ALUMINUM, ELECTROLESS NICKEL PLATED PER SAE-AMS-C-26074 OR SAE-AMS-2404E
LOCKING RING MATERIAL: BERYLLIUM COPPER, ELECTROLESS NICKEL PLATED PER SAE-AMS-C-26074 OR SAE-AMS-2404E
INSULATOR MATERIAL: LIQUID CRYSTAL POLYMER (LCP) PER ASTM D5138 OR POLYPHENYLENE SULFIDE (PPS) PER ASTM D4067
O-RING MATERIAL: FLUOROSILICONE
- 2 WIRE TERMINATION: 28 AWG SOLID, 30 AWG STRANDED WIRE OR SMALLER
- 3 LUBRICATE O-RING WITH PARKER SUPER-O-LUBE PRIOR TO INSTALLATION
- 4 THIS DRAWING ALSO IDENTIFIED AS NANONICS 303-0024

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M. STORRY 4 MAY 99	 TE Connectivity				
		CHK E. PAULUS 7 MAY 99					
DIMENSIONS: INCHES	TOLERANCES, UNLESS OTHERWISE SPECIFIED:	APVD S. KAIN 27 JAN 00	NAME				
	0 PLC ± -	PRODUCT SPEC	RECEPTACLE ASSEMBLY, CIRCULAR, FLUSH MOUNT, QUICK DISCONNECT, METAL, 7 POSITION				
	1 PLC ± -	—					
	2 PLC ± .010	APPLICATION SPEC					
	3 PLC ± .005	—					
	4 PLC ± -	—					
MATERIAL	FINISH	WEIGHT —	SIZE A2	CAGE CODE 0JPN9	DRAWING NO C=1589056	RESTRICTED TO —	
SEE NOTES	SEE NOTES	CUSTOMER DRAWING			SCALE 6:1	SHEET 1 of 1	REV G

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[QCM007SC2DMC16F](#)