



- 1 CONNECTOR BODY AND JAM NUT MATERIAL: 6061-T6 ALUMINUM, ELECTROLESS NICKEL PLATED PER SAE-AMS-C-26074 OR SAE-AMS-2404E  
LOCKING RING MATERIAL: BERYLLIUM COPPER, ELECTROLESS NICKEL PLATED PER SAE-AMS-C-26074 OR SAE-AMS-2404E  
INSULATOR MATERIAL: LIQUID CRYSTAL POLYMER (LCP) PER ASTM D5138 OR POLYPHENYLENE SULFIDE (PPS) PER ASTM D4067  
O-RING MATERIAL: FLUOROSILICONE
- 2 WIRE TERMINATION: 28 AWG SOLID, 30 AWG STRANDED WIRE OR SMALLER
- 3 LUBRICATE O-RING WITH PARKER SUPER-O-LUBE PRIOR TO INSTALLATION
- 4 THIS DRAWING PREVIOUSLY IDENTIFIED AS NANONICS 303-0029

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M. STORRY	7 MAY 99	 TE Connectivity									
DIMENSIONS: INCHES		CHK E. PAULUS	7 MAY 99										
	TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD S. KAIN	27 JAN 00	NAME  RECEPTACLE ASSEMBLY, CIRCULAR, PANEL MOUNT, THREADED COUPLING/ QUICK DISCONNECT, METAL, 7 POSITION								
			PRODUCT SPEC —										
			APPLICATION SPEC —										
				SIZE	CAGE CODE	DRAWING NO		RESTRICTED TO					
MATERIAL		FINISH		WEIGHT	A2		0PJN9	C=1589060	—				
SEE NOTES		SEE NOTES		CUSTOMER DRAWING				SCALE	6:1	SHEET	1 of 1	REV	H

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[QCM007SC2DC012P](#)