



SIZE	B DIM	C DIM $\pm .0050$	(L DIM)
05	.233	.3085	(.100)
09	.333	.4085	(.200)
15	.483	.5585	(.350)
25	.733	.8085	(.600)
37	1.033	1.1085	(.900)
51	1.383	1.4585	(1.250)

- |    |  |      |
|----|--|------|
| 1. | SHELL OPTIONS (TO BE SPECIFIED IN NANONICS PART NUMBER):<br>METAL: 6061-T6 ALUMINUM, ELECTROLESS NICKEL PLATED PER MIL-C-26074 (STANDARD) OR GOLD PLATED PER MIL-G-45204-303 STAINLESS STEEL, PASSIVATED PER SAE-AMS-QQ-P-35<br>INSULATOR MATERIAL FOR ALL METAL SHELLS IS LIQUID CRYSTAL POLYMER (LCP) PER MIL-M-24519 OR PER ASTM D5138<br>PLASTIC: LIQUID CRYSTAL POLYMER (LCP) PER MIL-M-24519 OR PER ASTM D5138 | TH   |
| 2. | STANDARD 1.0 X 0.25mm JACKSCREW AND MOUNTING THREADS ARE SHOWN FOR REFERENCE ONLY AND MUST BE SPECIFIED IN THE NANONICS PART NUMBER WHEN REQUIRED. 1.2 X 0.25mm THREADS ALSO AVAILABLE.  |      |
| 3. | MOUNTING HARDWARE IS AVAILABLE WITH THIS CONFIGURATION (NOT SHOWN). HARDWARE MUST BE SPECIFIED IN THE NANONICS PART NUMBER. CONSULT TYCO ELECTRONICS FOR DETAILS.  |      |
| 4. | LEAD MATERIAL: HH BRASS, TIN LEAD PLATED 60/40 COMPOSITION PER SAE-AMS-P-81728   |      |
| 5. | NANONICS TERMINATION CODE: L5  | MATE |
| 6. | THIS DRAWING PREVIOUSLY IDENTIFIED AS NANONICS N10138/104  |      |

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C. SCHOLL		03-23-01		 Tyco Electronics Corporation Harrisburg, PA 17105	
		CHK M. STORRY		03-27-01			
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD —		NAME	
		0 PLC ± — 1 PLC ± — 2 PLC ± .010 3 PLC ± .005 4 PLC ± — ANGLES ± 1°		PRODUCT SPEC —		RECEPTACLE ASSEMBLY, STRAIGHT LEADS, SINGLE ROW DUAL OBE, PLASTIC OR METAL	
				APPLICATION SPEC —			
MATERIAL		FINISH		SIZE		CAGE CODE	DRAWING NO
SEE NOTES		SEE NOTES		WEIGHT —		A2	00779
						C-1589459	
						RESTRICTED TO —	
CUSTOMER DRAWING						SCALE	8:1
						SHEET	1 OF 1
						REV	C

1589459

B

A

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[SSM009L5HN](#)