



TRANSZORB® Transient Voltage Suppressors

Stand Off Voltage 5.0 to 18V
Peak Pulse Power 1500W

Features

- Plastic package has Underwriters Laboratory Flammability Classification 94V-0
- Glass passivated junction
- 1500W peak pulse power capability with a 10/1000 μ s waveform, repetition rate (duty cycle): 0.05%
- Excellent clamping capability
- Low incremental surge resistance
- Very fast response time
- Ideal for data and bus line applications
- High temperature soldering guaranteed: 265°C/10 seconds, 0.375" (9.5mm) lead length, 5lbs. (2.3 kg) tension
- Includes 1N6373 thru 1N6386

Mechanical Data


Case: Molded plastic body over passivated junction**Terminals:** Plated axial leads, solderable per MIL-STD-750, Method 2026**Polarity:** For unidirectional types the color band denotes the cathode, which is positive with respect to the anode under normal TVS operation**Mounting Position:** Any**Weight:** 0.045 oz., 1.2 g**Packaging Codes – Options (Antistatic):**

51 – 1K per Bulk box, 10K/carton

54 – 1.4K per 13" paper Reel
(52mm horiz. tape), 4.2K/carton

73 – 1K per horiz. tape & Ammo box, 10K/carton

Case Style 1.5KE



Dimensions in inches and (millimeters)

Maximum Ratings and Thermal Characteristics (T_A = 25°C unless otherwise noted)

Parameter	Symbol	Limit	Unit
Peak pulse power dissipation with a 10/1000 μ s waveform ⁽¹⁾ (Fig. 1)	PPPM	Minimum 1500	W
Peak pulse current with a 10/1000 μ s waveform ⁽¹⁾ (Fig. 3)	IPPM	See Table 1 & 2	A
Steady state power dissipation, T _L = 75°C, at lead lengths 0.375" (9.5mm)	P _{M(AV)}	6.5	W
Peak forward surge current, 8.3ms single half sine-wave unidirectional only ⁽²⁾	I _{FSM}	200	A
Maximum instantaneous forward voltage at 100A for unidirectional only	V _F	3.5	V
Operating junction and storage temperature range	T _J , T _{STG}	-55 to +175	°C

Notes: (1) Non-repetitive current pulse, per Fig.3 and derated above T_A = 25°C per Fig. 2

(2) 8.3ms single half sine-wave, duty cycle = 4 pulses per minute maximum

Electrical Characteristics (JEDEC Registered Data) Table 1 – Unidirectional Types

Ratings at 25°C ambient temperature unless otherwise specified.

JEDEC Type Number	General Semiconductor Part Number	Stand-Off Voltage V_{WM} (V)	Minimum ⁽³⁾ Breakdown Voltage at 1.0mA $V_{(BR)}$ (V)	Maximum Reverse Leakage at V_{WM} I_D (μ A)	Maximum Clamping Voltage at $I_{PP} = 1.0A$ V_C (V)	Maximum Clamping Voltage at $I_{PP} = 10A$ V_C (V)	Maximum Peak Pulse Current I_{PP} (A)
1N6373 ⁽²⁾	ICTE-5 ⁽²⁾	5.0	6.0	300	7.1	7.5	160
1N6374	ICTE-8	8.0	9.4	25.0	11.3	11.5	100
1N6375	ICTE-10	10.0	11.7	2.0	13.7	14.1	90
1N6376	ICTE-12	12.0	14.1	2.0	16.1	16.5	70
1N6377	ICTE-15	15.0	17.6	2.0	20.1	20.6	60
1N6378	ICTE-18	18.0	21.2	2.0	24.2	25.2	50








Electrical Characteristics (JEDEC Registered Data) Table 2 – Bidirectional Types

Ratings at 25°C ambient temperature unless otherwise specified.

JEDEC Type Number	General Semiconductor Part Number	Stand-Off Voltage V_{WM} (V)	Minimum ⁽³⁾ Breakdown Voltage at 1.0mA $V_{(BR)}$ (V)	Maximum Reverse Leakage at V_{WM} I_D (μ A)	Maximum Clamping Voltage at $I_{PP} = 1.0A$ V_C (V)	Maximum Clamping Voltage at $I_{PP} = 10A$ V_C (V)	Maximum Peak Pulse Current I_{PP} (A)
1N6382	ICTE-8C	8.0	9.4	50.0	11.4	11.6	100
1N6383	ICTE-10C	10.0	11.7	2.0	14.1	14.5	90
1N6384	ICTE-12C	12.0	14.1	2.0	16.7	17.1	70
1N6385	ICTE-15C	15.0	17.6	2.0	20.8	21.4	60
1N6386	ICTE-18C	18.0	21.2	2.0	24.8	25.5	50

Notes:

- (1) " C " Suffix indicates bi-directional
- (2) ICTE-5 and 1N6373 are not available as bi-directional
- (3) The minimum breakdown voltage as shown takes into consideration the ± 1 Volt tolerance normally specified for power supply regulation on most integrated circuit manufacturers data sheets. Please consult factory for devices that require reduced clamping voltages where tighter regulated power supply voltages are employed.
- (4) Clamping Factor: 1.33 at full rated power; 1.20 at 50% rated power; Clamping Factor: the ratio of the actual V_C (Clamping Voltage) to the $V_{(BR)}$ (Breakdown Voltage) as measured on a specific device.

**Ratings and
Characteristic Curves** ($T_A = 25^\circ\text{C}$ unless otherwise noted)**Fig. 1 – Peak Pulse Power Rating Curve****Fig. 2 – Pulse Derating Curve****Fig. 3 – Pulse Waveform****Fig. 4 – Typical Junction Capacitance
Uni-Directional****Fig. 5 – Typical Junction Capacitance****Fig. 6 – Maximum Non-Repetitive Forward
Surge Current Uni-Directional Only****Fig. 7 – Typical Characteristics Clamping Voltage**



Notice

Specifications of the products displayed herein are subject to change without notice. Vishay Intertechnology, Inc., or anyone on its behalf, assumes no responsibility or liability for any errors or inaccuracies.

Information contained herein is intended to provide a product description only. No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document. Except as provided in Vishay's terms and conditions of sale for such products, Vishay assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of Vishay products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify Vishay for any damages resulting from such improper use or sale.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Vishay:

[1N6383-E3/51](#) [1N6383-E3/73](#) [1N6384-E3/51](#) [1N6384-E3/73](#) [1N6385-E3/51](#) [1N6385-E3/73](#) [1N6373-E3/51](#)
[1N6373-E3/73](#) [1N6374-E3/51](#) [1N6374-E3/73](#) [1N6375-E3/51](#) [1N6375-E3/73](#) [1N6376-E3/51](#) [1N6376-E3/73](#) [1N6377-](#)
[E3/51](#) [1N6377-E3/73](#) [1N6378-E3/51](#) [1N6378-E3/73](#) [ICTE18C-E3/73](#) [1N6386-E3/73](#)