


Low Capacitance TRANSZORB® Transient Voltage Suppressors



DO-204AC (DO-15)

FEATURES

- Glass passivated chip junction
- Excellent clamping capability
- 500 W peak pulse power capability with a 10/1000 μ s waveform, repetitive rate (duty cycle): 0.01 %
- Very fast response time
- Low incremental surge resistance
- Solder Dip 260 °C, 40 seconds
- Component in accordance to RoHS 2002/95/EC and WEEE 2002/96/EC



TYPICAL APPLICATIONS

Use in sensitive electronics protection against voltage transients induced by inductive load switching and lighting on ICs, MOSFET, signal lines of sensor units for consumer, computer, industrial and telecommunication.

MECHANICAL DATA

Case: DO-204AC, molded epoxy over passivated body
Epoxy meets UL 94V-0 flammability rating

Terminals: Matte tin plated leads, solderable per J-STD-002B and JESD22-B102D
E3 suffix for commercial grade

Polarity: Color band denotes TVS cathode end

MAJOR RATINGS AND CHARACTERISTICS

V_{WM}	5.0 V to 50 V
P_{PPM}	500 W
P_D	3.0 W
T_J max.	175 °C

MAXIMUM RATINGS ($T_A = 25$ °C unless otherwise noted)

PARAMETER	SYMBOL	LIMIT	UNIT
Peak pulse power dissipation with a 10/1000 μ s waveform	P_{PPM}	Minimum 500 ⁽¹⁾	W
Power dissipation on infinite heatsink at $T_L = 75$ °C (Fig. 2)	P_D	3.0	W
Peak pulse power surge current with a 10/1000 μ s waveform (Fig. 3)	I_{PPM}	see next table ⁽¹⁾	A
Operating junction and storage temperature range	T_J, T_{STG}	- 55 to + 175	°C

Note:

(1) Non-repetitive current pulse, per Fig. 3 and derated above $T_A = 25$ °C per Fig. 2

ELECTRICAL CHARACTERISTICS ($T_A = 25^\circ\text{C}$ unless otherwise noted)

PART NUMBER	STAND-OFF VOLTAGE ⁽¹⁾ V_{WM} (V)	MINIMUM BREAKDOWN VOLTAGE AT $I_T = 1.0\text{ mA}$ $V_{(BR)}$ (V)	MAXIMUM REVERSE LEAKAGE AT V_{WM} I_D (μA)	MAXIMUM CLAMPING VOLTAGE AT $I_{PP} = 5.0\text{ A}$ V_C (V)	MAXIMUM PEAK PULSE CURRENT PER FIG. 3 I_{PP} (A)	MAXIMUM JUNCTION CAPACITANCE AT 0 VOLTS (pF)	WORKING INVERSE BLOCKING VOLTAGE V_{WIB} (V)	INVERSE BLOCKING LEAKAGE CURRENT $V_{WIB} I_{IB}$ (mA)	PEAK INVERSE BLOCKING VOLTAGE V_{PIB} (V)
SAC5.0	5	7.60	300	10.0	44	50	75	1.0	100
SAC6.0	6	7.90	300	11.2	41	50	75	1.0	100
SAC7.0	7	8.33	300	12.6	38	50	75	1.0	100
SAC8.0	8	8.89	100	13.4	36	50	75	1.0	100
SAC8.5	8.5	9.44	50	14.0	34	50	75	1.0	100
SAC10	10	11.10	5.0	16.3	29	50	75	1.0	100
SAC12	12	13.30	5.0	19.0	25	50	75	1.0	100
SAC15	15	16.70	5.0	23.6	20	50	75	1.0	100
SAC18	18	20.00	5.0	28.8	15	50	75	1.0	100
SAC22	22	24.40	5.0	35.4	14	50	75	1.0	100
SAC26	26	28.90	5.0	42.3	11.1	50	75	1.0	100
SAC30	30	33.30	5.0	48.6	10.0	50	75	1.0	100
SAC36	36	40.00	5.0	60.0	8.6	50	75	1.0	100
SAC45	45	50.00	5.0	77.0	6.8	50	150	1.0	200
SAC50	50	55.50	5.0	88.0	5.8	50	150	1.0	200

Note:

(1) Non-repetitive current pulse, per Fig. 3 and derated above $T_A = 25^\circ\text{C}$ per Fig. 2

ORDERING INFORMATION

PREFERRED P/N	UNIT WEIGHT (g)	PREFERRED PACKAGE CODE	BASE QUANTITY	DELIVERY MODE
SAC5.0-E3/54	0.432	54	4000	13" Diameter Paper Tape & Reel

RATINGS AND CHARACTERISTICS CURVES

($T_A = 25^\circ\text{C}$ unless otherwise noted)




Figure 1. Peak Pulse Power Rating Curve




Figure 2. Power Derating Curve






Figure 3. Pulse Waveform



Application Note: Device must be used with two units in parallel, opposite in polarity as shown in circuit for AC signal line protection.


Figure 4. AC Line Protection Application

SCHEMATIC



PACKAGE OUTLINE DIMENSIONS in inches (millimeters)

DO-204AC (DO-15)





Notice

Specifications of the products displayed herein are subject to change without notice. Vishay Intertechnology, Inc., or anyone on its behalf, assumes no responsibility or liability for any errors or inaccuracies.

Information contained herein is intended to provide a product description only. No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document. Except as provided in Vishay's terms and conditions of sale for such products, Vishay assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of Vishay products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify Vishay for any damages resulting from such improper use or sale.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Vishay:

[SAC12-E3/73](#) [SAC22-E3/73](#) [SAC26-E3/73](#) [SAC5.0-E3/73](#) [SAC6.0-E3/73](#) [SAC7.0-E3/73](#) [SAC8.0-E3/73](#) [SAC8.5-E3/73](#)