

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

AUG ,2006.

C



COPYRIGHT 2011 BY TYCO ELECTRONICS CORPORATION.

ALL RIGHTS RESERVED.


LOC
DWDIST
—

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	F4	REVISED PER ECR-17-007600	05SEP2018	NG	RK





SECTION C-C




TOLERANCE: ± 0.05
RECOMMENDED PCB LAYOUT
(TOP VIEW)

NOTE:

- MATERIAL:
HOUSING: LCP WITH 30% GF, UL 94V-0, BLACK COLOR.
OR
PA6T WITH 30% GF, 33% REGRIND, UL 94V-0, BLUE OR WHITE COLOR.
CONTACTS: BRASS.
BOARDLOCKS: BRASS.
- FINISH:
CONTACTS: (SEE TABLE) GOLD PLATED ON CONTACT AREA, $2.54\mu\text{m}$ [100 μ] MIN.
MATTE-TIN ON SOLDER TAIL, WITH ENTIRE CONTACT UNDERPLATED
 $1.27\mu\text{m}$ [50 μ] MIN. NICKEL.
BOARDLOCKS: $2.54\mu\text{m}$ [100 μ] MIN. MATTE-TIN OVER $1.27\mu\text{m}$ [50 μ] MIN. NICKEL.
- WAVE SOLDER CAPABLE TO 265°C PER TEST SPEC. 109-202, CONDITION B.



SECTION B-B



3.37	3.3	BLUE (293C)	0.381μm [15μ"]	1-1734699-5	OBSOLETE	
		BLACK		1-1734699-4		
3.37	3	BLUE (293C)	0.381μm [15μ"]	1-1734699-3	OBSOLETE	
		BLACK	0.381μm [15μ"]	1-1734699-2		
2.57	2.05	WHITE	0.762μm [30μ"]	1734699-9	OBSOLETE	
			0.381μm [15μ"]	1734699-8		
			GOLD FLASH	1734699-7		OBSOLETE
		BLUE (293C)	0.762μm [30μ"]	1734699-6	OBSOLETE	
			0.381μm [15μ"]	1734699-5		
			GOLD FLASH	1734699-4		OBSOLETE
		BLACK	0.762μm [30μ"]	1734699-3	OBSOLETE	
			0.381μm [15μ"]	1734699-2		AVAILABLE
GOLD FLASH	1734699-1		OBSOLETE			
B A		HOUSING COLOR	MIN. GOLD THICKNESS	PART NUMBER	STATUS	

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: MM		TOLERANCES UNLESS OTHERWISE SPECIFIED:	
		0 PLC	±
		1 PLC	± 0.3
		2 PLC	± 0.25
		3 PLC	±
		4 PLC	±
MATERIAL		FINISH	
SEE NOTE		SEE NOTE	

DWN	A. WU	06JUN2008
CHK	S. HOU	06JUN2008
APVD	W. KODAMA	06JUN2008
PRODUCT SPEC		
108-57469		
APPLICATION SPEC		
—		
WEIGHT	0.48 GRAMS	
CUSTOMER DRAWING		



TE Connectivity

NAME					SERIAL ATA, 7 POS., PLUG, VERTICAL, A TYPE, DIP.				
SIZE		CAGE CODE		DRAWING NO			RESTRICTED TO		
A3		00779		C=1734699			—		
				SCALE —		SHEET 1 OF 2		REV F4	

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

AUG , 2006.



COPYRIGHT 2011






BY TYCO ELECTRONICS CORPORATION.

ALL RIGHTS RESERVED.

LOC
DWDIST
—

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
		SEE SHEET 1.			

SHIPPING BOXINNER CARTONSHEAFTUBE


NOTE:

- DIMENSION:
TUBE: L= 340, W= 12.65, H= 5.8
INNER CARTON: L= 140, W= 77, H= 355
SHIPPING BOX: L= 372, W= 293, H= 172
- QUANTITY:
20 PCS/TUBE
50 TUBES/SHEAF
2 SHEAFS/INNER CARTON
4 INNER CARTONS/SHIPPING BOX
8000 PCS/SHIPPING BOX
- WEIGHT:
NET WEIGHT: 7.5 KG
GROSS WEIGHT: 8.5 KG

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

MM



MATERIAL

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC	± -
1 PLC	± -
2 PLC	± -
3 PLC	± -
4 PLC	± -
ANGLES	± -

FINISH

DWN

CHK

APVD

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

—

CUSTOMER DRAWING



TE Connectivity

NAME

SERIAL ATA, 7 POS., PLUG,
VERTICAL, A TYPE, DIP.

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C=1734699

SCALE

—

SHEET

2 OF 2

REV

F4

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1734699-1](#)