


THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AF	50		B	REV PER 0G3A-0212-05	27APR05	JR	KR

- 1 CONTINUOUS STRIP ON REELS WITH TERMINALS  
LOCATED ON 6.86±0.08 [.270±.003] CENTERS.
- 2 SLOT ACCEPTS 0.36–0.51mm [#27–#24] AWG COPPER MAGNET  
WIRE. TWO WIRES OF THE SAME SIZE MAX PER SLOT.
- 3 IDENTIFICATION NUMBER 10 FOR THE MAGNET WIRE SLOT SIZE.
- 4 0.25[.010] MAX CARRIER CUT-OFF TABS.
- 5 0.002032[.000080] – 0.003870[.000150] TIN PLATE OVER  
0.00254[.000100] – 0.00508[.000200] COPPER UNDERPLATE.
- 6 PREPRODUCTION – FASR REQUIRED



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	08OCT2004	REVERSE			
		CHK	08OCT2004	STANDARD			
		APVD	08OCT2004	REELING			
		PRODUCT SPEC	108-1484	PART NUMBER			
		APPLICATION SPEC	114-2140	NAME			
		WEIGHT	-	TAB, 4.75[.187] SERIES, MAG-MATE Slim Line			
		CUSTOMER DRAWING		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
				A2	00779	C=1742189	-
				SCALE	10:1	SHEET	1 OF 1
						REV	B

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1742189-1](#)