

Metal Film Resistors, Axial, Industrial Power, Precision, Flameproof



FEATURES

- High power rating, small size
- Flameproof, high temperature silicone coating
- Special filming and coating processes
- Excellent high frequency characteristics
- Low noise
- Low voltage coefficient
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912


RoHS*
Available

Note

* This datasheet provides information about parts that are RoHS-compliant and /or parts that are non RoHS-compliant. For example, parts with lead (Pb) terminations are not RoHS-compliant. Please see the information / tables in this datasheet for details

STANDARD ELECTRICAL SPECIFICATIONS						
GLOBAL MODEL	HISTORICAL MODEL	MAXIMUM WORKING VOLTAGE ⁽¹⁾ V	POWER RATING $P_{70\text{ }^{\circ}\text{C}}$ W	RESISTANCE RANGE Ω	TOLERANCE $\pm \%$	TEMPERATURE COEFFICIENT $\pm \text{ppm}/^{\circ}\text{C}$
CPF1	CPF-1	250	1	5 to 150K	0.1, 0.25, 0.5, 1	25
				5 to 150K	0.1, 0.25, 0.5, 1, 2, 5	50
				1 to 150K	0.5, 1, 2, 5	100
				0.5 to 150K	1, 2, 5	150
				0.5 to 150K	1	200
				0.2 to 150K	2, 5	200
				0.1 to 150K	2, 5	300
CPF2	CPF-2	350	2	5 to 150K	0.1, 0.25, 0.5, 1	25
				5 to 150K	0.1, 0.25, 0.5, 1, 2, 5	50
				1 to 150K	0.5, 1, 2, 5	100
				0.5 to 150K	1, 2, 5	150
				0.5 to 150K	1	200
				0.2 to 150K	2, 5	200
				0.1 to 150K	2, 5	300
CPF3	CPF-3	500	3	8 to 150K	0.1, 0.25, 0.5, 1	25
				8 to 150K	0.1, 0.25, 0.5, 1, 2, 5	50
				1 to 150K	0.5, 1, 2, 5	100
				1 to 150K	1, 2, 5	150
				1 to 150K	1	200
				0.2 to 150K	2, 5	200
				0.1 to 150K	2, 5	300

Note

⁽¹⁾ Continuous working voltage shall be $\sqrt{P \times R}$ or maximum working voltage, whichever is less

GLOBAL PART NUMBER INFORMATION

New Global Part Numbering: CPF1562R00FKR36 (preferred part numbering format)

C	P	F	1	5	6	2	R	0	0	F	K	R	3	6			
GLOBAL MODEL			RESISTANCE VALUE			TOLERANCE CODE			TEMPERATURE COEFFICIENT			PACKAGING			SPECIAL		
CPF1 CPF2 CPF3			R = Ω K = k Ω R10000 = 0.1 Ω 10R000 = 10 Ω 150K00 = 150 k Ω			B = $\pm 0.1\%$ C = $\pm 0.25\%$ D = $\pm 0.5\%$ F = $\pm 1\%$ G = $\pm 2\%$ J = $\pm 5\%$			E = 25 ppm H = 50 ppm K = 100 ppm L = 150 ppm N = 200 ppm M = 300 ppm			E14 = lead (Pb)-free, bulk E36 = lead (Pb)-free, T/R (full) EE6 = lead (Pb)-free, T/R (1000 pcs) B14 = tin / lead, bulk R36 = tin / lead, T/R (full) RE6 = tin / lead, T/R (1000 pcs)			Blank = standard (dash number) (up to 3 digits) From 1 to 999 as applicable		

Historical Part Number Example: CPF-15620FT-1 R36 (will continue to be accepted)

CPF-1	5620	F	T-1	R36
HISTORICAL MODEL	RESISTANCE VALUE	TOLERANCE CODE	TEMP. COEFFICIENT	PACKAGING

Note

- For additional information on packaging, refer to the Through-Hole Resistor Packaging document (www.vishay.com/doc?31544)

TEMPERATURE COEFFICIENT CODES

GLOBAL TC CODE	HISTORICAL TC CODE	TEMPERATURE COEFFICIENT
E	T-9	25 ppm/ $^{\circ}\text{C}$
H	T-2	50 ppm/ $^{\circ}\text{C}$
K	T-1	100 ppm/ $^{\circ}\text{C}$
L	T-0	150 ppm/ $^{\circ}\text{C}$
N	T-00	200 ppm/ $^{\circ}\text{C}$
M	M	300 ppm/ $^{\circ}\text{C}$


TECHNICAL SPECIFICATIONS

PARAMETER	UNIT	CPF1	CPF2	CPF3
Rated Dissipation at 70 $^{\circ}\text{C}$	W	1	2	3
Limiting Element Voltage ⁽¹⁾	V $\cong$	250	350	500
Insulation Voltage	V _{eff}	900	900	900
Thermal Resistance	K/W	85	60	50
Insulation Resistance	Ω	10 ¹⁰		
Category Temperature Range	$^{\circ}\text{C}$	-65 $^{\circ}\text{C}$ / +230 $^{\circ}\text{C}$		

Note

- ⁽¹⁾ Rated voltage $\sqrt{P \times R}$


DIMENSIONS




Note

- ⁽¹⁾ Lead length for product in bulk pack. For product supplied in tape and reel, the actual lead length would be based on the body size, tape spacing and lead trim

GLOBAL MODEL	DIMENSIONS in inches (millimeters)			
	L	D	L ₁ max.	d
CPF1	0.240 $\pm$ 0.020 (6.10 $\pm$ 0.51)	0.090 $\pm$ 0.008 (2.29 $\pm$ 0.20)	0.310 (7.87)	0.025 $\pm$ 0.002 (0.64 $\pm$ 0.05)
CPF2	0.344 $\pm$ 0.031 (8.74 $\pm$ 0.79)	0.145 $\pm$ 0.015 (3.68 $\pm$ 0.38)	0.425 (10.80)	0.032 $\pm$ 0.002 (0.81 $\pm$ 0.05)
CPF3	0.555 $\pm$ 0.041 (14.10 $\pm$ 1.04)	0.180 $\pm$ 0.015 (4.57 $\pm$ 0.381)	0.650 (16.51)	0.032 $\pm$ 0.002 (0.81 $\pm$ 0.05)

**THERMAL RESISTANCE****Note**

- Surface temperatures were taken with an infrared pyrometer in +25 °C still air. Resistors were supported by their leads in test clips at a point 0.500" (12.70 mm) out from the resistor body ends

DERATING**MATERIAL SPECIFICATIONS**

Element	Proprietary nickel-chrome alloy
Core	Cleaned high purity ceramic
Coating	Special high temperature conformal coat
Termination	Standard lead material is solder-coated Solderable and weldable per MIL-STD-1276, type C

MECHANICAL SPECIFICATIONS

Terminal Strength	2 pound pull test
Solderability	Continuous satisfactory coverage when tested in accordance with MIL-STD-202, method 208

MARKING

Temperature Coefficient: T00 = 200 ppm, T0 = 150 ppm, T1 = 100 ppm, T2 = 50 ppm, T9 = 25 ppm, M = 300 ppm

CPF1, CPF2, CPF3: (5 lines)

DALE	Manufacturer's name
CPF-1	Style and size
49.9 kΩ	Value
1 % T2	Tolerance and TC
1208	4-digit date code

PERFORMANCE

TEST	MAX. ΔR (TYPICAL TEST LOTS)
Thermal Shock	± 1.0 %
Short Time Overload	± 0.5 %
Low Temperature Operation	± 0.5 %
Moisture Resistance	± 1.5 %
Resistance to Soldering Heat	± 0.5 %
Shock	± 0.5 %
Vibration	± 0.5 %
Terminal Strength	± 0.5 %
Dielectric Withstanding Voltage	± 0.5 %
Life	± 2.0 %



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Vishay:](#)

CPF151K000JKB14	CPF12R0000FKB14	CPF21K6200FKB14	CPF190K900FEB14	CPF15R0000FHB14
CPF3680R00GKB14	CPF3422R00BHB14	CPF230K000JKR36	CPF2898R00BEB14	CPF210R000JKR36
CPF3150K00FHB14	CPF2150K00FKB14	CPF1150K00FEB14	CPF3270R00GKB14	CPF3626R00DKB14
CPF3200R00BHB14	CPF3470R00GKB14	CPF1470R00GKB14	CPF1249R00BEB14	CPF31K0000BHB14
CPF12R2100FKB14	CPF230R000JKR36	CPF3150R00CHB14	CPF3100R00FKB14	CPF315R000FKB14
CPF111K000FEB14	CPF110K700FKB14	CPF251R100FKB14	CPF151R100FKB14	CPF212R000GKB14
CPF251R000GKB14	CPF310K000BHB14	CPF351K100FKB14	CPF37R5000DKB14	CPF2360R00BEB14
CPF310R000FKR36	CPF210R000FKR36	CPF13R0100FKB14	CPF22K7000FKB14	CPF33R6500FKB14
CPF322R100FKB14	CPF310K000FKR36	CPF222R100FKB14	CPF110R000FEB14	CPF32R2100DKB14
CPF2562R00FKB14	CPF11K2000BEB14	CPF12K0000BHB14	CPF25R0000FKB14	CPF21R0000FKB14
CPF22R0000FKB14	CPF23R0000JKB14	CPF362K000FKB14	CPF38R0600FKB14	CPF110R000BHR36
CPF150R000BHR36	CPF256K000FKR36	CPF1R56000JNB14	CPF13K2400FHB14	CPF211K000FKB14
CPF111K000FKB14	CPF11R0000FKRE5	CPF3100K00BHB14	CPF2100K00BEB14	CPF33R9200DKB14
CPF315K000FKB14	CPF115K000FEB14	CPF124K900FEB14	CPF3620R00FKB14	CPF320R000DKB14
CPF324R000JKB14	CPF1200R00FKR36	CPF12K2100FKB14	CPF1866R00FEB14	CPF310R000DKB14
CPF38R2000FHB14	CPF360K400FKB14	CPF33R0000JKB14	CPF312K600DKB14	CPF25K1100FKB14
CPF315R000JKB14	CPF318R000JKB14	CPF312R000JKB14	CPF382R000JKB14	CPF347R000JKB14
CPF11K2000JKB14	CPF218R200JHB14	CPF3271R00DKB14	CPF3R50000GNB14	CPF3R10000GNB14
CPF3R30000GNB14	CPF1R30000GNB14	CPF31K0000GKB14	CPF142K200FKB14	CPF215R000BEB14
CPF2200R00FKB14	CPF1200R00FKB14	CPF32K4900FKB14	CPF261R900FEB14	CPF22R0000FKRE5