



LOC	DIST	REVISIONS					
FT	0	P	LTR	DESCRIPTION	DATE	DWN	APVD
			02	REVISED PER ECO-12-007711	26APR2012	KH	MS

D




C

B

A



1776153-3 AS SHOWN



RECOMMENDED PC BOARD LAYOUT

1. MATERIALS AND FINISH
HOUSING: HIGH TEMPERATURE POLYAMIDE, UL 94V-0 RATED,
COLOR: BLACK.
TERMINAL: COPPER ALLOY, TIN PLATED.
2. SUITABLE FOR 1,6-2,4mm PC BOARD THICKNESS.
3. RECOGNIZED UNDER THE COMPONENT PROGRAM OF
UNDERWRITERS LABORATORIES INC., FILE N° E60677.
4. IMQ CERTIFICATE WITH SURVEILLANCE IN CONFORMITY
WITH IEC 998-1/998-2-1.

89.20	12	1-1776153-2
81.70	11	1-1776153-1
74.20	10	1-1776153-0
66.70	9	1776153-9
59.20	8	1776153-8
51.70	7	1776153-7
44.20	6	1776153-6
36.70	5	1776153-5
29.20	4	1776153-4
21.70	3	1776153-3
14.20	2	1776153-2

A	NO OF POSN	PART NUMBER
---	------------	-------------

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S. WELDON 26JUL2005	TE Connectivity			
DIMENSIONS:		CHK C. RICHARD 26JUL2005				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD C. RICHARD 26JUL2005	NAME TERMINAL BLOCK HEADER ASSEMBLY 180 DEGREE, CLOSED END 7.5mm PITCH			
mm		PRODUCT SPEC				
		-	SIZE CAGE CODE DRAWING NO RESTRICTED TO			
		APPLICATION SPEC				
		-				
		WEIGHT -				
MATERIAL -		FINISH -		A200779C-1776153		-
		CUSTOMER DRAWING		SCALE 4:1	SHEET 1 OF 1	REV 02

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1776153-4](#)