


Sample Kit

Standard Thick Film Chip Resistors

D10/CRCW0402 100 1 % e3



FEATURES

- AEC-Q200 qualified
- Material categorization:
for definitions of compliance please see
www.vishay.com/doc?99912



RoHS
COMPLIANT
HALOGEN
FREE

Transparent dividers / pages contain cardboard tapes holding 40 resistors. The kit contains every fourth value of the E96-series. Parts are sorted in the ascending order of its resistance value and appropriately marked.

SPECIFICATIONS

Laboratory kit	LAE2A CHIP 0402
Resistor type	D10/CRCW0402 -100 1 % e3
Temperature coefficient	± 100 ppm/K
Tolerance	± 1 %
Resistance range / E-series	10 Ω to 1 M Ω / every 4 th value of E96 ⁽¹⁾ ; jumper (0 Ω)
Number of resistance values	122
Resistors per value / total	40 / 4880
Number of dividers / pages	13 / 1

Notes

- The products are specified by the underlying standard product's datasheet "Standard Thick Film Chip Resistors" in its most current edition at www.vishay.com/doc?20035
- ⁽¹⁾ Supplemented by 1 M Ω

PART NUMBER AND PRODUCT DESCRIPTION

PART NUMBER: LAE2ACHIP0402KFE96

L	A	E	2	A	C	H	I	P	0	4	0	2	K	F	E	9	6
KIT		TYPE / SIZE				TCR		TOLERANCE				FRACTION OF E-SERIES					
LAE2A		CHIP RESISTOR 0402				K = ± 100 ppm/K		F = ± 1 %				1/4 E96					

PRODUCT DESCRIPTION: LAE D10/CRCW0402 100 1/4 E96 1 % 122x40 e3

LAE	D10/CRCW0402	100	1/4 E96	1 %	122x40	e3
KIT	VALUE / SERIES	TCR	TYPE / SIZE	TOLERANCE	QUANTITY	LEAD (Pb)-FREE
LAE2A	D10/CRCW0402	± 100 ppm/K	Every fourth value from E96 series	± 1 %	122 x 40	e3 = pure tin termination finish



RESISTANCE TABLE (Ω)						
0	10.0	100	1K	10K	100K	1M
	11.0	110	1.1K	11K	110K	
	12.1	121	1.21K	12.1K	121K	
	13.3	133	1.33K	13.3K	133K	
	14.7	147	1.47K	14.7K	147K	
	16.2	162	1.62K	16.2K	162K	
	17.8	178	1.78K	17.8K	178K	
	19.6	196	1.96K	19.6K	196K	
	21.5	215	2.15K	21.5K	215K	
	23.7	237	2.37K	23.7K	237K	
	26.1	261	2.61K	26.1K	261K	
	28.7	287	2.87K	28.7K	287K	
	31.6	316	3.16K	31.6K	316K	
	34.8	348	3.48K	34.8K	348K	
	38.3	383	3.83K	38.3K	383K	
	42.2	422	4.22K	42.2K	422K	
	46.4	464	4.64K	46.4K	464K	
	51.1	511	5.11K	51.1K	511K	
	56.2	562	5.62K	56.2K	562K	
	61.9	619	6.19K	61.9K	619K	
	68.1	681	6.81K	68.1K	681K	
	75.0	750	7.5K	75K	750K	
	82.5	825	8.25K	82.5K	825K	
	90.9	909	9.09K	90.9K	909K	

Note

- The series of resistances included in the kits are derived from the E96 series according to IEC 60063 by selecting only the first of each four successive values in the given range from 10.0 Ω through 1.00 M Ω

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Vishay:

[LAE2ACHIP0402KFE96](#)