

Semi-Precision Thick Film Chip Resistors



LINKS TO ADDITIONAL RESOURCES



D/CRCW-P e3 standard thick film chip resistors are the perfect choice for most fields of modern electronics where high reliability and stability are of major concern. Typical applications include automotive, telecommunications, and industrial.

FEATURES

- Low temperature coefficient (± 50 ppm/K) and tight tolerances (± 0.25 %)
- Stability at different environmental conditions $\Delta R/R \leq 1$ % (1000 h rated power at 70 °C)
- AEC-Q200 qualified
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912



RoHS
COMPLIANT
HALOGEN
FREE

APPLICATIONS

- Automotive
- Industrial
- Telecommunication

TECHNICAL SPECIFICATIONS

DESCRIPTION	D10/ CRCW0402-P e3	D11/ CRCW0603-P e3	D12/ CRCW0805-P e3	D25/ CRCW1206-P e3	CRCW1210-P e3	CRCW1218-P e3	CRCW2010-P e3	CRCW2512-P e3
Imperial size	0402	0603	0805	1206	1210	1218	2010	2512
Metric size code	RR1005M	RR1608M	RR2012M	RR3216M	RR3225M	RR3246M	RR5025M	RR6332M
Resistance range	1 Ω to 1.1 MΩ	1 Ω to 10 MΩ	10 Ω to 10 MΩ		100 Ω to 1 MΩ	100 Ω to 2.2 MΩ	10 Ω to 10 MΩ	
Resistance tolerance	± 1 %; ± 0.5 %; ± 0.25 %							
Temperature coefficient	± 100 ppm/K; ± 50 ppm/K							
Rated dissipation, P_{70} ⁽¹⁾	0.063 W	0.10 W	0.125 W	0.25 W	0.5 W	1.0 W	0.75 W	1.0 W
Operating voltage, U_{max} , AC _{RMS} /DC	50 V	75 V	150 V	200 V	200 V	200 V	400 V	500 V
Permissible film temperature, $\vartheta_{\text{F max}}$ ⁽¹⁾	155 °C							
Operating temperature range	-55 °C to +155 °C							
Max. resistance change at P_{70} for resistance range, $ \Delta R/R $ after: 1000 h 8000 h	 ≤ 1 % ≤ 2 %							
Permissible voltage against ambient (insulation): 1 min, U_{ins}	75 V	100 V	200 V	300 V	300 V	300 V	300 V	300 V
Failure rate: FIT _{observed}	≤ 0.1 x 10 ⁻⁹ /h							

Note

⁽¹⁾ Please refer to "Application Information" below

**APPLICATION INFORMATION**

When the resistor dissipates power, a temperature rise above the ambient temperature occurs, dependent on the thermal resistance of the assembled resistor together with the printed circuit board. The rated dissipation applies only if the permitted film temperature is not exceeded.

These resistors do not feature a limited lifetime when operated within the permissible limits. However, resistance value drift increasing over operating time may result in exceeding a limit acceptable to the specific application, thereby establishing a functional lifetime.

TEMPERATURE COEFFICIENT AND RESISTANCE RANGE				
TYPE / SIZE	TCR	TOLERANCE	RESISTANCE	E-SERIES
D10/CRCW0402-P e3	± 100 ppm/K	± 0.5 %	1 Ω to 1.1 MΩ	E24; E96
	± 50 ppm/K	± 1 %	100 Ω to 1 MΩ	E24; E96
	± 50 ppm/K	± 0.5 %	100 Ω to 1 MΩ	E24; E96
	± 50 ppm/K	± 0.25 %	100 Ω to 1 MΩ	E24; E96
D11/CRCW0603-P e3	± 100 ppm/K	± 0.5 %	1 Ω to 10 MΩ	E24; E96
	± 100 ppm/K	± 0.25 %	1 Ω to 10 MΩ	E24; E96
	± 50 ppm/K	± 1 %	100 Ω to 10 MΩ	E24; E96
	± 50 ppm/K	± 0.5 %	100 Ω to 10 MΩ	E24; E96
	± 50 ppm/K	± 0.25 %	100 Ω to 1 MΩ	E24; E96
D12/CRCW0805-P e3	± 100 ppm/K	± 0.5 %	10 Ω to 10 MΩ	E24; E96
	± 50 ppm/K	± 1 %	100 Ω to 10 MΩ	E24; E96
	± 50 ppm/K	± 0.5 %	100 Ω to 10 MΩ	E24; E96
	± 50 ppm/K	± 0.25 %	100 Ω to 1 MΩ	E24; E96
D25/CRCW1206-P e3	± 100 ppm/K	± 0.5 %	10 Ω to 10 MΩ	E24; E96
	± 50 ppm/K	± 1 %	100 Ω to 10 MΩ	E24; E96
	± 50 ppm/K	± 0.5 %	100 Ω to 10 MΩ	E24; E96
	± 50 ppm/K	± 0.25 %	100 Ω to 1 MΩ	E24; E96
CRCW1210-P e3	± 100 ppm/K	± 0.5 %	100 Ω to 1 MΩ	E24; E96
	± 50 ppm/K	± 1 %	100 Ω to 1 MΩ	E24; E96
	± 50 ppm/K	± 0.5 %	100 Ω to 1 MΩ	E24; E96
CRCW1218-P e3	± 100 ppm/K	± 0.5 %	100 Ω to 2.2 MΩ	E24; E96
	± 50 ppm/K	± 1 %	100 Ω to 2.2 MΩ	E24; E96
	± 50 ppm/K	± 0.5 %	100 Ω to 2.2 MΩ	E24; E96
CRCW2010-P e3	± 100 ppm/K	± 0.5 %	10 Ω to 10 MΩ	E24; E96
	± 50 ppm/K	± 1 %	100 Ω to 10 MΩ	E24; E96
	± 50 ppm/K	± 0.5 %	100 Ω to 10 MΩ	E24; E96
CRCW2512-P e3	± 100 ppm/K	± 0.5 %	10 Ω to 10 MΩ	E24; E96
	± 50 ppm/K	± 1 %	100 Ω to 10 MΩ	E24; E96
	± 50 ppm/K	± 0.5 %	100 Ω to 10 MΩ	E24; E96



PACKAGING

TYPE / SIZE	CODE	QUANTITY	PACKAGING STYLE	WIDTH	PITCH	PACKAGING DIMENSIONS
D10/CRCW0402-P e3	ED = ET7 EE = EF4	10 000 50 000	Paper tape acc. to IEC 60286-3, Type 1a	8 mm	2 mm	Ø 180 mm / 7" Ø 330 mm / 13"
D11/CRCW0603-P e3	EI = ET2	5000		8 mm	2 mm	Ø 180 mm / 7" Ø 180 mm / 7" Ø 285 mm / 11.25" Ø 330 mm / 13"
	ED = ET3 EL = ET4 EE = ET8	10 000 20 000 50 000				Ø 180 mm / 7" Ø 285 mm / 11.25" Ø 330 mm / 13"
	EA = ET1 EB = ET5 EC = ET6	5000 10 000 20 000		4 mm		Ø 180 mm / 7" Ø 285 mm / 11.25" Ø 330 mm / 13"
D12/CRCW0805-P e3	EA = ET1 EB = ET5 EC = ET6	5000 10 000 20 000		8 mm	4 mm	Ø 180 mm / 7" Ø 285 mm / 11.25" Ø 330 mm / 13"
D25/CRCW1206-P e3	EA = ET1 EB = ET5 EC = ET6	5000 10 000 20 000		8 mm	4 mm	Ø 180 mm / 7" Ø 285 mm / 11.25" Ø 330 mm / 13"
CRCW1210-P e3	EA = ET1 EB = ET5 EC = ET6	5000 10 000 20 000	Blister tape acc. to IEC 60286-3, Type 2a	12 mm	4 mm	Ø 180 mm / 7" Ø 285 mm / 11.25" Ø 330 mm / 13"
CRCW1218-P e3	EK = ET9	4000		12 mm	4 mm	Ø 180 mm / 7"
CRCW2010-P e3	EF = E02	4000		12 mm	4 mm	Ø 180 mm / 7"
CRCW2512-P e3	EG = E67 EH = E82	2000 4000		12 mm	8 mm 4 mm	Ø 180 mm / 7"

PART NUMBER AND PRODUCT DESCRIPTION

Part Number: CRCW040275R0DKEDP

C	R	C	W	0	4	0	2	7	5	R	0	D	K	E	D	P
TYPE / SIZE		RESISTANCE		TOLERANCE		TCR		PACKAGING		SPECIAL						
CRCW0402 CRCW0603 CRCW0805 CRCW1206 CRCW1210 CRCW1218 CRCW2010 CRCW2512		R = decimal K = thousand M = million		C = ± 0.25 % D = ± 0.5 % F = ± 1.0 %		H = ± 50 ppm/K K = ± 100 ppm/K		EA, EB, EC, ED, EE, EF, EG, EH, EI, EL, EK		Up to 2 digits P = semi-Precision						

Product Description: D10/CRCW0402-P 100 75R 0.5 % ET7 e3

D10/CRCW0402-P	100	75R	0.5 %	ET7	e3
TYPE / SIZE	TCR	RESISTANCE	TOLERANCE	PACKAGING	LEAD (Pb)-FREE
D10/CRCW0402-P D11/CRCW0603 -P D12/CRCW0805-P D25/CRCW1206-P CRCW1210-P CRCW1218-P CRCW2010-P CRCW2512-P	± 50 ppm/K ± 100 ppm/K	49K9 = 49.9 kΩ 5R1 = 5.1 Ω	± 0.25 % ± 0.5 % ± 1 %	ET1, ET2, ET3, ET4, ET5, ET6, ET7, ET8, ET9, EF4, E02, E67, E82	e3 = pure tin termination finish



DESCRIPTION

Production is strictly controlled and follows an extensive set of instructions established for reproducibility. A cermet film layer and a glass-over are deposited on a high grade (Al_2O_3) ceramic substrate with its prepared inner contacts. A special laser is used to achieve the target value by smoothly fine trimming the resistive layer without damaging the ceramics. The resistor elements are covered by a protective coating designed for electrical, mechanical and climatic protection. The terminations receive a final pure tin on nickel plating.

The result of the determined production is verified by an extensive testing procedure on 100 % of the individual chip resistors. Only accepted products are laid directly into the tape in accordance with **IEC 60286-3 Type 1a and Type 2a** ⁽¹⁾.

ASSEMBLY

The resistors are suitable for processing on automatic SMD assembly systems. They are suitable for automatic soldering using wave, reflow or vapor phase as shown in **IEC 61760-1** ⁽¹⁾. The encapsulation is resistant to all cleaning solvents commonly used in the electronics industry, including alcohols, esters and aqueous solutions. The suitability of conformal coatings, potting compounds and their processes, if applied, shall be qualified by appropriate means to ensure the long-term stability of the whole system.

The resistors are RoHS-compliant, the pure tin plating provides compatibility with lead (Pb)-free and lead-containing soldering processes. Solderability is specified for 2 years after production or requalification. The permitted storage time is 20 years. The immunity of the plating against tin whisker growth has been proven under extensive testing.

MATERIALS

Vishay acknowledges the following systems for the regulation of hazardous substances:

- IEC 62474, Material Declaration for Products of and for the Electrotechnical Industry, with the list of declarable substances given therein ⁽²⁾
- The Global Automotive Declarable Substance List (GADSL) ⁽³⁾
- The REACH regulation (1907/2006/EC) and the related list of substances with very high concern (SVHC) ⁽⁴⁾ for its supply chain

The products do not contain any of the banned substances as per IEC 62474, GADSL, or the SVHC list, see www.vishay.com/how/leadfree.

Hence the products fully comply with the following directives:

- 2000/53/EC End-of-Life Vehicle Directive (ELV) and Annex II (ELV II)
- 2011/65/EU Restriction of the Use of Hazardous Substances Directive (RoHS) with amendment 2015/863/EU
- 2012/19/EU Waste Electrical and Electronic Equipment Directive (WEEE)

Vishay pursues the elimination of conflict minerals from its supply chain, see the Conflict Minerals Policy at www.vishay.com/doc?49037.

APPROVALS

The resistors are qualified according to AEC-Q200.

Where applicable, the resistors are tested in accordance with **EN 140401-802** which refers to **EN 60115-1**, **EN 60115-8** and the variety of environmental test procedures of the **IEC 60068** ⁽¹⁾ series.

RELATED PRODUCTS

For more information about products with standard TCR and tolerance please refer to the “Standard Thick Film Chip Resistors” datasheet (www.vishay.com/doc?20035).

The D/CRCW-P with SnPb termination plating is designed for applications where lead bearing terminations are mandatory. For ordering D/CRCW-P with SnPb terminations please refer to latest edition of datasheet D/CRCW-P (www.vishay.com/doc?20009).

Notes

⁽¹⁾ The quoted IEC standards are also released as EN standards with the same number and identical contents


⁽²⁾ The IEC 62474 list of declarable substances is maintained in a dedicated database, which is available at <http://std.iec.ch/iec62474>

⁽³⁾ The Global Automotive Declarable Substance List (GADSL) is maintained by the American Chemistry Council and available at www.gadsl.org


⁽⁴⁾ The SVHC list is maintained by the European Chemical Agency (ECHA) and available at <http://echa.europa.eu/candidate-list-table>

FUNCTIONAL PERFORMANCE


Single Pulse




Continuous Pulse



Pulse Voltage



Derating



TESTS AND REQUIREMENTS

All executed tests are carried out in accordance with the following specifications:

EN 60115-1, generic specification

EN 60115-8 (successor of EN 140400), sectional specification

EN 140401-802, detail specification

IEC 60068-2-xx, test methods

The parameters stated in the Test Procedures and Requirements table are based on the required tests and permitted limits of EN 140401-802. The table presents only the most important tests, for the full test schedule refer to the documents listed above. However, some additional tests and a number of improvements against those minimum requirements have been included.

The testing also covers most of the requirements specified by EIA/IS-703 and JIS-C-5201-1.

The tests are carried out under standard atmospheric conditions in accordance with IEC 60068-1, 4.3, whereupon the following values are applied:

Temperature: 15 °C to 35 °C

Relative humidity: 25 % to 75 %

Air pressure: 86 kPa to 106 kPa (860 mbar to 1060 mbar).

A climatic category LCT / UCT / 56 is applied, defined by the lower category temperature (LCT), the upper category temperature (UCT), and the duration of exposure in the damp heat, steady state test (56 days). The components are mounted for testing on boards in accordance with EN 60115-8, 2.4.2 unless otherwise specified.


TEST PROCEDURES AND REQUIREMENTS				
EN 60115-1 CLAUSE	IEC 60068-2 (1) TEST METHOD	TEST	PROCEDURE	REQUIREMENTS PERMISSIBLE CHANGE (ΔR)
			Stability for product types:	STABILITY CLASS 1 OR BETTER
			D/CRCW-P e3	1 Ω to 10 M Ω
4.5	-	Resistance	-	$\pm 0.25\%$; $\pm 0.5\%$; $\pm 1\%$
4.8	-	Temperature coefficient	At (20 / -55 / 20) °C and (20 / 125 / 20) °C	± 50 ppm/K; ± 100 ppm/K
4.25.1	-	Endurance at 70 °C	$U = \sqrt{P_{70} \times R} \leq U_{max}$ 1.5 h on; 0.5 h off 70 °C; 1000 h 70 °C; 8000 h	$\pm (1\% R + 0.05 \Omega)$ $\pm (2\% R + 0.05 \Omega)$
4.25.3	-	Endurance at upper category temperature	155 °C; 1000 h	$\pm (1\% R + 0.05 \Omega)$
4.24	78 (Cab)	Damp heat, steady state	(40 \pm 2) °C; (93 \pm 3) % RH; 56 days	$\pm (1\% R + 0.05 \Omega)$
4.37	67 (Cy)	Damp heat, steady state, accelerated	(85 \pm 2) °C; (85 \pm 5) % RH; $U = \sqrt{0.1 \times P_{85} \times R} \leq 100$ V; 1000 h	$\pm (1\% R + 0.05 \Omega)$

TEST PROCEDURES AND REQUIREMENTS				
EN 60115-1 CLAUSE	IEC 60068-2 (1) TEST METHOD	TEST	PROCEDURE	REQUIREMENTS PERMISSIBLE CHANGE (ΔR)
			Stability for product types:	STABILITY CLASS 1 OR BETTER
			D/CRCW-P e3	1 Ω to 10 M Ω
4.23	-	Climatic sequence:		
4.23.2	2 (Ba)	Dry heat	125 °C; 16 h	
4.23.3	30 (Db)	Damp heat, cyclic	55 °C; 24 h; ≥ 90 % RH; 1 cycle	
4.23.4	1 (Ab)	Cold	-55 °C; 2 h	
4.23.5	13 (M)	Low air pressure	8.5 kPa; 2 h; (25 \pm 10) °C	
4.23.6	30 (Db)	Damp heat, cyclic	55 °C; 5 days; > 90 % RH; 5 cycles	
4.23.7	-	DC load	$U = \sqrt{P_{70} \times R} \leq U_{max.}$; 1 min	$\pm (1 \% R + 0.05 \Omega)$
-	1 (Aa)	Cold	-55 °C; 2 h	$\pm (0.25 \% R + 0.05 \Omega)$
4.19	14 (Na)	Rapid change of temperature	30 min. at -55 °C and 30 min. at 125 °C 5 cycles 1000 cycles	$\pm (0.25 \% R + 0.05 \Omega)$ $\pm (1 \% R + 0.05 \Omega)$
4.13	-	Short time overload	$U = 2.5 \times \sqrt{P_{70} \times R} \leq 2 \times U_{max.}$; whichever is the less severe; 5 s	$\pm (2 \% R + 0.05 \Omega)$
4.27	-	Single pulse high voltage overload	Severity no. 4: $U = 10 \times \sqrt{P_{70} \times R}$ or $U \leq 2 \times U_{max.}$; whichever is the less severe; 10 pulses 10 μ s / 700 μ s	$\pm (1 \% R + 0.05 \Omega)$
4.39	-	Periodic electric overload	$U = \sqrt{15 \times P_{70} \times R}$ $\leq 2 \times U_{max.}$; whichever is the less severe; 0.1 s on; 2.5 s off; 1000 cycles	$\pm (1 \% R + 0.05 \Omega)$ no visible damage
4.38	-	Electrostatic discharge (human body model)	IEC 61340-3-1 (1); 3 positive + 3 negative discharges; ESD voltage according to the size	$\pm (1 \% R + 0.05 \Omega)$
4.22	6 (Fc)	Vibration	Endurance by sweeping; 10 Hz to 2000 Hz; no resonance; amplitude ≤ 1.5 mm or ≤ 200 m/s ² ; 7.5 h	$\pm (0.25 \% R + 0.05 \Omega)$ no visible damage
4.17	58 (Td)	Solderability	Solder bath method, Sn60Pb40; non-activated flux (235 \pm 5) °C; (2 \pm 0.2) s Solder bath method, Sn96.5Ag3Cu0.5 or Sn99.3Cu0.7; non-activated flux (245 \pm 5) °C or (250 \pm 5) °C; (3 \pm 0.3) s	Good tinning (≥ 95 % covered); no visible damage
4.18	58 (Td)	Resistance to soldering heat	Soldering bath method; (260 \pm 5) °C; (10 \pm 1) s	$\pm (0.25 \% R + 0.05 \Omega)$
4.29	45 (XA)	Component solvent resistance	Isopropyl alcohol; +50 °C; method 2	No visible damage
4.32	21 (Uu ₃)	Shear (adhesion)	D11/CRCW0603-P e3 and smaller: 9 N D12/CRCW0805-P e3 to CRCW2512-P e3: 45 N	No visible damage
4.33	21 (Uu ₁)	Substrate bending	Depth 2 mm; 3 times	No visible damage, no open circuit in bent position $\pm (0.25 \% R + 0.05 \Omega)$
4.7	-	Voltage proof	$U = 1.4 \times U_{ins.}$; 60 s	No flashover or breakdown
4.35	-	Flammability, needle flame test	IEC 60695-11-5 (1); 10 s	No burning after 30 s

Note


(1) The quoted IEC standards are also released as EN standards with the same number and identical contents

DIMENSIONS



DIMENSIONS AND MASS						
TYPE / SIZE	L (mm)	W (mm)	H (mm)	T1 (mm)	T2 (mm)	MASS (mg)
D10/CRCW0402-P e3	1.0 ± 0.05	0.5 ± 0.05	0.35 ± 0.05	0.25 ± 0.05	0.2 ± 0.10	0.65
D11/CRCW0603-P e3	1.55 ± 0.10 / - 0.05	0.85 ± 0.10	0.45 ± 0.05	0.3 ± 0.20	0.3 ± 0.20	2
D12/CRCW0805-P e3	2.0 ± 0.20 / - 0.10	1.25 ± 0.15	0.45 ± 0.05	0.3 ± 0.20 / - 0.10	0.3 ± 0.20	5.5
D25/CRCW1206-P e3	3.2 ± 0.10 / - 0.20	1.6 ± 0.15	0.55 ± 0.05	0.45 ± 0.20	0.4 ± 0.20	10
CRCW1210-P e3	3.2 ± 0.20	2.5 ± 0.20	0.55 ± 0.05	0.45 ± 0.20	0.4 ± 0.20	16
CRCW1218-P e3	3.2 ± 0.10 / - 0.20	4.6 ± 0.15	0.55 ± 0.05	0.45 ± 0.20	0.4 ± 0.20	29.5
CRCW2010-P e3	5.0 ± 0.15	2.5 ± 0.15	0.6 ± 0.10	0.6 ± 0.20	0.6 ± 0.20	25.5
CRCW2512-P e3	6.3 ± 0.20	3.15 ± 0.15	0.6 ± 0.10	0.6 ± 0.20	0.6 ± 0.20	40.5

SOLDER PAD DIMENSIONS



RECOMMENDED SOLDER PAD DIMENSIONS								
TYPE / SIZE	WAVE SOLDERING				REFLOW SOLDERING			
	G (mm)	Y (mm)	X (mm)	Z (mm)	G (mm)	Y (mm)	X (mm)	Z (mm)
D10/CRCW0402-P e3	-	-	-	-	0.45	0.6	0.6	1.65
D11/CRCW0603-P e3	0.65	1.10	1.25	2.85	0.75	0.75	1.00	2.25
D12/CRCW0805-P e3	0.90	1.30	1.60	3.50	1.00	0.95	1.45	2.90
D25/CRCW1206-P e3	1.40	1.40	1.95	4.20	1.50	1.05	1.80	3.60
CRCW1210-P e3	1.80	1.45	2.95	4.70	1.70	1.10	2.80	3.90
CRCW1218-P e3	1.90	1.25	4.80	4.40	1.90	1.10	4.90	4.10
CRCW2010-P e3	3.40	1.65	2.85	6.70	3.50	1.45	2.80	6.40
CRCW2512-P e3	4.60	1.60	3.65	7.80	4.75	1.45	3.50	7.65

Note

- The rated dissipation applies only if the permitted film temperature is not exceeded. Furthermore, a high level of ambient temperature or of power dissipation may raise the temperature of the solder joint, hence special solder alloys or board materials may be required to maintain the reliability of the assembly.

The given solder pad dimensions reflect the considerations for board design and assembly as outlined e.g. in standards IEC 61188-5-x or in publication IPC-7351. They do not guarantee any supposed thermal properties, particularly as these are also strongly influenced by many other parameters. Still, the given solder pad dimensions will be found adequate for most general applications



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Vishay:](#)

CRCW08051K00DKEAP	CRCW080595K3DKEAP	CRCW08051M00DKEAP	CRCW080522R1DKEAP
CRCW040240R2DKEDP	CRCW0402665KCHEDP	CRCW0402634KCHEDP	CRCW0402332KCHEDP
CRCW0402909KCHEDP	CRCW080524R9DKEAP	CRCW0805121KFHEAP	CRCW0805475KFHEAP
CRCW06032M49DHEAP	CRCW080520K0DHEAP	CRCW0805100RDHEAP	CRCW06032K00DHEAP
CRCW060310M0DHEAP	CRCW0402100KDHEDP	CRCW12061M00DHEAP	CRCW0805100KDHEAP
CRCW080510M0DHEAP	CRCW08051M00DHEAP	CRCW0402100RDHEDP	CRCW04021K00DHEDP
CRCW0603100KDHEAP	CRCW06031M00DHEAP	CRCW04021M00DHEDP	CRCW06031K00DHEAP
CRCW040210K0DHEDP	CRCW120610K0DHEAP	CRCW080510K0DHEAP	CRCW060310K0DHEAP
CRCW08051K00DHEAP	CRCW120610M0DHEAP	CRCW0402100KFHEDP	CRCW12061K00DHEAP
CRCW0402200RDHEDP	CRCW04023K40DHEEP	CRCW0402464KCHEDP	CRCW0402160KCHEDP
CRCW0402220KCHEDP	CRCW0402154KCHEDP	CRCW120610M0DKEAP	CRCW06031K50DHEAP
CRCW060349K9DHEAP	CRCW0402499RDHEDP	CRCW08052K00DHEAP	CRCW040210K0DKEDP
CRCW060310K0DKEAP	CRCW060315K0DHEAP	CRCW06034K99DHEAP	CRCW0603499RDHEAP
CRCW0603100RDHEAP	CRCW1206100KDHEAP	CRCW120620K0DHEAP	CRCW12064K99DHEAP
CRCW12062K00DHEAP	CRCW080549K9DHEAP	CRCW040220K0DHEDP	CRCW040249K9DHEDP
CRCW08051K50DHEAP	CRCW120682R5DKEAP	CRCW040239K0FHEDP	CRCW06031K50FHEAP
CRCW0603100KFHEAP	CRCW060333K0FHEAP	CRCW060368K0FHEAP	CRCW08056K80FHEAP
CRCW060324K3FHEAP	CRCW060333K0DHEAP	CRCW040224K0FHEDP	CRCW040251K0FHEDP
CRCW060316K9DHEAP	CRCW06031M50DHEAP	CRCW060321K5DHEAP	CRCW0603249KFHEAP
CRCW06032K70DHEAP	CRCW06033K74DHEAP	CRCW1206215KFHEAP	CRCW0603191KFHEAP
CRCW06036M80DHEAP	CRCW04022K20DHEDP	CRCW06031K00DHEBP	CRCW06034M32DHEAP
CRCW06034K75FHEAP	CRCW12065K90FHEAP	CRCW120644K2DHEAP	CRCW060310K0FHEAP
CRCW08051K00FHEAP	CRCW120610K0FHEAP	CRCW080510K0DKEAP	CRCW060320K0DHEAP
CRCW060360R4DKEAP	CRCW06031K00FHEAP	CRCW06032K20FHEAP	CRCW12061K00FHEAP
CRCW08054K70FHEAP	CRCW040268K1FHEDP	CRCW25121K00FHEGP	CRCW0603100RFHEAP