


Thick Film Planar Resistors, Through-Hole, Radial Lead, High Voltage



MECHANICAL SPECIFICATIONS

Terminal Strength: 5 pound pull test

Solderability: Continuous satisfactory coverage when tested in accordance with MIL-R-10509

MATERIAL SPECIFICATIONS

Element: High temperature fired cermet film

Core: High purity 96 % alumina

Coating: Conformal coat epoxy

Termination: Standard lead material is tin plated copper

FEATURES

- Non-inductive design
- Matched sets available
- Ratio dividers available, see Vishay Techno's TR, TD datasheet
- Special testing available
- Low TCR: ± 200 ppm/°C standard, ± 100 ppm/°C available
- Tolerance: ± 10 %, ± 5 %, ± 2 %, ± 1 % standard
- Tolerance and/or TCR matching available upon request
- Material categorization: For definitions of compliance please see www.vishay.com/doc?99912



RoHS*
COMPLIANT
HALOGEN
FREE

Note

* This datasheet provides information about parts that are RoHS-compliant and/or parts that are non-RoHS-compliant. For example, parts with lead (Pb) terminations are not RoHS-compliant. Please see the information/tables in this datasheet for details.

TEMPERATURE COEFFICIENT CODE

CODE	TEMPERATURE COEFFICIENT	RANGE
K	± 100 ppm/°C	- 55 °C to + 125 °C
N	± 200 ppm/°C	- 55 °C to + 125 °C

STANDARD ELECTRICAL SPECIFICATIONS

GLOBAL MODEL / SIZE	POWER RATING		MAXIMUM WORKING VOLTAGE ⁽¹⁾ V	RESISTANCE RANGE ⁽²⁾ Ω	TOLERANCE $\pm$ %	TEMPERATURE COEFFICIENT $\pm$ ppm/°C
	P _{70 °C} W	P _{125 °C} W				
FHV025	0.25	0.125	750	10K to 100M	1, 2, 5, 10	100, 200
FHV050	0.50	0.25	1.5K	10K to 100M	1, 2, 5, 10	100
				10K to 500M	1, 2, 5, 10	200
FHV075	0.25	0.125	3.75K	500 to 500M	1, 2, 5, 10	100
				100 to 1G	1, 2, 5, 10	200
FHV100	1	0.50	7.5K	500 to 1G	1, 2, 5, 10	100
				100 to 1G	1, 2, 5, 10	200
				1.1G to 2G	5, 10	200
FHV150	1.5	0.75	11.25K	1M to 1G	1, 2, 5, 10	100
				10K to 1G	1, 2, 5, 10	200
				1.1G to 2G	5, 10	200
FHV160	1	0.50	3.5K	500 to 1G	1, 2, 5, 10	100
				100 to 1G	1, 2, 5, 10	200
				1.1G to 2G	5, 10	200
FHV200	2	1	15K	500M to 1G	1, 2, 5, 10	100
				200 to 1G	1, 2, 5, 10	200
				1.1G to 8G	5, 10	200
FHV400	2	1	7.5K	1M to 1G	1, 2, 5, 10	100
				20K to 1G	1, 2, 5, 10	200
				1.1G to 2G	5, 10	200
FHV500	4	2	15K	1M to 1G	1, 2, 5, 10	100
				30K to 1G	1, 2, 5, 10	200
				1.1G to 10G	5, 10	200

Notes

⁽¹⁾ Continuous working voltage shall be $\sqrt{P \times R}$ or maximum working voltage, whichever is less.

⁽²⁾ All resistance values are calibrated at 100 V_{DC}. Calibration at other voltages upon request.

GLOBAL PART NUMBER INFORMATION

New Global Part Numbering: FHV02510K0FNEB (preferred part number format)

F	H	V	0	2	5	1	0	K	0	F	N	E	B
GLOBAL MODEL	SIZE	RESISTANCE VALUE				TOLERANCE		TCR	TERMINAL FINISH		PACKAGING		
FHV	025 050 075 100 150 160 200 400 500	R = Ω K = $k\Omega$ M = $M\Omega$ G = $G\Omega$ 400R = 400 Ω 10M0 = 10 $M\Omega$ 10G0 = 10 $G\Omega$				F = $\pm 1.0\%$ G = $\pm 2.0\%$ J = $\pm 5.0\%$ K = $\pm 10.0\%$		K = 100 ppm N = 200 ppm	E = Sn100 R = Sn60/Pb40		B = Bag S = Strip		

Historical Part Numbering: FHV0251002FMe3 (will continue to be accepted)

FHV	025	1002	F	M	e3
HISTORICAL MODEL	SIZE	RESISTANCE VALUE	TOLERANCE	TCR	TERMINAL FINISH

Note

- For additional information on packaging, refer to the Through Hole Resistor Packaging document (www.vishay.com/doc?31544).

DIMENSIONS in inches (millimeters)

Figure 1






Figure 2



MODEL - SIZE	A (max.) (Height)	B (max.) (Length)	C (Lead Spacing)	D (Lead Length)	E (Lead DIA)	FIGURE
FHV025	0.300 (7.62)	0.300 (7.62)	0.200 (5.08)	0.250 (6.35)	0.018 (0.457)	1
FHV050	0.380 (9.65)	0.380 (9.65)	0.200 (5.08)	0.360 (9.14)	0.020 (0.508)	1
FHV075	0.210 (5.33)	0.570 (14.48)	0.400 (10.16)	1.50 (38.10)	0.025 (0.635)	2
FHV100	0.280 (7.11)	1.07 (27.18)	0.900 (22.86)	1.50 (38.10)	0.032 (0.813)	2
FHV150	0.330 (8.38)	1.57 (39.88)	1.40 (35.56)	1.50 (38.10)	0.032 (0.813)	2
FHV160	0.550 (13.97)	0.550 (13.97)	0.400 (10.16)	1.50 (38.10)	0.032 (0.813)	2
FHV200	0.330 (8.38)	2.04 (51.82)	1.90 (48.26)	1.50 (38.10)	0.032 (0.813)	2
FHV400	0.550 (13.97)	1.05 (26.67)	0.900 (22.86)	1.50 (38.10)	0.032 (0.813)	2
FHV500	0.550 (13.97)	2.07 (52.58)	1.90 (48.26)	1.50 (38.10)	0.032 (0.813)	2


ENVIRONMENTAL PERFORMANCE

TEST	MAXIMUM ΔR (Typical Test Lots)
Short time overload	$< \pm 0.2\%$
Moisture resistance	$< \pm 0.5\%$
Shock	$< \pm 0.2\%$
Vibration	$< \pm 0.2\%$
Temperature cycling	$< \pm 0.5\%$
Load life	$< \pm 1.0\%$
Dielectric withstanding voltage	$< \pm 0.15\%$
Resistance to soldering heat	$< \pm 0.1\%$

DERATING




VOLTAGE COEFFICIENT





Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Vishay:](#)

[FHV0752005FME3](#) [FHV0501M00FKRB](#) [FHV5002005FKE3](#) [FHV-025 10M 1%H](#) [FHV075330MKNEB](#)
[FHV2001G00FNEB](#) [FHV500100MKKEB](#) [FHV-050 100M .5%M](#) [FHV-075 330M 10%M](#) [FHV-100 400M 10%M](#) [FHV-](#)
[100 5M 1%M](#) [FHV-100 7.25M 5%M](#) [FHV-200 1G 2%ME3](#) [FHV1007M25JNRS](#) [FHV075100MKNES](#)
[FHV1001G00GNRB](#) [FHV-100 50M 10%M](#) [FHV0508663FKE3](#) [FHV0753006FME3](#) [FHV100100MFKEB](#)
[FHV075100MKMRB](#) [FHV075330MKNE](#) [FHV075330MKMES](#) [FHV050100MDMRS](#) [FHV2001G00GNEB](#)
[FHV100400MKNRS](#) [FHV075300MFNES](#) [FHV10050M0KNRB](#) [FHV07520M0FNES](#) [FHV07520M0FKEB](#)
[FHV07520M0FKES](#) [FHV02510M0FKRB](#) [FHV40047M0FKEB](#) [FHV50050M0JNRB](#) [FHV50020M0FKEB](#)
[FHV50030M0JKEB](#) [FHV50033M0JNEB](#) [FHV10050M0KNEB](#) [FHV075100MKNEB](#) [FHV50016M0GKRB](#)
[FHV200100MFKES](#) [FHV4001M00KKEB](#) [FHV1602K40FKRB](#) [FHV1002M70GKEB](#) [FHV150330MFNES](#)
[FHV16010M0FKEB](#) [FHV1503M01FKES](#) [FHV1005M60GKEB](#) [FHV2001G00FKES](#) [FHV075100MFKRB](#)
[FHV100200MJNEB](#) [FHV5002M00FKEB](#) [FHV400150KFKEB](#) [FHV160249KFNES](#) [FHV1004M70GKEB](#)
[FHV40013M3GKEB](#) [FHV5001M00FNEB](#) [FHV10020M0FKEB](#) [FHV15051M1FKES](#) [FHV20016M6FKEB](#)
[FHV10050M0GKEB](#) [FHV16025M0FKEB](#) [FHV0501M18FKRB](#) [FHV1501G00KKRS](#) [FHV2003M00FKEB](#)
[FHV1001M00FKES](#) [FHV1501G00FNES](#) [FHV1501M00KKRS](#) [FHV075100MJNRS](#) [FHV1001M20GKEB](#)
[FHV2005M00FKEB](#) [FHV1002M40KNRS](#) [FHV50050M0GKEB](#) [FHV50020M0JKES](#) [FHV1503M01FKEB](#)
[FHV1003M30FKEB](#) [FHV50033M0FKEB](#) [FHV1007M25JNES](#) [FHV100125MFKEB](#) [FHV0501M00FKEB](#)
[FHV075330MKNES](#) [FHV4001M00KKES](#) [FHV20030M0FKEB](#) [FHV07510M0KNEB](#) [FHV5002M00JNEB](#)
[FHV10022M0FNEB](#) [FHV1001G00GNEB](#) [FHV5001M80JNEB](#) [FHV10010M0FKEB](#) [FHV50020M0FKES](#)
[FHV1505M00FKEB](#) [FHV100334KKNRB](#) [FHV100150MKKEB](#) [FHV07550M0FKRB](#) [FHV50010M0GKEB](#)
[FHV10050M0GNES](#) [FHV07530M0FNEB](#) [FHV10020M0FKRB](#) [FHV0751M00KKEB](#) [FHV050866KFKEB](#)