

SMD Wraparound Ultra Low Value Thin Film Resistors



ADDITIONAL RESOURCES



With extremely low resistance and high power capabilities, these ultra low value resistors are available with solderable or weldable terminations.

FEATURES

- NiCr + Ta₂O₅ resistive layer
- Pre-soldered or gold terminations
- No inductance for high frequency applications
- Alumina substrates for high power handling capability
- Resistance range: 0.1 Ω to 9.99 Ω
- TCR down to 50 ppm/°C
- Power rating: up to 2 W at +70 °C
- Withstand AEC-Q200 humidity test
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912



RoHS*
Available
HALOGEN
FREE
Available
GREEN
(5-2008)
Available

Note

* This datasheet provides information about parts that are RoHS-compliant and / or parts that are non RoHS-compliant. For example, parts with lead (Pb) terminations are not RoHS-compliant. Please see the information / tables in this datasheet for details

STANDARD ELECTRICAL SPECIFICATIONS

MODEL	SIZE	RESISTANCE RANGE Ω	RATED POWER $P_{70\text{ }^{\circ}\text{C}}$ W	LIMITING ELEMENT VOLTAGE V	TOLERANCE \pm %	TEMPERATURE COEFFICIENT \pm ppm/°C
L0603	0603	0.1 to 9.99	0.125	50	1, 2, 3, 5, 10	50, 100, 200, 300
L0805	0805	0.1 to 9.99	0.2	50	1, 2, 3, 5, 10	50, 100, 200, 300
L1206	1206	0.1 to 9.99	0.33	50	1, 2, 3, 5, 10	50, 100, 200, 300
L1505	1505	0.1 to 9.99	0.5	50	1, 2, 3, 5, 10	50, 100, 200, 300
L2010	2010	0.1 to 9.99	1.0	50	1, 2, 3, 5, 10	50, 100, 200, 300
L2512	2512	0.1 to 9.99	2.0 ⁽¹⁾	50	1, 2, 3, 5, 10	50, 100, 200, 300

Note

⁽¹⁾ With special assembly care

CLIMATIC SPECIFICATIONS

Operating temperature range	-55 °C; +155 °C
-----------------------------	-----------------

MECHANICAL SPECIFICATIONS


Substrate	Alumina
Technology	NiCr + Ta ₂ O ₅
Coating	Silicone
Terminations	Solderable B type: SnPb over nickel barrier N type: SnAg over nickel barrier G type: Gold over nickel barrier

Note


- Refer to Application Note "Guidelines for Vishay Sfernice Resistive and Inductive Components" (document number: 52029) for recommended reflow profile. Profile #3 applies

TOLERANCE AND TCR VS. OHMIC VALUE

OHMIC VALUE RANGE in Ω	TIGHTEST TOLERANCE (%)	BEST TCR (ppm/°C)	TERMINATIONS
0R1 < 0R25	1	300	N or B
0R25 < 0R5	1	200	N or B
0R5 < 2R5	1	100	N or B
2R5 < 9R99	1	50	N or B
0R1 < 0R25	5	300	G
0R25 < 0R5	5	200	G
0R < 1R	5	100	G
1R < 2R5	3	100	G
2R5 to 9R99	3	50	G

DIMENSIONS in millimeters (inches)


CASE SIZE	A	B	C	D/E
	$\pm 0.152 (\pm 0.006)$	$\pm 0.127 (\pm 0.005)$	$\pm 0.127 (+ 0.005)$	$\pm 0.127 (\pm 0.005)$
0603	1.52 (0.060)	0.85 (0.033)	0.5 (0.020)	0.38 (0.015)
0805	1.91 (0.075)	1.27 (0.050)		0.40 (0.016)
1206	3.06 (0.120)	1.60 (0.063)		0.48 (0.019)
1505	3.81 (0.150)	1.32 (0.052)		
2010	5.08 (0.200)	2.54 (0.100)		
2512	6.30 (0.248)	3.30 (0.129)		

SUGGESTED LAND PATTERN in millimeters (inches) (to IPC-7351A)



CASE SIZE	Z _{max.}	G _{min.}	X _{max.}
0603	2.37 (0.093)	0.35 (0.014)	0.98 (0.039)
0805	2.76 (0.109)	0.74 (0.029)	1.40 (0.055)
1206	3.91 (0.154)	1.85 (0.073)	1.73 (0.068)
1505	4.66 (0.183)	2.44 (0.096)	1.45 (0.057)
2010	5.93 (0.233)	3.71 (0.146)	2.67 (0.105)
2512	7.15 (0.281)	4.93 (0.194)	3.43 (0.135)

Option: Enlarged Terminations: 0063

For stringent and special power dissipation requirements, the thermal resistance between the resistive layer and the solder joint can be reduced using enlarged terminations chip resistors which are soldered on large and thick copper pads acting as heat sinks (see application note: "Power Dissipation in High Precision Vishay Sfernice Chip Resistors and Arrays (P Thin Film, PRA Arrays, CHP Thick Film)": www.vishay.com/doc?53048).

For enlarged terminations: Please consult Vishay Sfernice.

POWER DERATING CURVE



PACKAGING RULES

Waffle Pack

Can be filled up to maximum quantity indicated in the table here above, taking into account the minimum order quantity. When quantity ordered exceeds maximum quantity of a single waffle pack, the waffle packs are stacked up on the top of each other and closed by one single cover.

To get “not stacked up” waffle pack in case of ordered quantity > maximum number of pieces per package: Please consult Vishay Sfernice for specific ordering code.

PACKAGING

Several types of packaging are proposed: waffle-pack and tape and reel

SIZE	MOQ	NUMBER OF PIECES PER PACKAGE		TAPE WIDTH
		WAFFLE PACK 2" x 2"	TAPE AND REEL	
			MIN.	
0603	100	100	5000	8 mm
0805			4000	
1206		60		
1505			50	
2010		2000		
2512				

Tape and Reel

Can be filled up to maximum quantity indicated in the table here above, taking into account the minimum order quantity. When quantity ordered is between the MOQ and the maximum reel capacity, only one reel is provided.

When several reels are needed for ordered quantity within MOQ and maximum reel capacity: Please consult Vishay Sfernice for specific ordering code.

PERFORMANCE			
TESTS	CONDITIONS	VALUES AND DRIFT	
		MIL-R-55342 REQUIREMENTS	TYPICAL PERFORMANCES
Thermal shock	MIL-R-55342 C MIL-STD-702, method 107	± 0.25 %	± 0.02 %
Short time overload	MIL-R-55342 C PARA 3.10.4.7.5	± 0.10 %	± 0.01 %
Low temperature operation	MIL-R-55342 C PARA 3.9 and 4.7.4	± 0.25 %	± 0.01 %
Resistance to solder heat	MIL-R-55342 C PARA 3.12, 4.7.7, 4.7.1.2	± 0.25 %	± 0.04 %
Moisture resistance	MIL-R-55342 C PARA 3.13 and 4.7.8 MIL-STD-202, method 106	± 0.40 %	± 0.01 %
	AEC-Q200 85 °C / 85 % RH / 0.1 Pn 1000 h	-	Max. < 0.5 % + 0.05 Ω
High temperature	MIL-R-55342 C PARA 3.11 and 4.7.6	± 0.20 %	± 0.075 %
Load life	MIL-R-55342 C 2000 h Pn at 70 °C MIL-STD-202, method 108	± 0.50 %	± 0.15 %

**GLOBAL PART NUMBER INFORMATION**

New Global Part Numbering: L0805K1R00FBT0099

L	0	8	0	5	K	1	R	0	0	F	B	T	0	0	9	9
GLOBAL MODEL	SIZE	TCR	VALUE	TOLERANCE	TERMINATION ⁽¹⁾	PACKAGING	OPTION									
L	0603 0805 1206 1505 2010 2512	H = ± 50 ppm K = ± 100 ppm L = ± 200 ppm M = ± 300 ppm	R designated decimal point For values under 1R Rxxx	F = ± 1 % G = ± 2 % H = ± 3 % J = ± 5 % K = ± 10 %	B: SnPb over nickel barrier N: SnAg over nickel barrier G: gold over nickel barrier	For more information see Codification of Packaging table	Leave blank if no option									

Historical Part Number Example: L 0805 K 1R00 1 % B T R0099

L	0805	K	1R00	1 %	B	T	R0099
MODEL	SIZE	TCR	VALUE	TOLERANCE	TERMINATION	PACKAGING	OPTION

Note

- ⁽¹⁾ **B:** lead bearing version
N and **G:** lead (Pb)-free / RoHS version

CODIFICATION OF PACKAGING

CODE 18	PACKAGING
WAFFLE PACK	
W	100 min., 1 mult.
WA	100 min., 100 mult. (available only in size 1206)
PLASTIC TAPE (Standard for all sizes)	
T	100 min., 1 mult.
TA	100 min., 100 mult.
TB	250 min., 250 mult.
TC	500 min., 500 mult.
TD	1000 min., 1000 mult.
TE	2500 min., 2500 mult.
TF	Full tape (quantity depending on size of chips)
PAPER TAPE (Available for 0603, 0805, and 1206. Please consult Vishay Sfernice for other sizes)	
PT	100 min., 1 mult.
PA	100 min., 100 mult.
PB	250 min., 250 mult.
PC	500 min., 500 mult.
PD	1000 min., 1000 mult.
PE	2500 min., 2500 mult.
PF	Full tape (quantity depending on size of chips)



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Vishay:](#)

[L1206H10R0FBW](#) [L1206MR120JBW](#) [L1206MR300KBT](#) [L1206M1R80JBT](#) [L0603K10R0FBT](#) [L0805M5R00FGW](#)
[L2512MR250FBT](#) [L1206MR100LBT](#) [L1505M2R00FBW](#) [L0805K2R20HBT](#) [L0805M2R43FBW](#) [L0805M4R70FBT](#)
[L0805MR100GBW](#) [L1020M1R00KBW](#) [L1206M1R50JBT](#) [L1206M2R00FBT](#) [L1206M4R99FBW](#) [L1206MR300KBW](#)
[L1206MR300KGW](#) [L1505MR750FBT](#) [L2512MR180GBT](#) [L1206MR100MBT](#) [L2010K6R20GBW](#) [L2010K7R50GBW](#)
[L1206MR100MST](#) [L0805M10R0FBT](#) [L2512M10R0FBW](#) [L2512M10R0FBT](#) [L1505K3R01GBT](#) [L1206MR100FBT](#)
[L0603MR100KNT](#) [L0805M4R75FBT](#) [L0603KR500JBT](#) [L0805LR330JBT](#) [L0805K6R81FBT](#) [L0805MR390KBT](#)
[L1206MR324KBT](#) [L2010K1R00FNT](#) [L0805K7R50FBT](#) [L0805LR330FBT](#) [L0603MR150KNT](#) [L2010H3R00FNT](#)
[L0805MR100KBW](#) [L0805MR200KBT](#) [L0805LR750JBT](#) [L1206K4R99GGT](#) [L1206M2R70JBW](#) [L2010KR500FNT](#)
[L0603MR100FBT](#) [L0603K4R00JGW](#) [L0805L3R30GBT](#) [L0603K1R00FNT](#) [L2010K3R00GGT](#) [L0805MR100KBT](#)
[L0805K9R09FBT](#) [L2010LR400FNT](#) [L0805K2R00GBT](#) [L0805L1R00HBT](#) [L1505K3R01HBT](#) [L1206K3R92GNT](#)
[L0805K5R62FBT](#) [L1206L2R00GNT](#) [L1206MR300GBW](#) [L0805LR470FNT](#) [L0805MR180FNT](#) [L0805MR200KNTC](#)
[L0805MR100GBT](#) [L1206K3R92FNT](#) [L0603MR150KNTD](#) [L1206K3R90HGT](#) [L2010M2R74JBT](#) [L0805MR510FBT](#)
[L1505K1R30HGT](#) [L2010K2R00FNT](#) [L0805MR200KNT](#) [L0603LR301FBT](#) [L0805MR510FBTC](#) [L0805K5R76FNT](#)
[L0805MR470KBT](#) [L0805L2R20GBT](#) [L0805K4R99FNT](#) [L2010MR200JBW](#) [L0805MR100JBT](#) [L0603KR604JBT](#)
[L0805LR910JBT](#) [L1206M1R10JGT](#) [L2010K2R00GBT](#) [L0805L4R70GBT](#) [L1206K1R00HBT](#) [L1206K4R02FBT](#)
[L0805K1R00HGT](#) [L2010K1R50HBT](#) [L2010K10R0JBT](#) [L0805LR560JBT](#) [L0603MR100KBT](#) [L0603MR250KNT](#)
[L1206MR100GBT](#) [L0805LR820JBT](#) [L2010H5R00FNT](#) [L1206K1R00HGT](#)