



Sample Kit

Precision Thin Film MELF Resistors

MMB 0207-25 0.1 %



FEATURES

- Approved to EN 140401-803
- AEC-Q200 qualified
- Advanced metal film technology
- Superior stability: class 0.05
- Sulfur resistance verified according to ASTM B 809
- Material categorization:
for definitions of compliance please see www.vishay.com/doc?99912

AUTOMOTIVE
GRADE

RoHS
COMPLIANT
HALOGEN
FREE
GREEN
(5-2008)

Files contain lengths of blister tape, each holding 20 resistors. The kit contains every fourth value of the E 96-series. Parts are sorted in the ascending order of its resistance value and appropriately marked.

SPECIFICATIONS

Laboratory kit	LMB 96/4
Resistor type	MMB 0207-25 0.1 %
Temperature coefficient	± 25 ppm/K
Tolerance	± 0.1 %
Resistance range/E-series	33 Ω to 1 MΩ/every 4 th value of E 96 ⁽¹⁾
Number of resistance values	109
Resistors per value/total	20/2180
Number of pages/files	11/1

Notes

- The products are specified by the underlying standard product's datasheet "Precision MELF Resistors" in its most current edition at www.vishay.com/doc?28714
- ⁽¹⁾ Supplemented by 33R

PART NUMBER AND PRODUCT DESCRIPTION

PART NUMBER: LMB964MMB02070DB00

L	M	B	9	6	4	M	M	B	0	2	0	7	0	D	B	0	0
KIT	E-SERIES	FRACTION OF E-SERIES	TYPE/SIZE	VERSION	TCR	TOLERANCE											
LMB	96	4 = 1/4	MMB 0207	0 = Standard	D = ± 25 ppm/K	B = ± 0.1 %											

PRODUCT DESCRIPTION: LMB 96 4 MMB 0207-25 0.1 %

LMB	96	4	MMB 0207	-25	0.1 %
KIT	E-SERIES	FRACTION OF E-SERIES	TYPE/SIZE	TCR	TOLERANCE
LMB	96	4 = 1/4	MMB 0207	± 25 ppm/K	± 0.1 %

Note

- The product can be ordered using either the PART NUMBER or the PRODUCT DESCRIPTION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Vishay:

[LMB964MMB02070DB00](#)