






8				7			
THIS DRAWING IS UNPUBLISHED.				RELEASED FOR PUBLICATION			
COPYRIGHT 20				20			
BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.							
PART NUMBER	REV	FIRST USED	POWER UNIT	FEED TYPE	DESCRIPTION		
1852667-1	A	122500-1	LEADMAKER	POST FEED	CUTS CARRIER		
1852667-2	A	565435-5	BENCH MODEL K	PRE FEED	CUTS CARRIER		
1852667-3	A	354500-1	BENCH MODEL G	PRE FEED	CUTS CARRIER		
1852667-6	A	122500-1	LEADMAKER	POST FEED	CONTINUOUS CARRIER		
7-1852667-7	A	-	-	-	SPARE PARTS		

- 1 RECOMMENDED SPARE PARTS
2 GREASE LIGHTLY
3 GUARD MUST BE IN PLACE WHEN OPERATING APPLICATOR IN A BENCH MACHINE
4 CUT TO LENGTH AT ASSEMBLY.



TERMINAL NAME: 6.3mm TAB CONTACT					
TE P/N	GHW/LEAR P/N	GHW/LEAR TERMINAL - TE CRIMP SPECS			
1949657-1	25297.123.178				
-	-	PAD LTR	CRIMP HEIGHT		WIRE SIZE
-	-	A	1.48mm+0.05/-0.05[.058+.002/-0.002]		1mm2
-	-	B	1.41mm+0.05/-0.05[.056+.002/-0.002]		0.8mm2
-	-	C	1.30mm+0.05/-0.05[.051+.002/-0.002]		0.5mm2
-	-	D			-
-	-	CRIMP	SIZE	TYPE	RANGE
-	-	WIRE	2.29mm [0.090]	F	0.5-1.0mm2
-	-	INSUL	3.94mm [0.155]	F	Ø3.200 MAX
WIRE STRIP LENGTH 4.600-5.400	TERM APPL SPEC NONE	FEED 13.970	APPLICATOR INSTRUCTIONS 408-8040		SET UP GAGE 458637-1



-	1	1	1	1	-	693855-1	FRONT STRIP GUIDE	195
-	2	2	2	2	-	2-354779-5	PIN, WIRE DISC, .3115	128
-	2	2	2	2	-	1-354779-5	PIN, WIRE DISC, .3065	127
-	2	2	2	2	-	354779-9	PIN, WIRE DISC, .3035	126
-	1	1	1	1	-	21055-5	WASHER, FLAT, REG NO 6	119
-	-	-	REF	-	...	455749-1	GUARD WINDOW	116
-77	-6	-3	-2	-1	U/M	PART NO	DESCRIPTION	ITEM NO

LOC		DIST		REVISIONS						
A	66	F	LTR	DESCRIPTION			DATE	DWN	APVD	
		A		RELEASED			07MAY2008	RK	GB	

DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		DWN		03APR2008		Tyco Electronics		Tyco Electronics</
-------------	--	--	--	-----	--	-----------	--	------------------	--	--------------------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1852667-1](#)