





THIS DRAWING IS UNPUBLISHED.
 RELEASED FOR PUBLICATION 20
 © COPYRIGHT 20 BY TYCO ELECTRONICS CORPORATION. ALL INTERNATIONAL RIGHTS RESERVED.

LOC		DIST		REVISIONS			
P	LTR	DESCRIPTION		DATE	OWN	APVD	
B		RELEASED PER ECO 11-005371		3-15-11	CT	RL	



MATING FACE



1) FRONT & REAR INSULATOR: HIGH-TEMP THERMOPLASTIC OR THERMOSET EPOXY PER ASTM D5948
 CONTACT RETENTION CLIPS: STAINLESS STEEL PER AISI 302 OR COPPER ALLOY PER ASTM B194
 REAR GROMMET & INTERFACIAL SEAL: FLUOROSILICON ELASTOMER PER MIL-R-25988 B, EXCEPT 4.6.6.1

2) PART TO BE MARKED WITH TE IDENTIFICATION,
 TE PART NO. AND DATE CODE: YEAR & WEEK (YY WW) IN APPROXIMATE AREA SHOWN.

- THIS INSERT CONTAINS: 8 CAVITIES FOR SIZE 20 CONTACTS AND 2 CAVITIES FOR SIZE 8 CONTACTS
- THIS PRODUCT IS SOLD BY TE UNDER A LICENSE FROM RADIALL SA.

ENVIRONMENTAL		EPXBE10Q2PA	1877702-1
REMARKS		DESCRIPTIVE PART NO.	PART NUMBER
DWN RJM3	04MAR2011	Tyco Electronics Tyco Electronics Corporation Harrisburg, PA 17105-3608	ENVIRONMENTAL 10Q2 INSERT FOR 8 SIZE 20 & 2 SIZE 8 PIN CTS
CHK R RELEASE	04MAR2011		
APVD R RELEASE	04MAR2011		
PRODUCT SPEC	-		
APPLICATION SPEC	-		
SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A2	00779	C=1877702	-
CUSTOMER DRAWING			SCALE 4:1 SHEET 1 OF 1 REV B

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION
 IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION
 SHOULD BE CONTACTED FOR THE LATEST REVISION.

DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:	
mm		0 PLC	±0.5
		1 PLC	±0.5
		2 PLC	±0.13
		3 PLC	±0.013
		4 PLC	±0.0001
		ANGLES	±-
MATERIAL		FINISH	-

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1877702-1](#)