








REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	B2	REVISED (ECR-16-009958)	31.OCT.16	SJ	JW




SECTION A1-A1



<TABLE 1>					
TYPE	PART NO.	WIRE SIZE(mm ²)	Insulation DIA(mm)	Applicable WIRE	FINISH
MTII	0-963902-1	0.2~0.5	1.15~1.6	AVSSXF 0.5 Max	CuSn4
	0-963902-3				CuSn4(GOLD)
	0-963904-1	0.5~1.0	1.4~2.1	AVSSXF 0.85 Max	CuSn4
	0-963904-3				CuSn4(GOLD)
JPT	1-962915-1	0.5~1.0	2.1 Max	AVSSXF 0.85 Max	CuSn4
	1-962915-3				CuSn4(GOLD)
	1-962916-1	1.0~2.5	3.0 Max	AVSS 2.0 Max or FLR 2.5 Max	CuSn4
	1-962916-3				CuSn4(GOLD)



ISOMETRIC VIEW




<TABLE 2>			
TYPE	PART NO.	WIRE INSULATION DIAMETER(mm)	COLOR
MTII	964971-1	1.2~1.6	RED
	963530-1	1.4~1.9	GRAY
	964972-1	1.9~2.1	YELLOW
	963531-1	CAVITY PLUG	WHITE
JPT	828904-2	1.2~2.1	BLUE
	828905-1	2.2~3.0	WHITE
	828922-1	CAVITY PLUG	NATURAL

NOTE

- GENERAL TOLERANCE: ± 0.3 , $\pm 3^\circ$
- APPLIED PLUG P/N:X-1897009-X
APPLIED WIRE COVER P/N:X-1897015-X
- APPLICABLE TAB CONTACT P/N:TABLE 1
- APPLICABLE WIRE SEAL P/N:TABLE 2

B2	CAP HSG FOR HYB 26P	PA66-GF30	GRAY	1897013-3
	CAP HSG FOR HYB 26P	PA66-GF30	BALCK	1897013-2
DESCRIPTION		MATERIAL	COLOR	P/N

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN SJ CHOI	NAME CAP HSG FOR MTII JPT SEALED 26P	
DIMENSIONS: mm		CHK SJ CHOI		
 3rd ANGLE PROJECTION		APVD JW JUNG	SIZE A2	
		PRODUCT SPEC		
MATERIAL SEE TABLE		APPLICATION SPEC	CAGE CODE 00779	
		WEIGHT	DRAWING NO C=1897013	
		CUSTOMER DRAWING	SCALE 2:1	SHEET 1 OF 1
			REV B2	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1897013-2](#)