

4

3

2

1

THIS DRAWING IS UNPUBLISHED.	RELEASED FOR PUBLICATION	LOC	DIST	REVISIONS			
(C) COPYRIGHT	ALL RIGHTS RESERVED.						
				P	LTR	DESCRIPTION	DATE
						A1 ECR-14-001883	11FEB2014
							GK HMR

# REPLACED BY OCEAN STYLE APPLICATOR PART NUMBER 2151357-6

FOR REPLACEMENT PARTS FOR APPLICATOR 1911048  
REFER TO ADDITIONAL PAGE(S). SPARE PARTS KIT (IF LISTED)  
WILL REMAIN AVAILABLE.

THE REPLACEMENT OCEAN STYLE APPLICATOR HAS THE  
SAME TERMINATOR/PRESS INTERFACE AS APPLICATOR  
1911048

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN GOPALAKRISHNA HV		TE Connectivity	
DIMENSIONS:		CHK RAGHAVENDRA			
		APVD RAGHAVENDRA			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC			
0 PLC ±		APPLICATION SPEC			
1 PLC ±					
2 PLC ±					
3 PLC ±					
4 PLC ±					
ANGLES ±					
MATERIAL		WEIGHT		RESTRICTED TO	
FINISH		CUSTOMER DRAWING		A3	
		DRAWING NO		C- 1911048	
		SCALE		SHEET 1 OF 2	
				REV A1	

8	7	6	5	4	3	2	1																																																																																																																																																																																																																																																																																																																																																																																																								
THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 26				REVISIONS																																																																																																																																																																																																																																																																																																																																																																																																											
<p>© COPYRIGHT 2000 BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.</p> <table border="1"> <tr> <td>PART NUMBER</td> <td>REV</td> <td>DESCRIPTION</td> <td>PROGRAMMED MEMORY CHIP</td> </tr> <tr> <td>1911048-1</td> <td>A</td> <td>CUTS CARRIER</td> <td>8-1911048-1</td> </tr> <tr> <td>1911048-6</td> <td>A</td> <td>CONTINUOUS CARRIER</td> <td>8-1911048-6</td> </tr> <tr> <td>7-1911048-1</td> <td>A</td> <td>-1 AND SPARE PARTS</td> <td>9-1911048-1</td> </tr> <tr> <td>7-1911048-6</td> <td>A</td> <td>-6 AND SPARE PARTS</td> <td>9-1911048-6</td> </tr> <tr> <td>7-1911048-7</td> <td>A</td> <td>SPARE PARTS KIT</td> <td>-</td> </tr> </table>				PART NUMBER	REV	DESCRIPTION	PROGRAMMED MEMORY CHIP	1911048-1	A	CUTS CARRIER	8-1911048-1	1911048-6	A	CONTINUOUS CARRIER	8-1911048-6	7-1911048-1	A	-1 AND SPARE PARTS	9-1911048-1	7-1911048-6	A	-6 AND SPARE PARTS	9-1911048-6	7-1911048-7	A	SPARE PARTS KIT	-	<p>FEED FINGER 1901694-1 SET UP GAGE 1901040-1 LOC A DIST 66</p> <table border="1"> <tr> <td>P</td> <td>LTR</td> <td>RELEASED</td> </tr> <tr> <td>A</td> <td></td> <td>05AUG2007 MEH GB</td> </tr> <tr> <td></td> <td></td> <td></td> </tr> </table>				P	LTR	RELEASED	A		05AUG2007 MEH GB																																																																																																																																																																																																																																																																																																																																																																										
PART NUMBER	REV	DESCRIPTION	PROGRAMMED MEMORY CHIP																																																																																																																																																																																																																																																																																																																																																																																																												
1911048-1	A	CUTS CARRIER	8-1911048-1																																																																																																																																																																																																																																																																																																																																																																																																												
1911048-6	A	CONTINUOUS CARRIER	8-1911048-6																																																																																																																																																																																																																																																																																																																																																																																																												
7-1911048-1	A	-1 AND SPARE PARTS	9-1911048-1																																																																																																																																																																																																																																																																																																																																																																																																												
7-1911048-6	A	-6 AND SPARE PARTS	9-1911048-6																																																																																																																																																																																																																																																																																																																																																																																																												
7-1911048-7	A	SPARE PARTS KIT	-																																																																																																																																																																																																																																																																																																																																																																																																												
P	LTR	RELEASED																																																																																																																																																																																																																																																																																																																																																																																																													
A		05AUG2007 MEH GB																																																																																																																																																																																																																																																																																																																																																																																																													
<table border="1"> <tr> <td>APPLICATOR DATA</td> </tr> <tr> <td>CRIMP SIZE TYPE</td> </tr> <tr> <td>WIRE 2.03mm [.080] F</td> </tr> <tr> <td>INSUL 4.06mm [.160] O</td> </tr> <tr> <td>APPL INSTRUCTIONS 408-10135</td> </tr> </table>				APPLICATOR DATA	CRIMP SIZE TYPE	WIRE 2.03mm [.080] F	INSUL 4.06mm [.160] O	APPL INSTRUCTIONS 408-10135																																																																																																																																																																																																																																																																																																																																																																																																							
APPLICATOR DATA																																																																																																																																																																																																																																																																																																																																																																																																															
CRIMP SIZE TYPE																																																																																																																																																																																																																																																																																																																																																																																																															
WIRE 2.03mm [.080] F																																																																																																																																																																																																																																																																																																																																																																																																															
INSUL 4.06mm [.160] O																																																																																																																																																																																																																																																																																																																																																																																																															
APPL INSTRUCTIONS 408-10135																																																																																																																																																																																																																																																																																																																																																																																																															
<p>TERMINAL DATA: DELPHI TERMINAL DELPHI CRIMP SPEC</p> <p>TERMINAL NAME: TAXI TERMINAL F GT 150</p> <p>WIRE STRIP LENGTH INSULATION DIAMETER RANGE 4</p> <p>4.5-4.5 mm [.177-.177 IN] 1.60-2.15mm [.062-.084 IN]</p> <p>TERMINAL 12191817 Rev 3 APPL SPEC -</p> <p>TERMINALS APPLIED</p> <table border="1"> <tr> <td>TE TERMINAL</td> <td>DELPHI TERMINAL</td> <td>TE SEAL</td> <td>DELPHI SEAL</td> </tr> <tr> <td>1949151-1</td> <td>12191817</td> <td>1949406-1</td> <td>15324976 10</td> </tr> </table>				TE TERMINAL	DELPHI TERMINAL	TE SEAL	DELPHI SEAL	1949151-1	12191817	1949406-1	15324976 10																																																																																																																																																																																																																																																																																																																																																																																																				
TE TERMINAL	DELPHI TERMINAL	TE SEAL	DELPHI SEAL																																																																																																																																																																																																																																																																																																																																																																																																												
1949151-1	12191817	1949406-1	15324976 10																																																																																																																																																																																																																																																																																																																																																																																																												
<table border="1"> <tr> <td>WIRE SIZE</td> <td>CRIMP HEIGHT mm [INCH]</td> </tr> <tr> <td>1mm<sup>2</sup></td> <td>1.40±.05 [.055±.002]</td> </tr> <tr> <td>0.75mm<sup>2</sup> or 0.80mm<sup>2</sup></td> <td>1.25±.05 [.049±.002]</td> </tr> </table>				WIRE SIZE	CRIMP HEIGHT mm [INCH]	1mm <sup>2</sup>	1.40±.05 [.055±.002]	0.75mm <sup>2</sup> or 0.80mm <sup>2</sup>	1.25±.05 [.049±.002]																																																																																																																																																																																																																																																																																																																																																																																																						
WIRE SIZE	CRIMP HEIGHT mm [INCH]																																																																																																																																																																																																																																																																																																																																																																																																														
1mm <sup>2</sup>	1.40±.05 [.055±.002]																																																																																																																																																																																																																																																																																																																																																																																																														
0.75mm <sup>2</sup> or 0.80mm <sup>2</sup>	1.25±.05 [.049±.002]																																																																																																																																																																																																																																																																																																																																																																																																														
				<table border="1"> <tr> <td>-</td> <td>1</td> <td>1</td> <td>1</td> <td>1</td> <td>1-993111-6</td> <td>PIN, SLOTTED SPRING 3.0 X 30.0</td> <td>177</td> </tr> <tr> <td>-</td> <td>2</td> <td>2</td> <td>2</td> <td>2</td> <td>3-22280-7</td> <td>SPRING, COMPRESSION</td> <td>176</td> </tr> <tr> <td>-</td> <td>1</td> <td>1</td> <td>1</td> <td>1</td> <td>1752353-1</td> <td>GUIDE PIN, HOLDDOWN</td> <td>175</td> </tr> <tr> <td>-</td> <td>1</td> <td>1</td> <td>1</td> <td>1</td> <td>1901680-1</td> <td>GUIDE PIN, HOLDDOWN</td> <td>174</td> </tr> <tr> <td>-</td> <td>REF</td> <td>REF</td> <td>REF</td> <td>REF</td> <td>SEE TABLE</td> <td>MEMORY CHIP, PROGRAMMED</td> <td>135</td> </tr> <tr> <td>-</td> <td>1</td> <td>1</td> <td>1</td> <td>1</td> <td>1633565-1</td> <td>DOCUMENTATION PACKAGE</td> <td>71</td> </tr> <tr> <td>-</td> <td>1</td> <td>1</td> <td>1</td> <td>1</td> <td>1901048-1</td> <td>TAG, IDENTIFICATION</td> <td>67</td> </tr> <tr> <td>-</td> <td>2</td> <td>2</td> <td>2</td> <td>2</td> <td>21017-1</td> <td>SCREW, DRIVE</td> <td>66</td> </tr> <tr> <td>-</td> <td>1</td> <td>1</td> <td>1</td> <td>1</td> <td>18028-1</td> <td>WASHER, FLAT, REG M3</td> <td>64</td> </tr> <tr> <td>-</td> <td>1</td> <td>1</td> <td>1</td> <td>1</td> <td>1655785-9</td> <td>SCR, BTN SKT HD CAP (M3 X 6)</td> <td>62</td> </tr> <tr> <td>-</td> <td>2</td> <td>2</td> <td>2</td> <td>2</td> <td>1655785-1</td> <td>SCR, BTN SKT HD CAP (M4 X 8)</td> <td>60</td> </tr> <tr> <td>-</td> <td>1</td> <td>1</td> <td>1</td> <td>1</td> <td>985575-3</td> <td>SCR, FLT SKT HD CAP M3 X 10.0</td> <td>57</td> </tr> <tr> <td>-</td> <td>4</td> <td>4</td> <td>4</td> <td>4</td> <td>1655783-3</td> <td>SCR, CAP, SOC HD, LOW HEAD, M4 X 12</td> <td>54</td> </tr> <tr> <td>-</td> <td>1</td> <td>1</td> <td>1</td> <td>1</td> <td>1-18030-0</td> <td>NUT, HEX, REG M3.5</td> <td>52</td> </tr> <tr> <td>-</td> <td>1</td> <td>1</td> <td>1</td> <td>1</td> <td>1901681-1</td> <td>HOLDDOWN, TERMINAL</td> <td>51</td> </tr> <tr> <td>-</td> <td>1</td> <td>1</td> <td>1</td> <td>1</td> <td>2-1752354-1</td> <td>STANDOFF, HOLD-DOWN</td> <td>50</td> </tr> <tr> <td>-</td> <td>1</td> <td>1</td> <td>1</td> <td>1</td> <td>1752300-1</td> <td>SF SYSTEM III APPLICATOR</td> <td>46</td> </tr> <tr> <td>-</td> <td>1</td> <td>1</td> <td>1</td> <td>1</td> <td>1752308-1</td> <td>RAM</td> <td>44</td> </tr> <tr> <td>-</td> <td>1</td> <td>1</td> <td>1</td> <td>1</td> <td>2-1655785-3</td> <td>SCR, BTN SKT HD CAP (M8 X 25)</td> <td>41</td> </tr> <tr> <td>-</td> <td>1</td> <td>1</td> <td>1</td> <td>1</td> <td>993002-4</td> <td>SCREW, SET, SFT TIP</td> <td>40</td> </tr> <tr> <td>-</td> <td>1</td> <td>1</td> <td>1</td> <td>1</td> <td>1962043-1</td> <td>PLUNGER, BALL, METRIC</td> <td>39</td> </tr> <tr> <td>-</td> <td>1</td> <td>1</td> <td>1</td> <td>1</td> <td>1-1752356-3</td> <td>RING, INSULATION CRIMP</td> <td>38</td> </tr> <tr> <td>-</td> <td>1</td> <td>1</td> <td>1</td> <td>1</td> <td>1-1752356-3</td> <td>SUPPORT, TERMINAL</td> <td>34</td> </tr> <tr> <td>-</td> <td>2</td> <td>2</td> <td>2</td> <td>2</td> <td>3-1655785-3</td> <td>SCR, BTN SKT HD CAP (M4 X 20)</td> <td>33</td> </tr> <tr> <td>-</td> <td>1</td> <td>1</td> <td>1</td> <td>1</td> <td>18028-3</td> <td>WASHER, FLAT, REG M5</td> <td>32</td> </tr> <tr> <td>-</td> <td>1</td> <td>1</td> <td>1</td> <td>1</td> <td>5-1655316-3</td> <td>SCR, SKT HD CAP, M5 X 10.0</td> <td>31</td> </tr> <tr> <td>-</td> <td>1</td> <td>1</td> <td>1</td> <td>1</td> <td>1320908-8</td> <td>SPACER, STRIP GUIDE</td> <td>30</td> </tr> <tr> <td>-</td> <td>1</td> <td>1</td> <td>1</td> <td>1</td> <td>1901087-1</td> <td>ASSEMBLY, STRIP GUIDE</td> <td>29</td> </tr> <tr> <td>-</td> <td>1</td> <td>1</td> <td>1</td> <td>1</td> <td>1-455888-0</td> <td>SPACER, CRIMPER</td> <td>28</td> </tr> <tr> <td>-</td> <td>1</td> <td>1</td> <td>1</td> <td>1</td> <td>1320928-1</td> <td>PLATE, STRIP GUIDE</td> <td>24</td> </tr> <tr> <td>-</td> <td>1</td> <td>1</td> <td>1</td> <td>1</td> <td>1976045-1</td> <td>STRIPPER</td> <td>22</td> </tr> <tr> <td>-</td> <td>1</td> <td>1</td> <td>1</td> <td>1</td> <td>18028-2</td> <td>WASHER, FLAT, REG M4</td> <td>20</td> </tr> <tr> <td>-</td> <td>REF</td> <td>REF</td> <td>REF</td> <td>REF</td> <td>1752311-1</td> <td>STRIPPER</td> <td>19</td> </tr> <tr> <td>-</td> <td>1</td> <td>-</td> <td>1</td> <td>-</td> <td>1338684-2</td> <td>SHEAR HOLDER, FRONT</td> <td>13</td> </tr> <tr> <td>-</td> <td>1</td> <td>1</td> <td>1</td> <td>1</td> <td>3-22280-3</td> <td>SPRING, COMPRESSION</td> <td>12</td> </tr> <tr> <td>-</td> <td>1</td> <td>1</td> <td>1</td> <td>1</td> <td>356885-5</td> <td>STOP, SHEAR</td> <td>11</td> </tr> <tr> <td>-</td> <td>-</td> <td>1</td> <td>-</td> <td>1</td> <td>1-1320921-0</td> <td>SHEAR HOLDER, FRONT, CUT</td> <td>10</td> </tr> <tr> <td>-</td> <td>1</td> <td>1</td> <td>1</td> <td>1</td> <td>318707-2</td> <td>FLOATING SHEAR, FRONT</td> <td>9</td> </tr> <tr> <td>-</td> <td>1</td> <td>2</td> <td>2</td> <td>1</td> <td>2-1633131-9</td> <td>ANVIL, COMBINATION .080</td> <td>8</td> </tr> <tr> <td>-</td> <td>1</td> <td>1</td> <td>1</td> <td>1</td> <td>1338680-1</td> <td>DEPRESSOR, SHEAR</td> <td>5</td> </tr> <tr> <td>-</td> <td>1</td> <td>1</td> <td>1</td> <td>1</td> <td>3-238011-3</td> <td>BLOCK, CRIMPER SPACER</td> <td>4</td> </tr> <tr> <td>-</td> <td>1</td> <td>2</td> <td>2</td> <td>1</td> <td>1583690-9</td> <td>CRIMPER, INSUL O</td> <td>3</td> </tr> <tr> <td>-</td> <td>1</td> <td>1</td> <td>1</td> <td>1</td> <td>1-455888-8</td> <td>SPACER, CRIMPER</td> <td>2</td> </tr> <tr> <td>-</td> <td>1</td> <td>2</td> <td>2</td> <td>1</td> <td>2-456405-4</td> <td>CRIMPER, WIRE PREMIUM</td> <td>1</td> </tr> <tr> <td>-</td> <td>77</td> <td>76</td> <td>71</td> <td>-</td> <td>-</td> <td>PART NO</td> <td>ITEM NO</td> </tr> <tr> <td colspan="4"> <p>THIS DRAWING IS A CONTROLLED DOCUMENT AND IS THE PROPERTY OF TYCO ELECTRONICS CORPORATION. IT IS SUBJECT TO CHANGE AND THE CONTROLLER IS RESPONSIBLE FOR APPROVAL OF CHANGES.</p> </td> <td colspan="4"> <p>05JUN2007 M. CLIFFORD CHK</p> <p>Tyco Electronics Harrisburg, PA 17105-3608</p> <p>SIDE FEED SYSTEM III APPLICATOR</p> </td> </tr> <tr> <td colspan="4"> <p>ITEM NO. 00779 C-1911048</p> </td> <td colspan="4"> <p>NAME</p> </td> </tr> <tr> <td colspan="4"> <p>AM 4805 REV 31MAR2000</p> </td> <td colspan="4"> <p>SIZE CAGE CODE DRAWING NO. RESTRICTED TO</p> </td> </tr> <tr> <td colspan="4"> <p>Pro/ENGINEER DRAWING</p> </td> <td colspan="4"> <p>SCALE 3:5 SHEET 1 OF 1 REV A</p> </td> </tr> </table>				-	1	1	1	1	1-993111-6	PIN, SLOTTED SPRING 3.0 X 30.0	177	-	2	2	2	2	3-22280-7	SPRING, COMPRESSION	176	-	1	1	1	1	1752353-1	GUIDE PIN, HOLDDOWN	175	-	1	1	1	1	1901680-1	GUIDE PIN, HOLDDOWN	174	-	REF	REF	REF	REF	SEE TABLE	MEMORY CHIP, PROGRAMMED	135	-	1	1	1	1	1633565-1	DOCUMENTATION PACKAGE	71	-	1	1	1	1	1901048-1	TAG, IDENTIFICATION	67	-	2	2	2	2	21017-1	SCREW, DRIVE	66	-	1	1	1	1	18028-1	WASHER, FLAT, REG M3	64	-	1	1	1	1	1655785-9	SCR, BTN SKT HD CAP (M3 X 6)	62	-	2	2	2	2	1655785-1	SCR, BTN SKT HD CAP (M4 X 8)	60	-	1	1	1	1	985575-3	SCR, FLT SKT HD CAP M3 X 10.0	57	-	4	4	4	4	1655783-3	SCR, CAP, SOC HD, LOW HEAD, M4 X 12	54	-	1	1	1	1	1-18030-0	NUT, HEX, REG M3.5	52	-	1	1	1	1	1901681-1	HOLDDOWN, TERMINAL	51	-	1	1	1	1	2-1752354-1	STANDOFF, HOLD-DOWN	50	-	1	1	1	1	1752300-1	SF SYSTEM III APPLICATOR	46	-	1	1	1	1	1752308-1	RAM	44	-	1	1	1	1	2-1655785-3	SCR, BTN SKT HD CAP (M8 X 25)	41	-	1	1	1	1	993002-4	SCREW, SET, SFT TIP	40	-	1	1	1	1	1962043-1	PLUNGER, BALL, METRIC	39	-	1	1	1	1	1-1752356-3	RING, INSULATION CRIMP	38	-	1	1	1	1	1-1752356-3	SUPPORT, TERMINAL	34	-	2	2	2	2	3-1655785-3	SCR, BTN SKT HD CAP (M4 X 20)	33	-	1	1	1	1	18028-3	WASHER, FLAT, REG M5	32	-	1	1	1	1	5-1655316-3	SCR, SKT HD CAP, M5 X 10.0	31	-	1	1	1	1	1320908-8	SPACER, STRIP GUIDE	30	-	1	1	1	1	1901087-1	ASSEMBLY, STRIP GUIDE	29	-	1	1	1	1	1-455888-0	SPACER, CRIMPER	28	-	1	1	1	1	1320928-1	PLATE, STRIP GUIDE	24	-	1	1	1	1	1976045-1	STRIPPER	22	-	1	1	1	1	18028-2	WASHER, FLAT, REG M4	20	-	REF	REF	REF	REF	1752311-1	STRIPPER	19	-	1	-	1	-	1338684-2	SHEAR HOLDER, FRONT	13	-	1	1	1	1	3-22280-3	SPRING, COMPRESSION	12	-	1	1	1	1	356885-5	STOP, SHEAR	11	-	-	1	-	1	1-1320921-0	SHEAR HOLDER, FRONT, CUT	10	-	1	1	1	1	318707-2	FLOATING SHEAR, FRONT	9	-	1	2	2	1	2-1633131-9	ANVIL, COMBINATION .080	8	-	1	1	1	1	1338680-1	DEPRESSOR, SHEAR	5	-	1	1	1	1	3-238011-3	BLOCK, CRIMPER SPACER	4	-	1	2	2	1	1583690-9	CRIMPER, INSUL O	3	-	1	1	1	1	1-455888-8	SPACER, CRIMPER	2	-	1	2	2	1	2-456405-4	CRIMPER, WIRE PREMIUM	1	-	77	76	71	-	-	PART NO	ITEM NO	<p>THIS DRAWING IS A CONTROLLED DOCUMENT AND IS THE PROPERTY OF TYCO ELECTRONICS CORPORATION. IT IS SUBJECT TO CHANGE AND THE CONTROLLER IS RESPONSIBLE FOR APPROVAL OF CHANGES.</p>				<p>05JUN2007 M. CLIFFORD CHK</p> <p>Tyco Electronics Harrisburg, PA 17105-3608</p> <p>SIDE FEED SYSTEM III APPLICATOR</p>				<p>ITEM NO. 00779 C-1911048</p>				<p>NAME</p>				<p>AM 4805 REV 31MAR2000</p>				<p>SIZE CAGE CODE DRAWING NO. RESTRICTED TO</p>				<p>Pro/ENGINEER DRAWING</p>				<p>SCALE 3:5 SHEET 1 OF 1 REV A</p>			
-	1	1	1	1	1-993111-6	PIN, SLOTTED SPRING 3.0 X 30.0	177																																																																																																																																																																																																																																																																																																																																																																																																								
-	2	2	2	2	3-22280-7	SPRING, COMPRESSION	176																																																																																																																																																																																																																																																																																																																																																																																																								
-	1	1	1	1	1752353-1	GUIDE PIN, HOLDDOWN	175																																																																																																																																																																																																																																																																																																																																																																																																								
-	1	1	1	1	1901680-1	GUIDE PIN, HOLDDOWN	174																																																																																																																																																																																																																																																																																																																																																																																																								
-	REF	REF	REF	REF	SEE TABLE	MEMORY CHIP, PROGRAMMED	135																																																																																																																																																																																																																																																																																																																																																																																																								
-	1	1	1	1	1633565-1	DOCUMENTATION PACKAGE	71																																																																																																																																																																																																																																																																																																																																																																																																								
-	1	1	1	1	1901048-1	TAG, IDENTIFICATION	67																																																																																																																																																																																																																																																																																																																																																																																																								
-	2	2	2	2	21017-1	SCREW, DRIVE	66																																																																																																																																																																																																																																																																																																																																																																																																								
-	1	1	1	1	18028-1	WASHER, FLAT, REG M3	64																																																																																																																																																																																																																																																																																																																																																																																																								
-	1	1	1	1	1655785-9	SCR, BTN SKT HD CAP (M3 X 6)	62																																																																																																																																																																																																																																																																																																																																																																																																								
-	2	2	2	2	1655785-1	SCR, BTN SKT HD CAP (M4 X 8)	60																																																																																																																																																																																																																																																																																																																																																																																																								
-	1	1	1	1	985575-3	SCR, FLT SKT HD CAP M3 X 10.0	57																																																																																																																																																																																																																																																																																																																																																																																																								
-	4	4	4	4	1655783-3	SCR, CAP, SOC HD, LOW HEAD, M4 X 12	54																																																																																																																																																																																																																																																																																																																																																																																																								
-	1	1	1	1	1-18030-0	NUT, HEX, REG M3.5	52																																																																																																																																																																																																																																																																																																																																																																																																								
-	1	1	1	1	1901681-1	HOLDDOWN, TERMINAL	51																																																																																																																																																																																																																																																																																																																																																																																																								
-	1	1	1	1	2-1752354-1	STANDOFF, HOLD-DOWN	50																																																																																																																																																																																																																																																																																																																																																																																																								
-	1	1	1	1	1752300-1	SF SYSTEM III APPLICATOR	46																																																																																																																																																																																																																																																																																																																																																																																																								
-	1	1	1	1	1752308-1	RAM	44																																																																																																																																																																																																																																																																																																																																																																																																								
-	1	1	1	1	2-1655785-3	SCR, BTN SKT HD CAP (M8 X 25)	41																																																																																																																																																																																																																																																																																																																																																																																																								
-	1	1	1	1	993002-4	SCREW, SET, SFT TIP	40																																																																																																																																																																																																																																																																																																																																																																																																								
-	1	1	1	1	1962043-1	PLUNGER, BALL, METRIC	39																																																																																																																																																																																																																																																																																																																																																																																																								
-	1	1	1	1	1-1752356-3	RING, INSULATION CRIMP	38																																																																																																																																																																																																																																																																																																																																																																																																								
-	1	1	1	1	1-1752356-3	SUPPORT, TERMINAL	34																																																																																																																																																																																																																																																																																																																																																																																																								
-	2	2	2	2	3-1655785-3	SCR, BTN SKT HD CAP (M4 X 20)	33																																																																																																																																																																																																																																																																																																																																																																																																								
-	1	1	1	1	18028-3	WASHER, FLAT, REG M5	32																																																																																																																																																																																																																																																																																																																																																																																																								
-	1	1	1	1	5-1655316-3	SCR, SKT HD CAP, M5 X 10.0	31																																																																																																																																																																																																																																																																																																																																																																																																								
-	1	1	1	1	1320908-8	SPACER, STRIP GUIDE	30																																																																																																																																																																																																																																																																																																																																																																																																								
-	1	1	1	1	1901087-1	ASSEMBLY, STRIP GUIDE	29																																																																																																																																																																																																																																																																																																																																																																																																								
-	1	1	1	1	1-455888-0	SPACER, CRIMPER	28																																																																																																																																																																																																																																																																																																																																																																																																								
-	1	1	1	1	1320928-1	PLATE, STRIP GUIDE	24																																																																																																																																																																																																																																																																																																																																																																																																								
-	1	1	1	1	1976045-1	STRIPPER	22																																																																																																																																																																																																																																																																																																																																																																																																								
-	1	1	1	1	18028-2	WASHER, FLAT, REG M4	20																																																																																																																																																																																																																																																																																																																																																																																																								
-	REF	REF	REF	REF	1752311-1	STRIPPER	19																																																																																																																																																																																																																																																																																																																																																																																																								
-	1	-	1	-	1338684-2	SHEAR HOLDER, FRONT	13																																																																																																																																																																																																																																																																																																																																																																																																								
-	1	1	1	1	3-22280-3	SPRING, COMPRESSION	12																																																																																																																																																																																																																																																																																																																																																																																																								
-	1	1	1	1	356885-5	STOP, SHEAR	11																																																																																																																																																																																																																																																																																																																																																																																																								
-	-	1	-	1	1-1320921-0	SHEAR HOLDER, FRONT, CUT	10																																																																																																																																																																																																																																																																																																																																																																																																								
-	1	1	1	1	318707-2	FLOATING SHEAR, FRONT	9																																																																																																																																																																																																																																																																																																																																																																																																								
-	1	2	2	1	2-1633131-9	ANVIL, COMBINATION .080	8																																																																																																																																																																																																																																																																																																																																																																																																								
-	1	1	1	1	1338680-1	DEPRESSOR, SHEAR	5																																																																																																																																																																																																																																																																																																																																																																																																								
-	1	1	1	1	3-238011-3	BLOCK, CRIMPER SPACER	4																																																																																																																																																																																																																																																																																																																																																																																																								
-	1	2	2	1	1583690-9	CRIMPER, INSUL O	3																																																																																																																																																																																																																																																																																																																																																																																																								
-	1	1	1	1	1-455888-8	SPACER, CRIMPER	2																																																																																																																																																																																																																																																																																																																																																																																																								
-	1	2	2	1	2-456405-4	CRIMPER, WIRE PREMIUM	1																																																																																																																																																																																																																																																																																																																																																																																																								
-	77	76	71	-	-	PART NO	ITEM NO																																																																																																																																																																																																																																																																																																																																																																																																								
<p>THIS DRAWING IS A CONTROLLED DOCUMENT AND IS THE PROPERTY OF TYCO ELECTRONICS CORPORATION. IT IS SUBJECT TO CHANGE AND THE CONTROLLER IS RESPONSIBLE FOR APPROVAL OF CHANGES.</p>				<p>05JUN2007 M. CLIFFORD CHK</p> <p>Tyco Electronics Harrisburg, PA 17105-3608</p> <p>SIDE FEED SYSTEM III APPLICATOR</p>																																																																																																																																																																																																																																																																																																																																																																																																											
<p>ITEM NO. 00779 C-1911048</p>				<p>NAME</p>																																																																																																																																																																																																																																																																																																																																																																																																											
<p>AM 4805 REV 31MAR2000</p>				<p>SIZE CAGE CODE DRAWING NO. RESTRICTED TO</p>																																																																																																																																																																																																																																																																																																																																																																																																											
<p>Pro/ENGINEER DRAWING</p>				<p>SCALE 3:5 SHEET 1 OF 1 REV A</p>																																																																																																																																																																																																																																																																																																																																																																																																											

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1911048-6](#)