





Detail
Scale 5:1



Function Chart




TE PN	Part			
3-6437630-5	F4TN0904	ON	NONE	ON
3-6437630-6	F4TPA0904	ON	ON	ON

NONE: no mechanical position


Date Code Printing
last digit of year
A-L = January to December
Day

Printing of
Logo and Rating


ALCO
F4TN0904
6A AC 250V
ON - ON
SW. Funct.



Panel Cutout



Panel Cutout
using Ring




Nut




1,5 thick

Ring



1 thick

L washer



0.63 thick

Notes:

Operating temperature -20°C to +70°C

All materials and finishes comply with RoHS directive

Materials Chart

1	Case	Polyester Resin	
2	F Contact	99.98% silver + C3602BD	Ep-Cu/Ni3,AuFb
3	Common	C3602BD	Ep-Cu/Ni3,AuFb
4	Frame	SUS	
5	Bushing	C3602BD	Ep-Cu/Ni3b
6	Actuator	C3602BD	Ep-Cu/Ni3,Cr1b
7	Nut	C3602BD	Ep-Cu/Ni3b
8	Ring	SPCC	Ep-Fe/Cu2,Ni3b
9	L washer	SK-5	Ep-Fe/Cu2,Ni4b

Specifications

TE PN	Part	Rating	Initial Contact Resistance	Insulation Resistance	Dielectric Strength	Endurance
3-6437630-5	F4TN0904	AC 125V 6A	MAX 10 milliohms at DC 2 ~ 4V 1A	MIN 1000 M Ohms at DC 500V	AC 1kV/1 min (rated load resistive) mechanically 50,000 cycles at 20 cycles/min	
3-6437630-6	F4TPA0904	AC 250V 6A				

REPLACEMENT FOR: DWG LOC NO: IF SHEET: 1 OF 1 REVISION: A A 2

THIS DRAWING IS A CONTROLLED DOCUMENT. HANDWRITTEN CHANGES ARE NOT ALLOWED

SCALE: NAME: DWG NO: **C=1968517**

Toggle Switch quad. pole
Standard Lever

Customer Drawing

ECR-NO: DATE NAME INFO DATE NAME

DEPARTMENT: D&E
DRAWER: 03.01.2007 SA008713
CHECKED: APPROVED: **Tyco Electronics**

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[F4TN0904](#)