

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A5	REVISED PER ECO-16-018632	05APR2017	SK	PO

SPECIFICATIONS:

MATERIALS:
CASE, PPS, UL94 V-0, BROWN
ACTUATOR, NYLON, UL94V-0, SEE P/N TABLE FOR FINISH
COVER, STEEL, TIN FINISH
TERMINAL/FIXED CONTACT, COPPER ALLOY-SILVER FINISH
MOVING CONTACT, STAINLESS STEEL-SILVER FINISH

ELECTRICAL:
MAX CONTACT RATING, 50MILLIAMP@24V DC
MIN CONTACT RATING, 1MICROAMP@1V DC
CONTACT RESISTANCE, 100 MILLIOHMS MAX
INSULATION RESISTANCE, 100 MEGOHM MIN.
DIELECTRIC STRENGTH, 500 V AC FOR 1 MINUTE
LIFE EXPECTANCY, 1,000,000 CYCLES


MECHANICAL:
ACTUATION FORCE, SEE P/N TABLE
ACTUATION TRAVEL, 0.25 +0.20/-0.10
LIFE EXPECTANCY, 1,000,000,
(2 CYCLES PER SECOND AND 150% ACTUATION FORCE)

ENVIRONMENTAL:
OPERATING TEMPERATURE, -40 TO +105° C
STORAGE TEMPERATURE, -40 TO +105° C
SOLDERABILITY, EIA-RS-186-9E, OR MIL-STD-202F
RESISTANCE TO SOLDER HEAT, 260° C FOR 10SEC-PER 109-201, COND B
1. NO CHANGE IN INITIAL ELECTRICAL AND MECHANICAL CHARACTERISTICS

NOTES:

- 1 TAPE AND REEL PACKAGING PER EIA 481.
- 2 ALL MATERIALS AND FINISHES SHALL COMPLY WITH EU DIRECTIVE 2002/95/EC OF 27JAN2003 (ROHS)

()-INDICATES MOMENTARY POSITION		
CIRCUIT CHARACTERISTICS		
CONTACT POSITION	CIRCUIT DIAGRAM	
OFF	(ON) 1 - 3 2 - 4	



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M.BINNER	07NOV2007	TE Connectivity		
DIMENSIONS: mm [INCHES]		CHK M.SARVER	07NOV07			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD M.SARVER	07NOV07	NAME MICRO MINIATURE PUSHBUTTON SWITCH FSM JSM		
0 PLC $\pm$ - 1 PLC $\pm$ - 2 PLC $\pm$ 0.30 [.012] 3 PLC $\pm$ - 4 PLC $\pm$ - ANGLES $\pm$ 1°		PRODUCT SPEC -	APPLICATION SPEC -			
MATERIAL -		FINISH -	WEIGHT 0	SIZE A2	CAGE CODE 00779	DRAWING NO C=1977223
CUSTOMER DRAWING				SCALE 8:1	SHEET 1 of 2	REV A5

[illegible]

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2-1977223-3](#)