



Leaded Magnetics Packaging Methods

REEL PACK



TAPE AND REEL in inches [millimeters]											
MODEL	PREVIOUS CODE	GLOBAL CODE LEAD (Pb)-BEARING	GLOBAL CODE LEAD (Pb)-FREE	REEL SIZE	CARRIER TAPE WIDTH (W)	COMPONENT PITCH (P)	UNITS/ REEL	PREVIOUS CODE	GLOBAL CODE LEAD (Pb)-BEARING	GLOBAL CODE LEAD (Pb)-FREE	UNITS/ BULK
IRF-24	-	-	ER	12	2.06 [52.39]	0.2 [5.08]	5000	-	-	-	-
IRF-36	-	-	ER	12	2.06 [52.39]	0.2 [5.08]	5000	-	-	-	-
IRF-46	-	-	ER	12	2.06 [52.39]	0.2 [5.08]	3000	-	-	-	-
IHD-1	R16	RR	ER	12	2.06 [52.39]	0.4 [10.16]	800	B08	BH	EB	50
IHD-3	RA3	AC	ER	12	2.87 [72.90]	0.6 [15.24]	200	B08	BH	EB	190
IHD-2	-	-	-	-	-	-	-	-	-	EB	150
IHD-4	-	-	-	-	-	-	-	-	-	EB	60
IHA-101	-	-	-	-	-	-	-	B01	BA	EB	210
IHA-102	-	-	-	-	-	-	-	B01	BA	EB	210
IHA-103	-	-	-	-	-	-	-	B01	BA	EB	200
IHA-104	-	-	-	-	-	-	-	B01	BA	EB	160
IHA-105	-	-	-	-	-	-	-	B01	BA	EB	160
IHA-201	-	-	-	-	-	-	-	B01	BA	EB	200
IHA-202	-	-	-	-	-	-	-	B01	BA	EB	180
IHA-203	-	-	-	-	-	-	-	B01	BA	EB	160
IHA-204	-	-	-	-	-	-	-	B01	BA	EB	120
IHA-205	-	-	-	-	-	-	-	B01	BA	EB	75
IHA-301	-	-	-	-	-	-	-	B01	BA	EB	210
IHA-302	-	-	-	-	-	-	-	B01	BA	EB	240
IHA-303	-	-	-	-	-	-	-	B01	BA	EB	160
IHA-304	-	-	-	-	-	-	-	B01	BA	EB	160
IHA-305	-	-	-	-	-	-	-	B01	BA	EB	160
IHA-501	-	-	-	-	-	-	-	B01	BA	EB	210
IHA-502	-	-	-	-	-	-	-	B01	BA	EB	200
IHA-503	-	-	-	-	-	-	-	B01	BA	EB	75
IHA-504	-	-	-	-	-	-	-	B01	BA	EB	75
IHA-505	-	-	-	-	-	-	-	B01	BA	EB	75
IHTH-0750IZ	-	-	-	-	-	-	-	-	-	EB	100
IHTH-1125KZ	-	-	-	-	-	-	-	-	-	EB	50
IHTH-1500MZ	-	-	-	-	-	-	-	-	-	EB	25
IHTH-1500TZ	-	-	-	-	-	-	-	-	-	EB	25
IHXL-1500VZ	-	-	-	-	-	-	-	-	-	EB	100
IHXL-2000VZ	-	-	-	-	-	-	-	-	-	EB	50
IH-3 5 μ H, 27 μ H, 50 μ H, 100 μ H	-	-	-	-	-	-	-	B15	BQ	EB	150
IH-3 10 μ H	-	-	-	-	-	-	-	B15	BQ	EB	200
IH-3 150 μ H	-	-	-	-	-	-	-	B15	BQ	EB	50
IH-3 250 μ H	-	-	-	-	-	-	-	B15	BQ	EB	75
IH-4 0 μ H	-	-	-	-	-	-	-	B15	BQ	EB	160



TAPE AND REEL in inches [millimeters]											
MODEL	PREVIOUS CODE	GLOBAL CODE LEAD (Pb)-BEARING	GLOBAL CODE LEAD (Pb)-FREE	REEL SIZE	CARRIER TAPE WIDTH (W)	COMPONENT PITCH (P)	UNITS/ REEL	PREVIOUS CODE	GLOBAL CODE LEAD (Pb)-BEARING	GLOBAL CODE LEAD (Pb)-FREE	UNITS/ BULK
IH-5 5 μ H, 10 μ H	-	-	-	-	-	-	-	B15	BQ	EB	200
IH-5 27 μ H	-	-	-	-	-	-	-	B15	BQ	EB	150
IH-5 50 μ H, 68 μ H, 100 μ H, 150 μ H	-	-	-	-	-	-	-	B15	BQ	EB	50
IH-10 5 μ H, 10 μ H	-	-	-	-	-	-	-	B15	BQ	EB	150
IH-10 27 μ H	-	-	-	-	-	-	-	B15	BQ	EB	50
IH-10 50 μ H, 68 μ H, 100 μ H	-	-	-	-	-	-	-	B15	BQ	EB	75
IH-15 5 μ H	-	-	-	-	-	-	-	B15	BQ	EB	50
IH-15 10 μ H, 27 μ H	-	-	-	-	-	-	-	B15	BQ	EB	75
IH-15 50 μ H	-	-	-	-	-	-	-	B15	BQ	EB	60
IHM-2	-	-	-	-	-	-	-	P12	PM	EB	20
IHB-1	-	-	-	-	-	-	-	B40	BV	EB	48
IHB-2	-	-	-	-	-	-	-	B40	BV	EB	30
IHB-3	-	-	-	-	-	-	-	B40	BV	EB	20
IHB-4	-	-	-	-	-	-	-	B40	BV	EB	16
IHB-5	-	-	-	-	-	-	-	B40	BV	EB	16
IHB-6	-	-	-	-	-	-	-	B40	BV	EB	16
IHV-15-500	-	-	-	-	-	-	-	B48	BZ	EB	10
IHV-20-200	-	-	-	-	-	-	-	B48	BZ	EB	10
IHV-28-60	-	-	-	-	-	-	-	B48	BZ	EB	14
IHV-30-150	-	-	-	-	-	-	-	B48	BZ	EB	5
IHV-40-39	-	-	-	-	-	-	-	B48	BZ	EB	10
IHV-45-92	-	-	-	-	-	-	-	B48	BZ	EB	5
IHV-50-50	-	-	-	-	-	-	-	B48	BZ	EB	5
IHV-60-24	-	-	-	-	-	-	-	B48	BZ	EB	5
TJ3-1U	-	-	-	-	-	-	-	T07	TG	EB	260
TJ3-2U	-	-	-	-	-	-	-	T07	TG	EB	169
TJ3-1U-HT	-	-	-	-	-	-	-	-	-	EB	260
TJ3-2U-HT	-	-	-	-	-	-	-	-	-	EB	169
TJ4-1U	-	-	-	-	-	-	-	T07	TG	EB	220
TJ4-2U	-	-	-	-	-	-	-	T07	TG	EB	121
TJ5-1U	-	-	-	-	-	-	-	T07	TG	EB	170
TJ5-2U	-	-	-	-	-	-	-	T07	TG	EB	100
TJ5-1U-HT	-	-	-	-	-	-	-	-	-	EB	170
TJ5-2U-HT	-	-	-	-	-	-	-	-	-	EB	100
TJ6-1U	-	-	-	-	-	-	-	T07	TG	EB	70
TJ6-2U	-	-	-	-	-	-	-	T07	TG	EB	49
TJ7-1U	-	-	-	-	-	-	-	T07	TG	EB	66
TJ7-2U	-	-	-	-	-	-	-	T07	TG	EB	30
TJ8-1U	-	-	-	-	-	-	-	T07	TG	EB	28
TJ8-2U	-	-	-	-	-	-	-	T07	TG	EB	16
TJ9-1U	-	-	-	-	-	-	-	T07	TG	EB	18
TJ9-2U	-	-	-	-	-	-	-	T07	TG	EB	9
IWAS-4832FF	-	-	-	-	-	-	-	-	-	EB	100
IWAS-4832EC	-	-	-	-	-	-	-	-	-	EB	100
IHDM1008	-	-	-	-	-	-	-	-	-	EV	270
IHDM1107	-	-	-	-	-	-	-	-	-	EV	240
IHDF1300	-	-	-	-	-	-	-	-	-	EH	240



MILITARY PART ORDERING EXAMPLES				
TRANSFORMERS AND INDUCTORS				
MIL-T-27E (Basic [TF]) (Established Reliability - None)				
M27	215	05	= Dale Type TE-3Q0TR 1.0 mH 2 %	
1	2	3		
MIL-C-15305E (Basic [LT]) (Established Reliability MIL-C-39010)			Note: Parts will be color banded. Value per military standard dash number.	
LT	4	K	= Dale Type IM-2 0.10 μ H to 1.00 μ H 10 %	
1	2	3		
			1. Military specification 2. Specification sheet number 3. Specification sheet dash number indicating value and electrical ratings	
			1. Style 2. Grade and class 3. Family K = Coil, radio frequency, fixed	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Vishay:

[IR04BH220K](#) [IR04BH270K](#) [IR04RU101J](#) [IR04BH122J](#) [IR02BH2R0H](#) [IR02BH5R1H](#) [IR02BHR22K](#) [IR02BHR47K](#)
[IR02BH6R8K](#) [IR04BH680J](#) [IR02BH560K](#) [IR02BH120K](#) [IR02BH100K](#) [IR02RU330K](#) [IR02BH101K](#) [IR02BH8R2K](#)
[IR04BH8R2K](#) [IR04BHR68K](#) [IR02RU4R7K](#) [IR04RU4R7K](#) [IR04BH330K](#) [IR02BHR33H](#) [IR04BH180K](#) [IR02BH4R3H](#)
[IR02BH5R6K](#) [IR02RU100K](#) [IR02BH102K](#) [IR02EV100K](#) [IR02EV330K](#) [IR02EB101K](#) [IR04BH1R0K](#) [IR2 .22 10%](#)
[IR02ER100J](#) [IR02EV100J](#) [IR02BHR10K](#) [IR02SH5R6J](#) [IR02ER8R2J](#) [IR04BH390J](#) [IR04BH560J](#) [IR02BH180K](#)
[IR02BH1R0K](#) [IR02BH560H](#) [IR02RUR10K](#) [IR04BHR22M](#) [IR02BH3R3K](#) [IR02BH3R9K](#) [IR04BHR15M](#) [IR02BH2R7K](#)
[IR04BHR22K](#) [IR02BH2R2K](#) [IR02BHR12K](#) [IR02BH270K](#) [IR02BH220K](#) [IR02BH470K](#) [IR02BH5R6J](#) [IR02BH5R1J](#)
[IR02BH1R8K](#) [IR02BH1R5K](#) [IR02BH1R2K](#) [IR04BH111J](#) [IR04BH101J](#) [IR02BH1R2J](#) [IR04BH151J](#) [IR04BH100K](#)
[IR04BH102J](#) [IR02BHR15K](#) [IR02BHR39K](#) [IR04BH5R6K](#) [IR02BH330K](#) [IR04BH221J](#) [IR2 .56 10%](#) [IR2 180 10%](#) [IR2](#)
[1K 10%](#) [IR2 4.7 10%](#) [IR2 5.6 10%TR](#) [IR04EB100K](#) [IR2 2.2 10%](#) [IR02EB220K](#) [IR02ER5R6J](#) [IR02BH181K](#)
[IR02BHR56K](#) [IR02SH5R6K](#) [IR02BH4R7K](#) [IHTH1500TZEB6R8M5A](#)