

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

2005

© COPYRIGHT 2005

ALL RIGHTS RESERVED.

LOC  
ALDIST  
2

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	J5	REVISED PER ECR-16-008286	25JUL2016	BW	RS

NOTES:

Bemerkungen:

	2-6µm Sn OVER Ni IN CRIMP-AREA 2-6µm Sn über Ni in der Crimpzone
	0.8µm Au OVER Ni IN CONTACT-AREA 0.8µm Au über Ni in der Kontaktzone
3	SUITABLE FOR Ø1.0-2.5mm Für Isolations Ø1.0-2.5mm geeignet
	0.8µm Au OVER 1.3µm Ni ON INSIDE OF WIRE BARREL AND CONTACT AREA 0.8µm Au über 1.3µm Ni in der Drahtcrimp und Kontaktzonen, sonst 1.3µm Ni

SUPERSEDED BY 350851-7	926895-7	926884-7	BRASS	
SUPERSEDED BY 350851-7	926895-6	926884-6	PHOS BRONZE	
	926895-3	926884-3	PHOS BRONZE	PRE-TIN
OBSOLETE	926895-2	926884-2	BRASS	
	926895-1	926884-1	BRASS	PRE-TIN
	LOOSE PIECE	PART NO.	MATERIAL	FINISH

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. Skoda	07NOV2005	TE Connectivity	
DIMENSIONS: mm		CHK R. Vlcek	-		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD -	-	NAME UNIVERSAL MNL SOCKET 0.2-0.8 mm <sup>2</sup> WIRE RANGE	
0 PLC ±0.2		PRODUCT SPEC 108-1031	-	SIZE A3	
1 PLC ±0.2		APPLICATION SPEC 114-18011	-	CAGE CODE 00779	DRAWING NO 926884
2 PLC ±0.2		WEIGHT -	-	RESTRICTED TO -	
3 PLC ±		CUSTOMER DRAWING	-	SCALE 5:1	SHEET 1
4 PLC ±				OF 1	REV J5
ANGLES ±°					
FINISH SEE TABLE					

1470-19 (3/11)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[926884-3](#)