### RS1A, RS1B, RS1D, RS1G, RS1J, RS1K

Vishay General Semiconductor

COMPLIANT

HALOGEN

**FREE** 

## **Surface Mount Fast Switching Rectifier**



**SMA (DO-214AC)** 

#### **DESIGN SUPPORT TOOLS**

click logo to get started



PRIMARY CHARACTERISTICS							
I <sub>F(AV)</sub>	1.0 A						
V <sub>RRM</sub>	50 V, 100 V, 200 V, 400 V, 600 V, 800 V						
I <sub>FSM</sub>	30 A						
t <sub>rr</sub>	150 ns, 250 ns, 500 ns						
V <sub>F</sub>	1.3 V						
T <sub>J</sub> max.	150 °C						
Package	SMA (DO-214AC)						
Circuit configuration	Single						

#### **FEATURES**

- Low profile package
- Ideal for automated placement
- · Glass passivated pellet chip junction
- Fast switching for high efficiency
- · High forward surge capability
- Meets MSL level 1, per J-STD-020, LF maximum peak of 260 °C
- AEC-Q101 qualified available
  - Automotive ordering code: base P/NHE3 or P/NHM3
- Material categorization: for definitions of compliance please see <a href="https://www.vishay.com/doc?99912"><u>www.vishay.com/doc?99912</u></a>

### **TYPICAL APPLICATIONS**

For use in fast switching rectification of power supply, inverters, converters, and freewheeling diodes for consumer, automotive and telecommunication.

### **MECHANICAL DATA**

Case: SMA (DO-214AC)

Molding compound meets UL 94 V-0 flammability rating Base P/N-E3 - RoHS-compliant, commercial grade

Base P/N-M3 - halogen-free, RoHS-compliant, commercial grade

Base P/NHE3\_X - RoHS-compliant and AEC-Q101 qualified Base P/NHM3\_X - halogen-free, RoHS-compliant and AEC-Q101 qualified

("\_X" denotes revision code e.g. A, B, ....)

**Terminals:** matte tin plated leads, solderable per J-STD-002 and JESD 22-B102

E3, M3, HE3 and HM3 suffix meets JESD 201 class 2 whisker test

Polarity: color band denotes cathode end

<b>MAXIMUM RATINGS</b> (T <sub>A</sub> = 25 °C unless otherwise noted)								
PARAMETER	SYMBOL	RS1A	RS1B	RS1D	RS1G	RS1J	RS1K	UNIT
Device marking code		RA	RB	RD	RG	RJ	RK	
Maximum repetitive peak reverse voltage	$V_{RRM}$	50	100	200	400	600	800	V
Maximum RMS voltage	$V_{RMS}$	35	70	140	280	420	500	V
Maximum DC blocking voltage	$V_{DC}$	50	100	200	400	600	800	V
Maximum average forward rectified current at $T_L = 90  ^{\circ}\text{C}$	I <sub>F(AV)</sub>	1.0					Α	
Peak forward surge current 8.3 ms single half sine-wave superimposed on rated load	I <sub>FSM</sub>	30					Α	
Operating junction and storage temperature range	T <sub>J</sub> , T <sub>STG</sub>	-55 to +150						°C

# RS1A, RS1B, RS1D, RS1G, RS1J, RS1K

### Vishay General Semiconductor

<b>ELECTRICAL CHARACTERISTICS</b> (T <sub>A</sub> = 25 °C unless otherwise noted)										
PARAMETER	TEST CONDITIONS		SYMBOL	RS1A	RS1B	RS1D	RS1G	RS1J	RS1K	UNIT
Maximum instantaneous forward voltage	1.0 A		V <sub>F</sub> 1.3					V		
Maximum DC reverse current at		T <sub>A</sub> = 25 °C	1_	5.0						μA
rated DC blocking voltage		T <sub>A</sub> = 125 °C	I IR	50					μΛ	
Maximum reverse recovery time	$I_F = 0.5$ $I_{rr} = 0.2$	A, I <sub>R</sub> = 1.0 A, 5 A	t <sub>rr</sub>	150			250	500	ns	
Typical junction capacitance	4.0 V, 1 MHz		CJ	10			7	pF		

THERMAL CHARACTERISTICS (T <sub>A</sub> = 25 °C unless otherwise noted)								
PARAMETER	SYMBOL RS1A RS1B RS1D RS1G RS1J RS1K UNIT						UNIT	
Typical thermal resistance	R <sub>0JA</sub> (1)	105						°C/W
Typical thermal resistance	R <sub>0</sub> JL (1)	32						C/VV


#### Note


<sup>(1)</sup> Thermal resistance from junction to ambient and from junction to lead mounted on PCB with 0.2" x 0.2" (5.0 mm x 5.0 mm) copper pad areas

ORDERING INFORMATION (Example)									
PREFERRED P/N	UNIT WEIGHT (g)	PREFERRED PACKAGE CODE	BASE QUANTITY	DELIVERY MODE					
RS1J-E3/61T	0.064	61T	1800	7" diameter plastic tape and reel					
RS1J-E3/5AT	0.064	5AT	7500	13" diameter plastic tape and reel					
RS1JHE3_A/H (1)	0.064	Н	1800	7" diameter plastic tape and reel					
RS1JHE3_A/I (1)	0.064	I	7500	13" diameter plastic tape and reel					
RS1J-M3/61T	0.064	61T	1800	7" diameter plastic tape and reel					
RS1J-M3/5AT	0.064	5AT	7500	13" diameter plastic tape and reel					
RS1JHM3_A/H (1)	0.064	Н	1800	7" diameter plastic tape and reel					
RS1JHM3_A/I (1)	0.064	I	7500	13" diameter plastic tape and reel					

### Note

## **RATINGS AND CHARACTERISTICS CURVES** ( $T_A = 25~^{\circ}\text{C}$ unless otherwise noted)








Fig. 2 - Maximum Non-Repetitive Peak Forward Surge Current

<sup>(1)</sup> AEC-Q101 qualified

## Vishay General Semiconductor




Fig. 3 - Typical Instantaneous Forward Characteristics




Fig. 4 - Typical Reverse Characteristics




Fig. 5 - Typical Junction Capacitance





Fig. 6 - Typical Transient Thermal Impedance

### **PACKAGE OUTLINE DIMENSIONS** in inches (millimeters)

### SMA (DO-214AC)





### **Legal Disclaimer Notice**

Vishay

### **Disclaimer**

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

# **Mouser Electronics**

**Authorized Distributor** 

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

### Vishay:

RS1A/11T RS1A/5AT RS1A/61T RS1A/63T RS1A-E3/63T RS1B/11T RS1B/5AT RS1B/61T RS1B/63T RS1B-E3/63T RS1BHE3/63T RS1D/5AT RS1D/61T RS1G/2GT RS1G/5AT RS1G/61T RS1G/63T RS1GHE3/2GT RS1GHE3/63T RS1J/2GT RS1J/5AT RS1JHE3/63T RS1K/13T RS1K/2GT RS1K/2GT RS1K/63T RS1K-E3/2GT RS1K-E3/63T RS1KHE3/2GT RS1KHE