

		<table><tr><th colspan="4">REVISIONS</th></tr><tr><th>REV</th><th>DESCRIPTION</th><th>DATE</th><th>APPROVED</th></tr><tr><td>03<sub>0</sub></td><td>REVISED</td><td>12/07/94</td><td><i>AD</i></td></tr></table>				REVISIONS				REV	DESCRIPTION	DATE	APPROVED	03 <sub>0</sub>	REVISED	12/07/94	<i>AD</i>																																																								
		REVISIONS																																																																							
		REV	DESCRIPTION	DATE	APPROVED																																																																				
03 <sub>0</sub>	REVISED	12/07/94	<i>AD</i>																																																																						
<table><tr><th>ELECTRICAL</th><th>MECHANICAL</th><th>ENVIRONMENTAL</th></tr><tr><td>Nominal Impedance (Ohms) <u>50</u></td><td>Force to Engage (Lbs MAX) <u>15</u></td><td>Temperature Rating <u>-65°C To +125°C</u></td></tr><tr><td>Frequency Range (GHz) DC to <u>26.5</u></td><td>Disengage (Lbs MIN) <u>2.0</u></td><td>Vibration MIL-STD-202, Method 204, Condition D</td></tr><tr><td>Volt Rating (VRMS MAX) @ Sea Level <u>250</u></td><td>Center Contact Retention <u>1.5 Lbs MIN</u></td><td>Thermal Shock MIL-STD-202, Method 107, Condition B,</td></tr><tr><td>VSWR <u>1.25 MAX</u> @ 26.5 GHz</td><td>Durability <u>100 cycles</u></td><td>Corrosion - MIL-STD-202, Method 101, Condition B</td></tr><tr><td>Insertion Loss <u>.12f GHz dB MIN</u></td><td></td><td></td></tr><tr><td>Corona, 70,000 Ft (VRMS MIN) <u>190</u></td><td></td><td></td></tr><tr><td>Dielectric Withstanding Voltage (VRMS MIN) @ Sea Level <u>500</u></td><td></td><td></td></tr><tr><td>Contact Resistance (Milliohms MAX) Center Contact <u>6.0</u> Outer Contact <u>2.0</u> Cable to Housing <u>0.5</u></td><td>DESIGNED FOR USE WITH <u>.085 DIA S.R.</u></td><td></td></tr><tr><td>RF High Potential @ Sea Level (VRMS MIN @ 5 MHz) <u>325</u></td><td>CABLE ENTRY DIAMETER MINIMUM HOUSING <u>.089</u></td><td></td></tr><tr><td>IR.(Megohms MIN) <u>5000</u></td><td></td><td></td></tr></table>	ELECTRICAL	MECHANICAL	ENVIRONMENTAL	Nominal Impedance (Ohms) <u>50</u>	Force to Engage (Lbs MAX) <u>15</u>	Temperature Rating <u>-65°C To +125°C</u>	Frequency Range (GHz) DC to <u>26.5</u>	Disengage (Lbs MIN) <u>2.0</u>	Vibration MIL-STD-202, Method 204, Condition D	Volt Rating (VRMS MAX) @ Sea Level <u>250</u>	Center Contact Retention <u>1.5 Lbs MIN</u>	Thermal Shock MIL-STD-202, Method 107, Condition B,	VSWR <u>1.25 MAX</u> @ 26.5 GHz	Durability <u>100 cycles</u>	Corrosion - MIL-STD-202, Method 101, Condition B	Insertion Loss <u>.12f GHz dB MIN</u>			Corona, 70,000 Ft (VRMS MIN) <u>190</u>			Dielectric Withstanding Voltage (VRMS MIN) @ Sea Level <u>500</u>			Contact Resistance (Milliohms MAX) Center Contact <u>6.0</u> Outer Contact <u>2.0</u> Cable to Housing <u>0.5</u>	DESIGNED FOR USE WITH <u>.085 DIA S.R.</u>		RF High Potential @ Sea Level (VRMS MIN @ 5 MHz) <u>325</u>	CABLE ENTRY DIAMETER MINIMUM HOUSING <u>.089</u>		IR.(Megohms MIN) <u>5000</u>			<table><tr><th>HOUSING</th><th>COMPONENT</th><th>MATERIAL</th><th>FINISH</th></tr><tr><td>BERYLLIUM COPPER PER ASTM-B-196, ALLOY C17300, CONDITION H</td><td>DIELECTRIC</td><td>PTFE FLUOROCARBON PER ASTM-D-1457</td><td>GOLD PLATE PER MIL-G-45204</td></tr><tr><td>CENTER CONTACT CONTACT FINGER ANTI-ROCK RING EMI RING</td><td></td><td>BERYLLIUM COPPER PER ASTM B 196, ALLOY C17300, CONDITION H</td><td>N/A</td></tr><tr><td></td><td></td><td></td><td>GOLD PLATE PER MIL-G-45204</td></tr></table>	HOUSING	COMPONENT	MATERIAL	FINISH	BERYLLIUM COPPER PER ASTM-B-196, ALLOY C17300, CONDITION H	DIELECTRIC	PTFE FLUOROCARBON PER ASTM-D-1457	GOLD PLATE PER MIL-G-45204	CENTER CONTACT CONTACT FINGER ANTI-ROCK RING EMI RING		BERYLLIUM COPPER PER ASTM B 196, ALLOY C17300, CONDITION H	N/A				GOLD PLATE PER MIL-G-45204	<table><tr><td>UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES</td><td>DRAWN BY <i>AD</i> DATE <u>4/15/93</u></td><td rowspan="3"></td><td rowspan="3">AMP Incorporated 140 Fourth Avenue Waltham, MA 02451-7599</td></tr><tr><td>FRAC. DEC. ANGLES ± 1/64 ±.005 ± 1°</td><td>CHECKED BY <i>AD</i></td></tr><tr><td></td><td>APPD BY <i>DC</i> DATE <u>4/21/93</u></td></tr><tr><td rowspan="3">These drawings and specifications are the property of AMP Incorporated and shall not be reproduced or copied or used in whole or in part as the basis for the manufacture or sale of item(s) without written permission.</td><td>USE ASSY PROCEDURE</td><td colspan="2">TITLE OSMP RIGHT ANGLE CABLE JACK DIRECT SOLDER ATTACHMENT</td></tr><tr><td>408-04740 NO. A.P. <u>29-002</u></td><td>SIZE B</td><td>CODE IDENT NO. 26805</td></tr><tr><td></td><td>2908-7985-62</td><td>REV 03<sub>0</sub></td></tr><tr><td></td><td></td><td>SCALE 10:1</td><td>SHEET 1 OF 1</td></tr></table>	UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES	DRAWN BY <i>AD</i> DATE <u>4/15/93</u>		AMP Incorporated 140 Fourth Avenue Waltham, MA 02451-7599	FRAC. DEC. ANGLES ± 1/64 ±.005 ± 1°	CHECKED BY <i>AD</i>		APPD BY <i>DC</i> DATE <u>4/21/93</u>	These drawings and specifications are the property of AMP Incorporated and shall not be reproduced or copied or used in whole or in part as the basis for the manufacture or sale of item(s) without written permission.	USE ASSY PROCEDURE	TITLE OSMP RIGHT ANGLE CABLE JACK DIRECT SOLDER ATTACHMENT		408-04740 NO. A.P. <u>29-002</u>	SIZE B	CODE IDENT NO. 26805		2908-7985-62	REV 03 <sub>0</sub>			SCALE 10:1	SHEET 1 OF 1
ELECTRICAL	MECHANICAL	ENVIRONMENTAL																																																																							
Nominal Impedance (Ohms) <u>50</u>	Force to Engage (Lbs MAX) <u>15</u>	Temperature Rating <u>-65°C To +125°C</u>																																																																							
Frequency Range (GHz) DC to <u>26.5</u>	Disengage (Lbs MIN) <u>2.0</u>	Vibration MIL-STD-202, Method 204, Condition D																																																																							
Volt Rating (VRMS MAX) @ Sea Level <u>250</u>	Center Contact Retention <u>1.5 Lbs MIN</u>	Thermal Shock MIL-STD-202, Method 107, Condition B,																																																																							
VSWR <u>1.25 MAX</u> @ 26.5 GHz	Durability <u>100 cycles</u>	Corrosion - MIL-STD-202, Method 101, Condition B																																																																							
Insertion Loss <u>.12f GHz dB MIN</u>																																																																									
Corona, 70,000 Ft (VRMS MIN) <u>190</u>																																																																									
Dielectric Withstanding Voltage (VRMS MIN) @ Sea Level <u>500</u>																																																																									
Contact Resistance (Milliohms MAX) Center Contact <u>6.0</u> Outer Contact <u>2.0</u> Cable to Housing <u>0.5</u>	DESIGNED FOR USE WITH <u>.085 DIA S.R.</u>																																																																								
RF High Potential @ Sea Level (VRMS MIN @ 5 MHz) <u>325</u>	CABLE ENTRY DIAMETER MINIMUM HOUSING <u>.089</u>																																																																								
IR.(Megohms MIN) <u>5000</u>																																																																									
HOUSING	COMPONENT	MATERIAL	FINISH																																																																						
BERYLLIUM COPPER PER ASTM-B-196, ALLOY C17300, CONDITION H	DIELECTRIC	PTFE FLUOROCARBON PER ASTM-D-1457	GOLD PLATE PER MIL-G-45204																																																																						
CENTER CONTACT CONTACT FINGER ANTI-ROCK RING EMI RING		BERYLLIUM COPPER PER ASTM B 196, ALLOY C17300, CONDITION H	N/A																																																																						
			GOLD PLATE PER MIL-G-45204																																																																						
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES	DRAWN BY <i>AD</i> DATE <u>4/15/93</u>		AMP Incorporated 140 Fourth Avenue Waltham, MA 02451-7599																																																																						
FRAC. DEC. ANGLES ± 1/64 ±.005 ± 1°	CHECKED BY <i>AD</i>																																																																								
	APPD BY <i>DC</i> DATE <u>4/21/93</u>																																																																								
These drawings and specifications are the property of AMP Incorporated and shall not be reproduced or copied or used in whole or in part as the basis for the manufacture or sale of item(s) without written permission.	USE ASSY PROCEDURE	TITLE OSMP RIGHT ANGLE CABLE JACK DIRECT SOLDER ATTACHMENT																																																																							
	408-04740 NO. A.P. <u>29-002</u>	SIZE B	CODE IDENT NO. 26805																																																																						
		2908-7985-62	REV 03 <sub>0</sub>																																																																						
		SCALE 10:1	SHEET 1 OF 1																																																																						

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2908-7985-62](#)