



CONNECTOR ASSEMBLY EXAMPLARY LOADED



CONTACT DIMENSIONS



DO NOT SCALE
DIMENSIONS IN mm

METRIC

THIRD ANGLE
PROJECTION



CONTACT LAYOUT


	z	a	b	c	d	e	f
1	B	B	B	B	B		
2	C	B	C	C	C		
3	C	B	C	C	C		
4	C	B	C	C	C		
5	C	B	C	C	C		
6	C	B	C	C	C		
7	C	B	C	C	C		
8	C	B	C	C	C		
9	C	B	C	C	C		
10	C	B	C	C	C		
11	C	B	C	C	C		
MULTI PURPOSE CENTRE							
15	B	B	B	B	B		
16	B	B	B	B	B		
17	B	B	B	B	B		
18	B	B	B	B	B		
19	B	B	B	B	B		
20	B	B	B	B	B		
21	B	B	B	B	B		
22	B	B	B	B	B		
23	B	B	B	B	B		
24	B	B	B	B	B		
25	B	B	B	B	B		

THIS DRAWING IS
PRELIMINARY

NOTES:

- ⚠ PLATING
CONTACT AREA: 0,8µm Au MIN. OVER 1,3µm Ni MIN.
ACTION PIN : 0,5µm SnPb MIN. OVER 1,3µm Ni MIN.
- ⚠ MATERIAL CONTACT: PHOSPHORBRONZE.
MATERIAL HOUSING: GLASSFILLED POLYESTER.
- ⚠ CONNECTOR PRINTED WITH PARTNUMBER AND DATECODE.
- ⚠ PLATED-THROUGH HOLES AT 2x2mm SQUARE GRID.
TOTAL 110 HOLES .
- ⚠ AREA RESERVED FOR KEYING PART (BASIC P.N. 100525).
- ⚠ FOR ACTUAL PIN LOADING SEE "CONTACT LAYOUT"
- ⚠ POLARIZING NIPPLE

**RECOMMENDED PCB-HOLE LAY-OUT
COMPONENT SIDE SHOWN**



P.C.B. HOLE DIM. ACTION PIN
 DRILLED HOLE: 0,7±0,025mm
 FIN. HOLE : 0,55 TO 0,65mm
 Cu-thks : 0,025 TO 0,050mm
 SnPb-thks : 0,004 TO 0,010mm

				⚠	⚠	106755-1
				FINISH	MATERIAL	PARTNUMBER
-	-	-	-	-	-	-
CUSTOMER DRAWING FOR REFERENCE ONLY WILL NOT BE UPDATED						
© COPYRIGHT 19- BY AMP HOLLAND B.V. ALL INTERNATIONAL RIGHTS RESERVED. AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN AND/OR PATENTS PENDING. THIS DRAWING IS UNPUBLISHED RELEASED FOR PUBLICATION ,19-						
				AMP AMP HOLLAND B.V. 's-Hertogenbosch, The Netherlands.		
				NAME Z-PACK 2mm HM TYPE A 110 POS. MALE BACKPANEL CONNECTOR ASSEMBLY		
0	EH-0922-93	JVD	BM	01-DEC-93		
LTR.	REVISION RECORD	DR.	CHK.	DATE		
DR.:	J.V. DREUMEL	CHK.:	B. MOOIJ	APP.:		
DATE:	01-DEC-93	DATE:	01-DEC-93	DATE:	10-12-93	DWG. No. C-106755
				REV. LTR.	SHEET	A2
				0	1 OF 1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[106755-1](#)