



PART NUMBER	REV	FIRST USED
1385268 -1	A	122500-1
1385268 -2	A	565435-5
1385268 -3	A	354500-1



TERMINAL NAME: HARTING TERMINAL							
AMP PN		MFR PN		HARTING TERMINAL AMP CRIMP SPECS			
286954		0906-000-8471		PAD LTR	CRIMP HEIGHT		WIRE SIZE
				A	.038 ±.002 [0.97 ±0.05mm]		20
				B	NOT		USED
				C	NOT		USED
				D	NOT		USED
				CRIMP	SIZE	TYPE	RANGE
				WIRE	.070 [1.78mm]	F	20
				INSUL	.110 [2.79mm]	0	.080
WIRE STRIP LENGTH	TERM APPL SPEC	FEED	APPL INSTRUCTION	SET UP GAGE	LAYOUT		
—	—	.493	408-8040	458637-1	L2530		

							129
							128
							127
2	2	2	-	C	5-354779-1	PIN, WIRE DISC (.3245)A	126
1	1	1	-	A	986950-1	WASHER, FLAT PRECISION	125
1	1	1	-	A	217238-1	GENERAL INSTRUCTION PACKAGE	124
1	1	1	-	-	4088040	SF APPL INST 408-8040	123
							122
1	1	1	-	A	4-21028-0	PIN,SLT SPR(Ø.093x.75)ST GDE PL	121
REF	REF	REF	-	A	1-21030-1	PIN,DOWEL (Ø.187x.50)LEVER	120
REF	REF	REF	-	A	1-21030-6	PIN,DOWEL (Ø.187x1.25)HOUSING	119
REF	REF	REF	-	A	21045-3	RING,RET "C"(Ø.187)FD FING PIN	118
1	1	1	-	A	21024-5	WASHER, LOCK (#10)ADJ BLOCK	117
REF	REF	REF	-	A	21024-5	WASHER,LOCK (#10)ADJ. PLATE	116
REF	REF	REF	-	A	21024-5	WASHER, LOCK (#10)FEED GDE ROD	115
2	2	2	-	A	21024-2	WASHER,LOCK (#4)FRONT STP GUIDE	114
REF	REF	REF	-	A	5-21028-1	PIN,SLT SPR(Ø.125x.50)ADJ ROD	113
							112
4	4	4	-	A	21024-4	WASHER, LOCK (#8)STRIPPER	111
REF	REF	REF	-	A	21899-4	WASHER,FLAT (Ø5/16)SCREW ADJ	110
							109
1	1	1	-	A	21018-5	NUT, HEX (NO. 6)HOLDDOWN	108
REF	REF	REF	-	A	21068-5	NUT, HEX (6-32)FEED ADJ	107
							106
							105
1	1	-	-	A	992031-1	PIN, CLEVIS	104
1	1	1	-	A	21009-2	SCR,5KT SET(1/4-20x.25 LW)RAM	103
2	2	2	-	A	21017-2	SCR,DRIVE (#2x.19)ID PLATE	102
REF	REF	REF	-	A	6-23715-5	SCR,PAN HD (6-32x1.50)FEED ADJ	101
1	1	1	-	B	461264-1	PLATE, IDENTIFICATION	100
2	2	2	-	A	3-21002-0	SCR,BHC (10-32x.88)DRAG	99
1	1	1	-	A	22733-8	SCR,BHC (8-32x.38 LW)ANVIL	98
REF	REF	REF	-	A	2-21002-9	SCR,BHC (10-32x.75)CAP	97
REF	REF	REF	-	A	2-22733-8	SCR,BHC (1/4-20x.62)HOUSING	96
REF	REF	REF	-	A	2-21002-7	SCR,BHC (10-32x.50)SG ADJ BLOCK	95
4	4	4	-	A	2-21002-2	SCR,BHC (8-32x.50)TERM H DWN	94
2	2	2	-	A	2-21002-2	SCR,BHC (8-32x.62)R STP GDE	93
							92
1	1	1	-	A	1-21002-7	SCR,BHC (6-32x.38)CAM	91
							90
1	1	-	-	A	7-21000-9	SCR,SHC (4-40x.19)STRIPPER	89
							88
							87
1	1	1	-	A	2-22603-0	SCR,HEX HD (8-32x.31)FEED FINGER	86
2	2	2	-	A	1-21000-3	SCR,SHC (4-40x.25)F ST GUIDE	85
3	3	3	-	A	2-21000-7	SCR,SHC (8-32x.50)STRIPPER	84
REF	REF	REF	-	A	3-21000-7	SCR,SHC (10-32x.75)FEED ROD GD	83
REF	REF	REF	-	A	3-21000-6	SCR,SHC (10-32x.62)FD ADJ BLK	82
1	1	1	-	A	3-21000-4	SCR,SHC (10-32x.38)SG ADJ BL	81
REF	REF	REF	-	A	3-21000-4	SCR,SHC (10-32x.38)PIVOT BLK	80
-	REF	-	-	B	455749-1	GUARD, WINDOW	79
REF	-	-	-	B	679532-1	INSERT, GUARD	78
							77
							76
							75
1	1	1	-	A	690603-1	SPRING, ASSIST	74
1	1	1	-	A	23030-1	SCR,SHC (6-32x.25 SL)INS DISC	73
REF	REF	REF	-	A	458109-1	WASHER, SPECIAL	72
REF	REF	REF	-	A	690517-1	SPACER	71
-3	-2	-1	U/M	DWG SIZE	PART NO	DESCRIPTION	ITEM NO
QTY RECD PER ASSY				PARTS LIST			

-1			LEADMAKER			MECH POST FEED			
-2			BENCH MODEL K			MECH PRE FEED			
-3			BENCH MODEL G			MECH PRE FEED			
REF	REF	REF	-	B	22594-8	NUT, HEX (1/2-20)		70	
REF	REF	REF	-	B	240628-1	PLATE, ADJUSTMENT		69	
REF	REF	REF	-	B	240626-1	SHAFT, PIVOT		68	
REF	REF	REF	-	B	240633-1	BUSHING		67	
REF	REF	REF	-	A	455680-1	LEVER, INTERMEDIATE		66	
REF	REF	REF	-	B	240629-1	BLOCK, PIVOT		65	
REF	REF	REF	-	A	240632-2	SCREW, ADJ FEED ROD		64	
REF	REF	REF	-	B	240659-3	PIN, CAM ROLLER		63	
REF	REF	REF	-	B	240658-1	ROLLER, CAM		62	
REF	REF	REF	-	B	454398-2	ROD, FEED		61	
REF	REF	REF	-	A	454178-1	GUIDE, FEED ROD		60	
REF	REF	REF	-	C	454220-1	CAP, RAM		59	
REF	REF	REF	-	D	454485-1	HOUSING		58	
								57	
1	1	1	-	B	690542-2	PAWL, FEED		56	
REF	REF	REF	-	B	240624-1	PIN, FEED FINGER		55	
REF	REF	REF	-	B	691499-1	SPRING, FEED FINGER		54	
REF	REF	REF	-	B	690541-1	HOLDER, FEED FINGER		53	
REF	REF	REF	-	A	455679-1	LEVER, TERMINAL FEED ARM		52	
1	1	1	-	A	811242-2	BUMPER, HOLDDOWN		51	
1	1	1	-	A	690753-1	SPACER, TONKER		50	
1	-	-	-	B	690602-6	CAM, PRE-FEED 1 5/8 ST		49	
-	1	-	-	B	690602-5	CAM, PRE-FEED 1 1/8 ST		48	
-	-	1	-	B	690501-4	CAM, POST-FEED 1 5/8 ST		47	
1	1	1	-	B	459456-1	APPLICATOR, BASIC (SUBASSY)		46	
1	1	1	-	A	690191-1	PLUG, NYLON		45	
1	1	1	-	C	455673-1	RAM		44	
1	1	1	-	A	690125-1	WASHER, LAMINATED		43	
1	1	1	-	A	690124-1	WASHER, RAM		42	
1	1	1	-	A	7-21002-9	BOLT, CRIMPER (5/16x1.00)		41	
1	1	1	-	A	23241-6	BALL, STEEL		40	
1	1	1	-	A	690170-1	SPRING, COMPRESSION		39	
1	1	1	-	C	690142-1	DISC, INSULATION		38	
1	1	1	-	D	354777-1	WIRE DISC, PLASTIC		37	
1	1	1	-	A	22480-5	WASHER, SPRING		36	
1	1	1	-	B	690212-1	POST, RAM		35	
1	1	1	-	B	690786-1	SUPPORT, TERMINAL		34	
REF	REF	REF	-	D	455675-1	PLATE, BASE		33	
1	1	1	-	A	690432-3	SCREW, ADJUSTMENT		32	
								31	
REF	REF	REF	-	B	455689-1	BLOCK, STRIP GUIDE ADJ		30	
1	1	1	-	C	2-455671-0	PLATE, STRIP GUIDE		29	
1	1	1	-	C	1-455888-2	SPACER, FRONT SHEAR DEP		28	
2	2	2	-	A	1-22284-0	SPRING, DRAG		27	
1	1	1	-	B	690546-1	LEVER, DRAG RELEASE		26	
1	1	1	-	B	240792-1	DRAG, TERMINAL		25	
1	1	1	-	D	6-690504-8	GUIDE, STRIP (REAR)		24	
1	1	1	-	A	690438-1	GUIDE, STRIP (FRONT)		23	
-	-	1	-	B	690472-2	STRIPPER		22	
REF	REF	REF	-	A	4-22284-9	SPRING, FEED RETURN		21	
1	1	-	-	A	679218-1	STRIPPER WIRE STOP ASSY		20	
1	1	-	-	B	458949-1	STRIPPER		19	
								18	
								17	
1	1	1	-	B	318563-1	GUARD, CHIP, FRONT		16	
								15	
								14	
								13	
1	1	1	-	A	5-22280-0	SPRING, SHEAR		12	
1	1	1	-	B	690461-1	STOP, SHEAR		11	
1	1	1	-	C	690459-1	HOLDER, SHEAR (FRONT)		10	
1	1	1	-	C	462006-2	SHEAR, FLOAT (FRONT)		9	
1	1	1	-	C	4-662185-3	ANVIL		8	
								7	
								6	
1	1	1	-	C	1-455889-4	DEPRESSOR, SHEAR (FRONT)		5	
1	1	1	-	B	238011-4	SPACER, BLOCK CRIMPER		4	
1	1	1	-	C	9-456135-3	CRIMPER, INSULATION		3	
1	1	1	-	C	455888-4	SPACER, CRIMPER		2	
1	1	1	-	C	1-456404-5	CRIMPER, WIRE		1	
-3	-2	-1	U/M	DWG SIZE	PART NO	DESCRIPTION		ITEM NO	
← REVISION OF EACH ASSY NO (WHEN BLANK, USE DWG REVISION)									
QTY REQD PER ASSY					PARTS LIST				



1. RECOMMENDED SPARE PARTS.
2. GREASE LIGHTLY.
3. GUARD MUST BE IN PLACE WHEN OPERATING APPLICATOR IN A BENCH MACHINE.
4. LUBRICATE DAILY USING NO. 20 MACHINE OIL.
5. ITEMS WITH QTY OF REF SPECIFIED (EXCEPT ITEMS 78 AND 79) ARE USED ON ITEM 46.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1385268-1](#)