


P-Channel 30 V (D-S) MOSFET



PRODUCT SUMMARY	
V_{DS} (V)	-30
$R_{DS(on)}$ max. (Ω) at $V_{GS} = -10$ V	0.0055
$R_{DS(on)}$ max. (Ω) at $V_{GS} = -4.5$ V	0.0093
Q_g typ. (nC)	36
I_D (A)	-60 ^{a, g}
Configuration	Single

ORDERING INFORMATION	
Package	PowerPAK SO-8
Lead (Pb)-free and halogen-free	SiR167DP-T1-GE3

ABSOLUTE MAXIMUM RATINGS ($T_A = 25^\circ\text{C}$, unless otherwise noted)				
PARAMETER	SYMBOL	LIMIT	UNIT	
Drain-source voltage	V_{DS}	-30	V	
Gate-source voltage	V_{GS}	± 25		
Continuous drain current ($T_J = 150^\circ\text{C}$)	$T_C = 25^\circ\text{C}$	-60 ^a	A	
	$T_C = 70^\circ\text{C}$	-60 ^a		
	$T_A = 25^\circ\text{C}$	-23.8 ^{b, c}		
	$T_A = 70^\circ\text{C}$	-19.1 ^{b, c}		
Pulsed drain current ($t = 100 \mu\text{s}$)	I_{DM}	-120		
Continuous source-drain diode current	$T_C = 25^\circ\text{C}$	-54.8		
	$T_A = 25^\circ\text{C}$	-4.2 ^{b, c}		
Single pulse avalanche current	I_{AS}	-20		
Single pulse avalanche energy	E_{AS}	20	mJ	
Maximum power dissipation	$T_C = 25^\circ\text{C}$	65.8	W	
	$T_C = 70^\circ\text{C}$	42.1		
	$T_A = 25^\circ\text{C}$	5.1 ^{b, c}		
	$T_A = 70^\circ\text{C}$	3.2 ^{b, c}		
Operating junction and storage temperature range	T_J, T_{stg}	-55 to +150		$^\circ\text{C}$
Soldering recommendations (peak temperature) ^c		260		

THERMAL RESISTANCE RATINGS					
PARAMETER		SYMBOL	TYPICAL	MAXIMUM	UNIT
Maximum junction-to-ambient ^b	$t \leq 10$ s	R_{thJA}	20	25	$^\circ\text{C/W}$
Maximum junction-to-case (drain)	Steady state	R_{thJC}	1.5	1.9	

Notes

- Package limited
- Surface mounted on 1" x 1" FR4 board
- $t = 10$ s
- See solder profile (www.vishay.com/doc?73257). The PowerPAK SO-8 is a leadless package. The end of the lead terminal is exposed copper (not plated) as a result of the singulation process in manufacturing. A solder fillet at the exposed copper tip cannot be guaranteed and is not required to ensure adequate bottom side solder interconnection
- Rework conditions: manual soldering with a soldering iron is not recommended for leadless components
- Maximum under steady state conditions is 65°C/W
- $T_C = 25^\circ\text{C}$

FEATURES


- TrenchFET[®] Gen III p-channel power MOSFET
- 100 % R_g and UIS tested
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912



RoHS
COMPLIANT
HALOGEN
FREE

APPLICATIONS

- Adapter and charger switch
- Load switch
- Battery management



P-Channel MOSFET









SPECIFICATIONS (T _J = 25 °C, unless otherwise noted)						
PARAMETER	SYMBOL	TEST CONDITIONS	MIN.	TYP.	MAX.	UNIT
Static						
Drain-source breakdown voltage	V _{DS}	V _{GS} = 0 V, I _D = -250 μA	-30	-	-	V
V _{DS} temperature coefficient	ΔV _{DS} /T _J	I _D = -10 mA	-	-25.8	-	mV/°C
V _{GS(th)} temperature coefficient	ΔV _{GS(th)} /T _J	I _D = -250 μA	-	4.2	-	
Gate-source threshold voltage	V _{GS(th)}	V _{DS} = V _{GS} , I _D = -250 μA	-1	-	-2.5	V
Gate-source leakage	I _{GSS}	V _{DS} = 0 V, V _{GS} = ± 25 V	-	-	100	nA
Zero gate voltage drain current	I _{DSS}	V _{DS} = -30 V, V _{GS} = 0 V	-	-	-1	μA
		V _{DS} = -30 V, V _{GS} = 0 V, T _J = 70 °C	-	-	-15	
On-state drain current ^a	I _{D(on)}	V _{DS} ≥ -10 V, V _{GS} = -10 V	-30	-	-	A
Drain-source on-state resistance ^a	R _{DS(on)}	V _{GS} = -10 V, I _D = -15 A	-	0.0046	0.0055	Ω
		V _{GS} = -4.5 V, I _D = -10 A	-	0.0078	0.0093	
Forward transconductance ^a	g _{fs}	V _{DS} = -15 V, I _D = -20 A	-	60	-	S
Dynamic ^b						
Input capacitance	C _{iSS}	V _{DS} = -15 V, V _{GS} = 0 V, f = 1 MHz	-	4380	-	pF
Output capacitance	C _{oss}		-	535	-	
Reverse transfer capacitance	C _{rSS}		-	460	-	
Total gate charge	Q _g	V _{DS} = -15 V, V _{GS} = -10 V, I _D = -23.8 A	-	74	111	nC
Gate-source charge	Q _{gs}	V _{DS} = -15 V, V _{GS} = -4.5 V, I _D = -23.8 A	-	36	54	
Gate-drain charge	Q _{gd}		-	12.1	-	
Gate resistance	R _g		-	12.3	-	
Gate resistance	R _g	f = 1 MHz	0.32	1.6	3.2	Ω
Turn-on delay time	t _{d(on)}	V _{DD} = -15 V, R _L = 0.79 Ω, I _D ≅ -19.1 A, V _{GEN} = -10 V, R _g = 1 Ω	-	20	40	ns
Rise time	t _r		-	25	50	
Turn-off delay time	t _{d(off)}		-	35	70	
Fall time	t _f		-	18	36	
Turn-on delay time	t _{d(on)}	V _{DD} = -15 V, R _L = 0.79 Ω, I _D ≅ -19.1 A, V _{GEN} = -4.5 V, R _g = 1 Ω	-	25	50	
Rise time	t _r		-	25	50	
Turn-off delay time	t _{d(off)}		-	35	70	
Fall time	t _f		-	22	44	
Drain-Source Body Diode Characteristics						
Continuous source-drain diode current	I _S	T _C = 25 °C	-	-	-54.8	A
Pulse diode forward current	I _{SM}		-	-	-120	
Body diode voltage	V _{SD}	I _S = -5 A, V _{GS} = 0 V	-	-0.73	-1.2	V
Body diode reverse recovery charge	Q _{rr}	I _F = -19.1 A, di/dt = 100 A/μs, T _J = 25 °C	-	45	90	nC
Reverse recovery fall time	t _a		-	19	-	ns
Reverse recovery rise time	t _b		-	22	-	


Notes

- a. Pulse test; pulse width $\leq 300\text{ }\mu\text{s}$, duty cycle $\leq 2\%$
b. Guaranteed by design, not subject to production testing


Stresses beyond those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated in the operational sections of the specifications is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.

TYPICAL CHARACTERISTICS (25 °C, unless otherwise noted)



TYPICAL CHARACTERISTICS (25 °C, unless otherwise noted)




Source-Drain Diode Forward Voltage




Threshold Voltage






On-Resistance vs. Gate-to-Source Voltage





Single Pulse Power, Junction-to-Ambient



Safe Operating Area, Junction-to-Ambient

TYPICAL CHARACTERISTICS (25 °C, unless otherwise noted)

Current Derating ^a

Power, Junction-to-Case

Power, Junction-to-Ambient
Note

- a. The power dissipation P_D is based on T_J max. = 150 °C, using junction-to-case thermal resistance, and is more useful in settling the upper dissipation limit for cases where additional heatsinking is used. It is used to determine the current rating, when this rating falls below the package limit

TYPICAL CHARACTERISTICS (25 °C, unless otherwise noted)

Normalized Thermal Transient Impedance, Junction-to-Ambient

Normalized Thermal Transient Impedance, Junction-to-Case

Vishay Siliconix maintains worldwide manufacturing capability. Products may be manufactured at one of several qualified locations. Reliability data for Silicon Technology and Package Reliability represent a composite of all qualified locations. For related documents such as package / tape drawings, part marking, and reliability data, see www.vishay.com/ppg?76017.



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Vishay:

[SIR167DP-T1-GE3](#)