

K43C334=RELAY, VACUUM, SPDT

✓ ACTIVE

Kilovac | Kilovac K43

TE Part # 2-1618240-7

TE Internal #: K43C334

[View on TE.com >](#)



Relays, Contactors & Switches > Relays > High Voltage Relays



Contact Voltage Rating: 10 kVDC

Contact Arrangement: 1 Form C, SPDT

High Voltage Connection (Coil): Bus Wires

High Voltage Connection (Power): High Voltage Tabs

Economizer: Without

Features

Product Type Features

RF Rated	Yes
Product Type	Relay
Relay Type	High Voltage

Configuration Features

Economizer	Without
Power Switching	Yes

Electrical Characteristics

Contact Voltage Rating	10 kVDC
Voltage (Max)	26.5 VDC
Coil Voltage Rating	26.5 VDC
Coil Resistance	290 Ω

Contact Features

Contact Arrangement	1 Form C, SPDT
Auxiliary Contacts	Without
Contact Current Rating	25 A

Termination Features

High Voltage Connection (Coil)	Bus Wires
High Voltage Connection (Power)	High Voltage Tabs
Termination Style	Bus Wires



Mechanical Attachment

Mounting Type	Non-Flanged
---------------	-------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2019 (197) Candidate List Declared Against: JAN 2019 (197)
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not lead free process capable

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE’s information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) ‘Guidance on requirements for substances in articles’(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts



TE Part # 1-1618239-8
K41A334=RELAY,
VACUUM, SPST-NO



Also in the Series | Kilovac K43



High Voltage Relays(29)


Customers Also Bought




TE Part #5-1618239-0
K41C334=RELAY,
VACUUM, SPDT




TE Part #861648-7
PLUG ASSY HV 7 PIN



TE Part #926933-3
WIRE PIN 18-17 AWG .01
PTPB




TE Part #2-647127-7
07P MTA156 SHRDR HDR
ASSY LF




TE Part #60432-1
FAST REC IS 22-18 PTPBR



TE Part #8-34823-2
TERMINAL,PG R 16-14HD
10



TE Part #926539-3
FASTON 250 HSG NYLON
BLACK



TE Part #1-1658526-0
609-1601MLF FEM SCKT,
LEAD FREE



TE Part #1625856-7
RH73 2A 50M 5% 100PPM



TE Part #3-1393763-7
V23100V4315C011

Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2-1618240-7_R.2d_dxf.zip

English

Customer View Model



[ENG_CVM_CVM_2-1618240-7_R.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2-1618240-7_R.3d_stp.zip](#)

English

Datasheets & Catalog Pages

[5-1773450-5_sec7_K43](#)

English

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[K43C334](#)