

1006X=WILMAR PHASE FAILURE RE

✓ ACTIVE

Kilovac | Kilovac 1000 Series

TE Part # 1-1618059-8

TE Internal #: 1006X

[View on TE.com >](#)



Relays, Contactors & Switches > Relays > Protective Relays



Contact Arrangement: 1 Form A, SPST-NO, 1 NO

Contact Current Rating: 10 A

Input Voltage: 575 VAC

Time Delay: Without

Mounting Type: Flanged

Features

Product Type Features

Relay Type	Protective Relay
Product Type	Relay
Protection Function	Phase Failure, Voltage Sensitive
Time Delay	Without
Phase	Three

Electrical Characteristics

Actuating System	AC
Input Voltage	575 VAC

Contact Features

Contact Arrangement (Additional Output)	None
Contact Arrangement	1 Form A, SPST-NO, 1 NO
Contact Current Rating	10 A

Mechanical Attachment

Mounting Type	Flanged
---------------	---------

Usage Conditions

Operating Temperature Range	-40 – 70 °C
-----------------------------	-------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)



EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2019 (197) Candidate List Declared Against: JAN 2019 (197)
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE’s information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) ‘Guidance on requirements for substances in articles’(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts



TE Part # 1-1618059-6
[1004X=WILMAR PHASE FAILURE RE](#)

Also in the Series | [Kilovac 1000 Series](#)



Protective Relays(6)

Customers Also Bought



TE Part #66601-8
III+ SKT,18-14,30AU/FL,
SMPACK



TE Part #320755
TERMINAL,SOLIS R 2 3/4




TE Part #6-1437622-9
KN900BA1/4=KNOB
KNURL BLK/ALUM



TE Part #1-1437391-8
0525=MD SECT BLCK
DOVETAIL BAS



TE Part #2329359-1
PN OFF/ON HC BLK M1
TERM IP68 500MM LHS




TE Part #607381P038
SCT-NO.2-E5-0-27MM




TE Part #001885-000
ST63-4-00



TE Part #365881-000
TXR41AB00-2407AI



TE Part #474575-000
TXR41AB00-2408AI



TE Part #168289-000
TXR41AB00-2414AI

Documents

[Datasheets & Catalog Pages](#)
[5-1773450-5_sec11_1000](#)

English

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1006X](#)